THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -.- .
© COPYRIGHT - By - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	P5	REVISED PER ECO-16-012733	01SEP2016	NK	MM
	P6	REVISED PER ECO-18-014731	18SEP2018	RS	MM





1 TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADERS ARE HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD.

2 ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS.

△3 .000100–.000200 MATTE TIN–LEAD OVER .000050 NICKEL.

△4 .000100–.000200 BRIGHT TIN OVER .000050 NICKEL.

△5 PRELIMINARY PART – NOT RELEASED FOR PRODUCTION.

△6 HOUSING MATERIAL: FLAME RETARDANT THERMOPLASTIC; COLOR–BLACK.

△7 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



RECOMMENDED HOLE LAYOUT

		A	B	C	NO OF POSN	PART NUMBER
△5	△4	1.684	1.600	16	34	4-103328-9
△5	△4	1.284	1.200	12	26	4-103328-8
	△4	.884	.800	8	18	4-103328-7
△7 OBSOLETE	△4	.584	.500	5	12	~~4-103328-6~~
	△4	3.984	3.900	39	80	4-103328-5
	△4	.984	.900	9	20	4-103328-4
	△4	.684	.600	6	14	4-103328-3
	△4	.284	.200	2	6	4-103328-2
	△4	.084	——	——	2	4-103328-1
	△3	3.984	3.900	39	80	4-103328-0
△7 OBSOLETE	△3	3.884	3.800	38	78	~~3-103328-9~~
△7 OBSOLETE	△3	3.784	3.700	37	76	~~3-103328-8~~
△7 OBSOLETE	△3	3.684	3.600	36	74	~~3-103328-7~~
△7 OBSOLETE	△3	3.584	3.500	35	72	~~3-103328-6~~
	△3	3.484	3.400	34	70	3-103328-5
△7 OBSOLETE	△3	3.384	3.300	33	68	~~3-103328-4~~
△7 OBSOLETE	△3	3.284	3.200	32	66	~~3-103328-3~~
△7 OBSOLETE	△3	3.184	3.100	31	64	~~3-103328-2~~
△7 OBSOLETE	△3	3.084	3.000	30	62	~~3-103328-1~~
△7 OBSOLETE	△3	2.984	2.900	29	60	~~3-103328-0~~
△7 OBSOLETE	△3	2.884	2.800	28	58	~~2-103328-9~~
△7 OBSOLETE	△3	2.784	2.700	27	56	~~2-103328-8~~
△7 OBSOLETE	△3	2.684	2.600	26	54	~~2-103328-7~~
△7 OBSOLETE	△3	2.584	2.500	25	52	~~2-103328-6~~
	△3	2.484	2.400	24	50	2-103328-5
△7 OBSOLETE	△3	2.384	2.300	23	48	~~2-103328-4~~
△7 OBSOLETE	△3	2.284	2.200	22	46	~~2-103328-3~~
△7 OBSOLETE	△3	2.184	2.100	21	44	~~2-103328-2~~
△7 OBSOLETE	△3	2.084	2.000	20	42	~~2-103328-1~~
	△3	1.984	1.900	19	40	2-103328-0
△7 OBSOLETE	△3	1.884	1.800	18	38	~~1-103328-9~~
△7 OBSOLETE	△3	1.784	1.700	17	36	~~1-103328-8~~
	△3	1.684	1.600	16	34	1-103328-7
	△3	1.584	1.500	15	32	1-103328-6
△7 OBSOLETE	△3	1.484	1.400	14	30	~~1-103328-5~~
	△3	1.384	1.300	13	28	1-103328-4
	△3	1.284	1.200	12	26	1-103328-3
	△3	1.184	1.100	11	24	1-103328-2
△7 SUPERSEDED BY 6-146254-1	△3	1.084	1.000	10	22	~~1-103328-1~~
	△3	.984	.900	9	20	1-103328-0
	△3	.884	.800	8	18	103328-9
	△3	.784	.700	7	16	103328-8
	△3	.684	.600	6	14	103328-7
	△3	.584	.500	5	12	103328-6
	△3	.484	.400	4	10	103328-5
	△3	.384	.300	3	8	103328-4
	△3	.284	.200	2	6	103328-3
	△3	.184	.100	1	4	103328-2
	△3	.084	——	——	2	103328-1
	PLATING	C	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± –
1 PLC ± –
2 PLC ± –
3 PLC ± .005
4 PLC ± –
ANGLES ± –

MATERIAL: POST: COPPER ALLOY △6

FINISH: SEE TABLE

DWN J.MARTINELLI 10/15/92
CHK JOHN KNITTLE 23NOV92
APVD B. FLINCHBAUGH 23NOV92
PRODUCT SPEC —
APPLICATION SPEC —
WEIGHT —

TE Connectivity

NAME: ASSEMBLY, HEADER, BREAKAWAY, MOD II, DOUBLE ROW, .100 X .100 C/L, VERTICAL, WITH .025 SQUARE POSTS

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A1	00779	C-103328	—

CUSTOMER DRAWING | SCALE 4:1 | SHEET 1 OF 1 | REV P6

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TE Connectivity:

103328-5