

LOC		DIST		REVISIONS				
P	LTR	DESCRIPTION			DATE	DWN	APVD	
		D1	REVISED	PER				
GP	00			ECO-11-004835	11MAR11	RK	HMR	

- 1

FOR MINI-APPLICATOR AND STRIPPER CRIMPER.
- 2





FOR HAND TOOL USE ONLY.
3. WIRE RANGE OF 20-24 AWG. INSULATION RANGE OF 1.27/1.52 [.050-.060].
4. TIN PLATING MAY NOT APPEAR ON CARRIER STRIP.
- 5

GOLD FLASH ON INSIDE OF LOCALIZED GOLD PLATE AREA, 2.54μm [.000100] TIN PLATED ON CRIMP BARRELS, ALL OVER 0.76μm [.000030] NICKEL UNDERPLATE.
- 6

PLATED WITH 0.76μm [.000030] GOLD ON INSIDE OF LOCALIZED GOLD PLATE AREA, 2.54μm [.000100] TIN ON CRIMP BARRELS, ALL OVER 1.27μm [.000050] NICKEL UNDERPLATE.
-OR-
GOLD FLASH OVER PALLADIUM-NICKEL, 0.76μm [.000030] TOTAL ON INSIDE OF LOCALIZED GOLD PLATE AREA, 2.54μm [.000100] TIN ON CRIMP BARRELS, ALL OVER 1.27μm [.000050] NICKEL UNDERPLATE.
- 7

GOLD FLASH ON INSIDE OF LOCALIZED GOLD PLATE AREA, 0.76μm [.000030] MIN TIN ON CRIMP BARRELS, ALL OVER 0.76μm [.000030] MIN NICKEL UNDERPLATE.
- 8

SPECIAL PACKAGING.



6	1	-	8 1658537-6
7	1	-	1658537-5
6	2	SEE DETAIL Z	1658537-4
6	1	-	1658537-3
5	2	SEE DETAIL Z	1658537-2
5	1	-	1658537-1
FINISH	USE	LOOSE PIECE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G. ATTADIA - 01-10-05	TE Connectivity	
		CHK J. GERACE - 01-10-05		
DIMENSIONS: mm [INCHES]		APVD M. WALMSLEY 01-10-05	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		
0 PLC ± -		108-40005		
1 PLC ± -		APPLICATION SPEC		
2 PLC ± 0.13 [.005]		114-10000		
3 PLC ± -		SIZE		
4 PLC ± -		CAGE CODE		
ANGLES		DRAWING NO		
FINISH		RESTRICTED TO		
MATERIAL PHOSPHOR BRONZE		A1 00779 1658537		
SEE TABLE		CUSTOMER DRAWING		
		SCALE - SHEET 1 OF 1 REV D1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1658537-6](#)