




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B2	Released as per ECR-09-006012	16-MAR-09	SP	JC
	B3	ECR-13-007968	14MAY2013	KR	TN
	S	ECR-16-003733	14MAR2016	KR	TN

LASER MARKING: TE LOGO PN VALUE
TOLERANCE & DATE CODE




- 1 FOR FURTHER INFORMATION SEE DATA SHEET FOR
HS SERIES-ALUMINIUM HOUSED RESISTORS
- 2 FOR A SPECIFIC PN FOR A RESISTANCE VALUE
AND TOLERANCE, PLEASE REFER TO DMF
- 3 TECHNICAL SPECIFICATION

DISSIPATION AT 25°C : 10 WATTS MOUNTED
ON STD HEATSINK
BS OHMIC RANGE : R051 TO 7KS
STABILITY : ΔR < =1% PER 1000Hrs
ISOLATION VOLTAGE : 1400V DC/AC pk
MAX WORKING VOLTAGE : 150V DC/AC rms
TEMP COEFFICIENT : > 1R0 50ppm
> 100R 25ppm
CLIMATIC CATEGORY : 55/200/56



RoHS Compliant



SCALE 2:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVE KENNEDY 30.SEP.05	TE TE Connectivity		
DIMENSIONS: mm		CHK J CATCHPOLE 03.OCT.05			
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD J CATCHPOLE 03.OCT.05	NAME HSA 5 METAL CLAD RESISTOR		
		PRODUCT SPEC	-		
	0 PLC ±0.5 1 PLC ±0.2 2 PLC ±0.1 3 PLC ± 4 PLC ± ANGLES ±5°	APPLICATION SPEC	-		
		WEIGHT	-		
MATERIAL -	FINISH -	CUSTOMER DRAWING	SIZE A3	CAGE CODE 00779	DRAWING NO C-1676814
material_2	finish_spec_2		SCALE 4:1	SHEET 1 OF 1	REV S

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1676814-7](#)