




- 1 Gehaeuse fuer MQS-Kontakt:
PN 928999, 1355717, 963715
- 2 Verwendet mit 2050723
- 3 Verpackung: Schuetgut im Karton
- 4 Kammerbestueckung: Maximal 25% der Kontaktkammern
bestueckt mit Kontakten mit Kabelquerschnitt 0.5mm²,
gleichmaessig verteilt ueber das Gehaeuse ist zulaessig.
Groessere Kabelquerschnitte sind nicht zulaessig.

- 1 HOUSING FOR MQS-CONTACT:
PN 928999, 1355717, 963715
- 2 USED WITH 2050723
- 3 PACKAGING: LOOSE PIECE IN BOX
- 4 ASSIGNMENT OF CAVITIES: MAXIMUM 25% OF CONTACT
CAVITIES ASSIGNED WITH CONTACTS WITH A CABLE
CROSS SECTION OF 0.5mm^2 , UNIFORMLY DISTRIBUTED
OVER THE HOUSING. LARGER CABLE CROSS SECTION
ARE NOT PERMISSIBLE.

A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN MANJU DG	30AUG2012	 TE Connectivity	
		CHK RUDRESH BT	30AUG2012		
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	-	NAME	SOCKET HOUSING, 32 POSN. MQS Buchsengehaeuse, 32 pol. MQS
		PRODUCT SPEC		SIZE	CAGE CODE
		108-18924			
		APPLICATION SPEC		DRAWING NO	RESTRICTED TO
		114-18630			
MATERIAL	ANGLES FINISH	WEIGHT	-	A2	00779
-	-	CUSTOMER DRAWING		SCALE	5.1
				SHEET	1 OF 1
				REV	A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1719059-1](#)