

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
AD	00		H3	REVISED PER ECO-11-004917	11MAR11	RK HMR

- 1

POINT OF MEASUREMENT FOR PLATING THICKNESS
- 2



THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
3.

TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADERS ARE HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD
- 4

FINISH: POSTS, .000030 GOLD IN CONTACT AREA, .000100-.000200 MATTE TIN-LEAD ON SOLDER TAIL, ALL OVER .000050 NICKEL.
- 5

FINISH: POSTS, .000030 GOLD IN CONTACT AREA, .000100-.000200 MATTE TIN ON SOLDER TAIL, ALL OVER .000050 NICKEL.
- 6

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



RECOMMENDED HOLE LAYOUT

6	OBSOLETE	5	.284	.200	2	3	9-103336-0
6	OBSOLETE	5	.684	.600	6	7	8-103336-9
6	OBSOLETE	5	.484	.400	4	5	8-103336-8
		5	.584	.500	5	6	8-103336-7
6	OBSOLETE	5	.384	.300	3	4	8-103336-6
6	OBSOLETE	5	.084	0	0	1	8-103336-5
		5	.184	.100	1	2	8-103336-4
		5	3.984	3.900	39	40	8-103336-3
6	OBSOLETE	5	3.584	3.500	35	36	7-103336-9
6	OBSOLETE	5	3.184	3.100	31	32	7-103336-5
6	OBSOLETE	5	2.984	2.900	29	30	7-103336-3
6	OBSOLETE	5	2.484	2.400	24	25	6-103336-8
6	OBSOLETE	5	1.984	1.900	19	20	6-103336-3
6	OBSOLETE	5	1.884	1.800	18	19	6-103336-2
6	OBSOLETE	5	1.784	1.700	17	18	6-103336-1
6	OBSOLETE	5	1.684	1.600	16	17	6-103336-0
		5	1.584	1.500	15	16	5-103336-9
6	OBSOLETE	5	1.484	1.400	14	15	5-103336-8
6	OBSOLETE	5	1.384	1.300	13	14	5-103336-7
6	OBSOLETE	5	1.284	1.200	12	13	5-103336-6
		5	1.184	1.100	11	12	5-103336-5
6	OBSOLETE	5	1.084	1.000	10	11	5-103336-4
6	OBSOLETE	5	.984	.900	9	10	5-103336-3
6	OBSOLETE	5	.884	.800	8	9	5-103336-2
6	OBSOLETE	5	.784	.700	7	8	5-103336-1
	PLATING	C	B	A	NO OF POSN	ASSEMBLY PART NUMBER	

△	OBSOLETE	△	.284	.200	2	3	4-103336-0
		△	.684	.600	6	7	3-103336-9
		△	.484	.400	4	5	3-103336-8
		△	.584	.500	5	6	3-103336-7
		△	.384	.300	3	4	3-103336-6
△	OBSOLETE	△	.084	0	0	1	3-103336-5
		△	.184	.100	1	2	3-103336-4
		△	3.984	3.900	39	40	3-103336-3
		△	3.884	3.800	38	39	3-103336-2
		△	3.784	3.700	37	38	3-103336-1
△	OBSOLETE	△	3.684	3.600	36	37	3-103336-0
		△	3.584	3.500	35	36	2-103336-9
		△	3.484	3.400	34	35	2-103336-8
		△	3.384	3.300	33	34	2-103336-7
		△	3.284	3.200	32	33	2-103336-6
△	OBSOLETE	△	3.184	3.100	31	32	2-103336-5
		△	3.084	3.000	30	31	2-103336-4
		△	2.984	2.900	29	30	2-103336-3
		△	2.884	2.800	28	29	2-103336-2
		△	2.784	2.700	27	28	2-103336-1
△	OBSOLETE	△	2.684	2.600	26	27	2-103336-0
		△	2.584	2.500	25	26	1-103336-9
		△	2.484	2.400	24	25	1-103336-8
		△	2.384	2.300	23	24	1-103336-7
		△	2.284	2.200	22	23	1-103336-6
△	OBSOLETE	△	2.184	2.100	21	22	1-103336-5
		△	2.084	2.000	20	21	1-103336-4
		△	1.984	1.900	19	20	1-103336-3
		△	1.884	1.800	18	19	1-103336-2
		△	1.784	1.700	17	18	1-103336-1
△	OBSOLETE	△	1.684	1.600	16	17	1-103336-0
		△	1.584	1.500	15	16	103336-9
		△	1.484	1.400	14	15	103336-8
		△	1.384	1.300	13	14	103336-7
		△	1.284	1.200	12	13	103336-6
△	OBSOLETE	△	1.184	1.100	11	12	103336-5
		△	1.084	1.000	10	11	103336-4
		△	.984	.900	9	10	103336-3
		△	.884	.800	8	9	103336-2
		△	.784	.700	7	8	103336-1
		PLATING	C	B	A	NO OF POSN	ASSEMBLY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
H.MOLL
16 JULY 87
CHK
L.A.MAYER
16 JULY 87
APVD
T.C.CLARK
17 JULY 87

TE Connectivity

DIMENSIONS:
INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± .005
4 PLC ± -
ANGLES ± -

APPLICATION SPEC

RESTRICTED TO

MATERIAL
-

FINISH
SEE TABLE

WEIGHT
-

SIZE
A1

CAGE CODE
00779

DRAWING NO
103336

CUSTOMER DRAWING

SCALE
4:1

SHEET
1

OF
1

REV
H3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-103336-7](#)