

THIS DRAWING IS UNPUBLISHED.







RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC
DWDIST
—

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A2	ECR-12-012115	26OCT12	EL	WK



RECOMMENDED PCB LAYOUT (THICKNESS: 1.6mm)
DIMENSION TOLERANCE: 1 PLC: ±0.1 2PLC: ±0.05

NOTE:

- MATERIAL:
HOUSING: PA46 WITH 30% GF, UL94 V-0, BLACK COLOR.
CONTACTS: PHOSPHOR BRONZE.
SHIELD: BRASS.
- FINISH:
CONTACTS: (SEE TABLE) GOLD PLATED ON CONTACT AREA, GOLD FLASH ON SOLDER TAIL, WITH ENTIRE CONTACT UNDERPLATED 1.27μm [50μ"] MIN. NICKEL.
SHIELD: 0.51μm [20μ"] MIN. NICKEL PLATED.
- WAVE SOLDER CAPABLE TO 265°C PER 109-202, CONDITION B.

4. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

OBSOLETE	6P2C	REEL	1.27μm [50μ"]	2-1734723-8
			0.762μm [30μ"]	2-1734723-7
			0.381μm [15μ"]	2-1734723-6
			0.152μm [6μ"]	2-1734723-5
OBSOLETE	6P2C	TRAY	1.27μm [50μ"]	2-1734723-4
			0.762μm [30μ"]	2-1734723-3
			0.381μm [15μ"]	2-1734723-2
			0.152μm [6μ"]	2-1734723-1
OBSOLETE	6P6C	REEL	1.27μm [50μ"]	1734723-8
			0.762μm [30μ"]	1734723-7
			0.381μm [15μ"]	1734723-6
			0.152μm [6μ"]	1734723-5
OBSOLETE	6P6C	TRAY	1.27μm [50μ"]	1734723-4
			0.762μm [30μ"]	1734723-3
			0.381μm [15μ"]	1734723-2
			0.152μm [6μ"]	1734723-1
	RJ11	PACKAGE	MIN. GOLD THICKNESS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN A. WU 10MAR2008

CHK S. HOU 10MAR2008

APVD W. KODAMA 10MAR2008

PRODUCT SPEC

108-57527

APPLICATION SPEC

—

WEIGHT 3 GRAMS

CUSTOMER DRAWING



TE Connectivity

MODULAR JACK, RJ11,
SINGLE, DIP TYPE

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	—	©=1734723	—
SCALE —		SHEET 1 OF 5	REV A2

THIS DRAWING IS UNPUBLISHED.







RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC
DWDIST
—

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1.			





RECOMMENDED PCB LAYOUT (THICKNESS: 1.6mm)
DIMENSION TOLERANCE: 1 PLC: ±0.1 2PLC: ±0.05

NOTE:

- MATERIAL:
HOUSING: PA46 WITH 30% GF, UL94 V-0, BLACK COLOR.
CONTACTS: PHOSPHOR BRONZE.
SHIELD: BRASS.
- FINISH:
CONTACTS: (SEE TABLE) GOLD PLATED ON CONTACT AREA, GOLD FLASH ON SOLDER TAIL, WITH ENTIRE CONTACT UNDERPLATED 1.27µm [50µ"] MIN. NICKEL.
- WAVE SOLDER CAPABLE TO 265°C PER 109-202, CONDITION B.

4. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

OBSOLETE	6P6C	REEL	1.27µm [50µ"]	1-1734723-8
			0.762µm [30µ"]	1-1734723-7
			0.381µm [15µ"]	1-1734723-6
			0.152µm [6µ"]	1-1734723-5
OBSOLETE	6P6C	TRAY	1.27µm [50µ"]	1-1734723-4
			0.762µm [30µ"]	1-1734723-3
			0.381µm [15µ"]	1-1734723-2
			0.152µm [6µ"]	1-1734723-1
	RJ11	PACKAGE	MIN. GOLD THICKNESS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. WU 10MAR2008	 TE Connectivity	
DIMENSIONS: MM		CHK S. HOU 10MAR2008		
		APVD W. KODAMA 10MAR2008		
		PRODUCT SPEC 108-57527		
MATERIAL SEE NOTE		APPLICATION SPEC —	NAME MODULAR JACK, RJ11, SINGLE, DIP TYPE	
FINISH SEE NOTE		WEIGHT 2.5 GRAMS	SIZE A3	RESTRICTED TO —
		CUSTOMER DRAWING	SCALE —	SHEET 2 OF 5
			REV A2	

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION



COPYRIGHT

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

DW

—

P

LTR




DESCRIPTION

DATE




DWN

APVD

SEE SHEET 1.



LOGO

RECOMMENDED PCB LAYOUT (THICKNESS: 1.6mm)
DIMENSION TOLERANCE: 1 PLC: ±0.1 2PLC: ±0.05

NOTE:

- MATERIAL:
HOUSING: PA46 WITH 30% GF, UL94 V-0, BLACK COLOR.
CONTACTS: PHOSPHOR BRONZE.
SHIELD: BRASS.
- FINISH:
CONTACTS: (SEE TABLE) GOLD PLATED ON CONTACT AREA, GOLD FLASH ON SOLDER TAIL, WITH ENTIRE CONTACT UNDERPLATED 1.27μm [50μ"] MIN. NICKEL.
SHIELD: 0.51μm [20μ"] MIN. NICKEL PLATED.
- WAVE SOLDER CAPABLE TO 265°C PER TE TEST SPEC. 109-202, CONDITION B.

OBSOLETE	6P2C	REEL	1.27μm [50μ"]	4-1734723-8
			0.762μm [30μ"]	4-1734723-7
			0.381μm [15μ"]	4-1734723-6
			0.152μm [6μ"]	4-1734723-5
OBSOLETE		TRAY	1.27μm [50μ"]	4-1734723-4
			0.762μm [30μ"]	4-1734723-3
			0.381μm [15μ"]	4-1734723-2
			0.152μm [6μ"]	4-1734723-1
	RJ11	PACKAGE	MIN. GOLD THICKNESS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN A. WU 10MAR2008

CHK S. HOU 10MAR2008

APVD W. KODAMA 10MAR2008

PRODUCT SPEC

108-57527

APPLICATION SPEC

—

WEIGHT 3 GRAMS

CUSTOMER DRAWING



TE Connectivity

NAME

MODULAR JACK, RJ11,
SINGLE, DIP TYPE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

—

C=1734723

—

SCALE —


SHEET

3 OF 5

REV A2

DIMENSIONS:

MM



MATERIAL

SEE NOTE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± 0.50
1 PLC	± 0.30
2 PLC	± 0.20
3 PLC	± 0.10
4 PLC	± 0.10
ANGLES	± —

FINISH

SEE NOTE

4

3

2

1

D

C

B


A

D



C

B

A



13.2 Kg	3960	120	1734723-1
GROSS WEIGHT	TOTAL	PCS/TRAY	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. WU 10MAR2008	 TE Connectivity	
DIMENSIONS: MM		CHK S. HOU 10MAR2008		
		APVD W. KODAMA 10MAR2008		
		PRODUCT SPEC		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	NAME MODULAR JACK, RJ11, SINGLE, DIP TYPE	
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		—		
MATERIAL		WEIGHT	SIZE A3	CAGE CODE —
FINISH		CUSTOMER DRAWING	DRAWING NO ©=1734723	RESTRICTED TO —
		SCALE —	SHEET 4 of 5	REV A2

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


-,-

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC
DWDIST
—

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1.			



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM

MATERIAL

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC \pm -
 1 PLC \pm -
 2 PLC \pm -
 3 PLC \pm -
 4 PLC \pm -
 ANGLES \pm -

FINISH

DWN 10MAR2008

A. WU

CHK 10MAR2008

S. HOU

APVD 10MAR2008

W. KODAMA

PRODUCT SPEC

—

APPLICATION SPEC

—

WEIGHT

—

CUSTOMER DRAWING

NAME

—

SIZE

A3

CAGE CODE

—

DRAWING NO

C=1734723

RESTRICTED TO

—

TE Connectivity

MODULAR JACK, RJ11,
SINGLE, DIP TYPE

200	8	1600	7	5
PCS/ TAPE	REELS/ BOX	QUANTITY (PCS)	G/W (Kg)	N/W (Kg)

SCALE

—

SHEET

5 of 5

REV

A2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1734723-1](#)