

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


103639 , 103639

© COPYRIGHT 103639MM

ALL RIGHTS RESERVED.



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	Z	REVISED PER ECO-17-015890	31OCT2017	RS	MM
	AA	REVISED PER ECO-20-001323	17JUN2020	SM	JO




0.64 ± 0.02
[.025 \pm .001]

$0.38[.015]$ M
TYP AT POST TIPS



SECTION A-A



RECOMMENDED HOLE LAYOUT

- 1 .000100 BRIGHT TIN-LEAD OVER .000050 NICKEL.
- 2 POINT OF MEASUREMENT FOR PLATING THICKNESS.
- 3 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND THE HOUSING.
- 4 ON ASSEMBLIES WITH FOUR OR MORE POSITIONS, TWO POLARIZATION SLOTS. ON ASSEMBLIES WITH TWO OR THREE POSITIONS, ONE POLARIZATION SLOT.
- 5 .000100 BRIGHT TIN OVER .000050 NICKEL.
- 6 PRELIMINARY PART-NOT RELEASED FOR PRODUCTION.
- 7 .000100 MATTE TIN OVER .000050 NICKEL.
- 8 HIGH TEMPERATURE CONFIGURATION
- 9 STANDOFFS NOT PRESENT ON UNDERSIDE OF ASSEMBLY
- 10 SUPERSEDED BY P/N 5-103639-2.
- 11 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 12 0.25 [.010] RECESS PERMISSIBLE IN THIS AREA FOR MOLD SHUT OFF

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.SHUEY 05MAR91	TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK L.CASTAGNA 27MAR93		
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
	0 PLC \pm -		APVD L.CASTAGNA 27MAR93	
	1 PLC \pm -		PRODUCT SPEC	
	2 PLC \pm 0.13[.005]		108-25034	
	3 PLC \pm -		APPLICATION SPEC	
	4 PLC \pm -		114-25026	
MATERIAL		FINISH	WEIGHT	SCALE
HOUSING:		SEE TABLE	-	4:1
		CUSTOMER DRAWING	SIZE A2	SHEET 1 of 2
			CAGE CODE -	REV AA
			DRAWING NO C=103639	
			RESTRICTED TO -	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-103639-9](#)