


LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
AD	00		M	EC 0G3C 0759 04	28JAN05	BSV JLG
			M1	REVISED PER ECO-09-020932	25AUG09	KK AEG

D

C

B

A



- 1

CONTACTS ARE LATCHED INTO THE PRELOAD WINDOWS
- 2

USE WITH #22-#26 AWG WIRE SIZE, .054/.030 INSULATION DIAMETER, .015 MAXIMUM INSULATION THICKNESS
- 3

THE DIMENSION APPLIES WITH THE FORWARD PRELOAD STOP IN CONTACT WITH THE HOUSING SURFACE
- 4

POINT OF MEASUREMENT FOR PLATING THICKNESS
- 5

FOR STRIP ASSEMBLIES SEE PART NUMBER 103969
- 6

POINT OF MEASUREMENT FOR PLATING THICKNESS (INSIDE BEAMS)
- 7

.000015 GOLD IN THE CONTACT AREA, .000050-.000100 BRIGHT TIN-LEAD ON THE TERMINATION AREA, ALL OVER .000050 NICKEL
- 8

.000015 GOLD IN THE CONTACT AREA, .000050-.000100 MATTE TIN ON THE TERMINATION AREA, ALL OVER .000050 NICKEL
- 9

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

OBSOLETE	8	2-103648-4	25	7-103651-4
	8	2-103648-3	24	7-103651-3
	8	2-103648-2	23	7-103651-2
	8	2-103648-1	22	7-103651-1
	8	2-103648-0	21	7-103651-0
	8	1-103648-9	20	6-103651-9
	8	1-103648-8	19	6-103651-8
	8	1-103648-7	18	6-103651-7
	8	1-103648-6	17	6-103651-6
	8	1-103648-5	16	6-103651-5
	8	1-103648-4	15	6-103651-4
	8	1-103648-3	14	6-103651-3
OBSOLETE	7	2-103648-4	25	2-103651-4
	7	2-103648-3	24	2-103651-3
	7	2-103648-2	23	2-103651-2
	7	2-103648-1	22	2-103651-1
	7	2-103648-0	21	2-103651-0
	7	1-103648-9	20	1-103651-9
	7	1-103648-8	19	1-103651-8
	7	1-103648-7	18	1-103651-7
	7	1-103648-6	17	1-103651-6
	7	1-103648-5	16	1-103651-5
	7	1-103648-4	15	1-103651-4
	7	1-103648-3	14	1-103651-3
SUPERSEDED BY 1-103969-1		1-103648-1	12	1-103651-1
		1-103648-0	11	1-103651-0
SUPERSEDED BY 103969-9		103648-9	10	103651-9
		103648-8	9	103651-8
SUPERSEDED BY 103969-8		103648-7	8	103651-7
		103648-6	7	103651-6
SUPERSEDED BY 103969-6		103648-5	6	103651-5
		103648-4	5	103651-4
SUPERSEDED BY 103969-5		103648-3	4	103651-3
		103648-2	3	103651-2
SUPERSEDED BY 103969-4		103648-1	2	103651-1
SUPERSEDED BY 103969-3				
SUPERSEDED BY 103969-2				
SUPERSEDED BY 103969-1				
	PLATING	HOUSING PART NUMBER	NO OF POSN	ASSEMBLY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. MAYER 05 NOV 1986	Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: INCHES		CHK P.DEJONG 12-11-86		
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD 12-11-86	NAME	
	0 PLC ± - 1 PLC ± - 2 PLC ± .02 3 PLC ± .005 4 PLC ± - ANGLES ± - FINISH	PRODUCT SPEC 108-25034 APPLICATION SPEC 114-25026 WEIGHT -	RCPT ASSY, AMPMODU MTE, SINGLE ROW, .100 CL WITH GUIDE RIBS, FOR #22-#26 AWG WIRE SIZE	
MATERIALS: HOUSING- FLAME RETARDANT, THERMOPLASTIC, COLOR-BLACK CONTACTS- PHOS BRONZE		CUSTOMER DRAWING	SIZE A2 CAGE CODE 00779 DRAWING NO C-103651	RESTRICTED TO -
		SCALE 4:1	SHEET 1 OF 1	REV M1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-103651-4](#)