

D

8.7	GEN II & GEN III	 PA9T	2.30	71.35	70	73.15	89	71.65	164	BLACK	30u"	4-1734774-8
5.45				38.35	37	40.15	56	38.65	98	WHITE		4-1734774-7
3.85										BLACK		4-1734774-6
										WHITE		4-1734774-5
2.55										BLACK		4-1734774-4
										WHITE		4-1734774-3
8.7										71.35	70	73.15
				WHITE	G/F	4-1734774-1						
					15u"	3-1734774-0						
						G/F	3-1734774-9					
5.45				38.35	37	40.15	56	38.65	98	BLACK	15u"	3-1734774-8
										WHITE	G/F	3-1734774-7
											15u"	3-1734774-6
												G/F
3.85				21.35	20	23.15	39	21.65	64	BLACK	15u"	3-1734774-4
										WHITE	G/F	3-1734774-3
											15u"	3-1734774-2
												G/F
2.55				7.35	6	9.15	25	7.65	36	BLACK	15u"	3-1734774-0
										WHITE	G/F	2-1734774-9
											15u"	2-1734774-8
												G/F
8.7				71.35	70	73.15	89	71.65	164	BLACK	15u"	2-1734774-6
										WHITE	G/F	2-1734774-5
	15u"	2-1734774-4										
		G/F	2-1734774-3									
5.45	38.35	37	40.15	56	38.65	98	BLACK	15u"	2-1734774-2			
							WHITE	G/F	2-1734774-1			
								15u"	2-1734774-0			
									G/F	2-1734774-9		
3.85	21.35	20	23.15	39	21.65	64	BLACK	15u"	1-1734774-8			
							WHITE	G/F	1-1734774-7			
								15u"	1-1734774-6			
									G/F	1-1734774-5		
2.55	7.35	6	9.15	25	7.65	36	BLACK	15u"	1-1734774-4			
							WHITE	G/F	1-1734774-3			
								15u"	1-1734774-2			
									G/F	1-1734774-1		
WEIGHT(g)	PCI-E COMPLIANCE	HOUSING MATERIAL	DIM. L	DIM. E	DIM. D	DIM. C	DIM. B	DIM. A	POS.	HOUSING COLOR	MIN. GOLD THICKNESS	PART NUMBER

D

C

C

B

B

A

A

8.8	GEN II	PA46	2.30	71.35	70	73.15	89	71.65	164	BLACK	30u"	9-1734774-7
5.5				38.35	37	40.15	56	38.65	98	WHITE		9-1734774-6
3.9										BLACK		9-1734774-5
2.55				21.35	20	23.15	39	21.65	64	WHITE		9-1734774-4
										BLACK		9-1734774-3
8.8				7.35	6	9.15	25	7.65	36	WHITE		9-1734774-2
										BLACK	9-1734774-1	
5.5				71.35	70	73.15	89	71.65	164	BLACK	15u"	8-1734774-9
										G/F	8-1734774-8	
3.9				38.35	37	40.15	56	38.65	98	WHITE	15u"	8-1734774-7
										G/F	8-1734774-6	
2.55				21.35	20	23.15	39	21.65	64	BLACK	15u"	8-1734774-5
			G/F							8-1734774-4		
8.8			7.35	6	9.15	25	7.65	36	WHITE	15u"	8-1734774-3	
									G/F	8-1734774-2		
5.5			38.35	37	40.15	56	38.65	98	BLACK	15u"	8-1734774-1	
									G/F	8-1734774-0		
3.9			21.35	20	23.15	39	21.65	64	WHITE	15u"	8-1734774-9	
									G/F	8-1734774-8		
2.55	7.35	6	9.15	25	7.65	36	BLACK	15u"	7-1734774-7			
							G/F	7-1734774-6				
8.8	71.35	70	73.15	89	71.65	164	WHITE	15u"	7-1734774-5			
							G/F	7-1734774-4				
5.5	38.35	37	40.15	56	38.65	98	BLACK	15u"	7-1734774-3			
							G/F	7-1734774-2				
3.9	21.35	20	23.15	39	21.65	64	WHITE	15u"	7-1734774-1			
							G/F	7-1734774-0				
2.55	7.35	6	9.15	25	7.65	36	BLACK	15u"	7-1734774-9			
							G/F	7-1734774-8				
3.10	71.35	70	73.15	89	71.65	164	BLACK	15u"	7-1734774-7			
							G/F	7-1734774-6				
							WHITE	15u"	6-1734774-5			
							G/F	6-1734774-4				
							BLACK	15u"	6-1734774-3			
							G/F	6-1734774-2				
	38.35	37	40.15	56	38.65	98	BLACK	15u"	6-1734774-1			
							G/F	6-1734774-0				
							WHITE	15u"	6-1734774-9			
							G/F	6-1734774-8				
							BLACK	15u"	6-1734774-7			
							G/F	6-1734774-6				
21.35	20	23.15	39	21.65	64	BLACK	15u"	6-1734774-5				
						G/F	6-1734774-4					
						WHITE	15u"	6-1734774-3				
						G/F	6-1734774-2					
						BLACK	15u"	6-1734774-1				
						G/F	6-1734774-0					
7.35	6	9.15	25	7.65	36	BLACK	15u"	5-1734774-9				
						G/F	5-1734774-8					
						WHITE	15u"	5-1734774-7				
						G/F	5-1734774-6					
						BLACK	15u"	5-1734774-5				
						G/F	5-1734774-4					
5.5	38.35	37	40.15	56	38.65	98	BLACK	15u"	5-1734774-3			
							G/F	5-1734774-2				
							WHITE	15u"	5-1734774-1			
							G/F	5-1734774-0				
							BLACK	15u"	5-1734774-9			
							G/F	5-1734774-8				
3.9	21.35	20	23.15	39	21.65	64	BLACK	15u"	5-1734774-7			
							G/F	5-1734774-6				
							WHITE	15u"	5-1734774-5			
							G/F	5-1734774-4				
							BLACK	15u"	5-1734774-3			
							G/F	5-1734774-2				
2.55	7.35	6	9.15	25	7.65	36	BLACK	15u"	5-1734774-1			
							G/F	5-1734774-0				
							WHITE	15u"	5-1734774-9			
							G/F	5-1734774-8				
							BLACK	15u"	5-1734774-7			
							G/F	5-1734774-6				

WEIGHT(g)	PCI-E COMPLIANCE	HOUSING MATERIAL	DIM. L	DIM. E	DIM. D	DIM. C	DIM. B	DIM. A	POS.	HOUSING COLOR	MIN. GOLD THICKNESS	PART NUMBER
-----------	------------------	------------------	--------	--------	--------	--------	--------	--------	------	---------------	---------------------	-------------

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

AUG ,2006.



COPYRIGHT

-

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

DW

P

LTR

DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1

NOTES:

1. MATERIAL:

1.1 HOUSING: 1.PA46 WITH 40% G.F, UL94 V-0, COLOR: SEE TABLE.

2.PA9T WITH 30% GF, UL94 V-0, COLOR: SEE TABLE.

1.2 CONTACT: PHOSPHOR BRONZE

2. FINISH:

CONTACT: (SEE TABLE) GOLD PLATING ON CONTACT AREA.

2.54um [100u"] MIN. MATTE-TIN PALTING ON SOLDER TAIL AREA.

1.27um [50u"] MIN. NICKEL UNDERPLATING OVERALL.

3. CONNECTOR HAS MET THE REQUIREMENTS

PER PCI EXPRESS GEN 2 TECHNICAL DOCUMENT.

4. WEIGHT:






36 POS.: 2.55 GRAMS; 64 POS.: 3.90 GRAMS

98 POS.: 5.50 GRAMS; 164 POS.: 8.80 GRAMS


5. WAVE SOLDER CAPABLE TO 265°C PER TEST SPEC. 109-202 CONDITION B.

6. REFLOW SOLDER CAPABLE TO 260°C PER TEST SPEC. 109-201 CONDITION B.

(REFLOW SOLDERING PLEASE USE PN : 1734774-1 TO 4-1734774-8)



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM

MATERIAL

SEE NOTE

TOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ± -
1 PLC ± 0.3
2 PLC ± 0.2
3 PLC ± 0.15
4 PLC ± -
ANGLES ± 3°

FINISH

SEE NOTE

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

SEE NOTE 4

CUSTOMER DRAWING



TE Connectivity

NAME

PCI EXPRESS CARD EDGE CONNECTOR
VERTICAL, DIP TYPE, 3GIO

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779C-1734774

SCALE

SHEET

2 OF 5

REV

G

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

AUG ,2006.


© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
DW		P	LTR	DESCRIPTION	DATE	DWN
				SEE SHEET 1.		


D

D



PN X-1 TO 4-X-8
(PA9T TYPE)


36 POS.




PN 5-X-0 TO 9-X-7
(PA46 TYPE)

C

C




64 POS.




B

B




98 POS.




A

A



164 POS.



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± 0.25
2 PLC ± 0.25
3 PLC ± 0.25
4 PLC ± -
ANGLES ± -
FINISH

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE Connectivity

NAME

PCI EXPRESS CARD EDGE CONNECTOR
VERTICAL, DIP TYPE, 3GIO

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=1734774

SCALE

SHEET 3 OF 5

REV G

AMP 1470-19 REV 31MAR2000

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

AUG ,2006.

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

DW

P

LTR

DESCRIPTION

DATE


DWN

APVD

SEE SHEET 1.


ADD-IN CARD EDGE-FINGER DIMENSIONS

NOTES:
CHAMFER EDGE MUST BE FREE OF CUTTING BURRS



RECOMMENDED PCB LAYOUT

TOLERANCE: ±0.05
FOR DIM.L=3.1mm PCB THICKNESS: 2.4mm
FOR DIM.L=2.3mm PCB THICKNESS: 1.6mm



164	70.0	73.15	72.15	A1, B17, B31, B48, B81
98	37.0	40.15	39.15	A1, B17, B31, B48
64	20.0	23.15	22.15	A1, B17, B31
36	6.0	9.15	8.15	A1, B17
POS.	DIM. F	DIM. G	DIM. H	"K"


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		TE TE Connectivity	
DIMENSIONS: MM		CHK			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD			
0 PLC ± -		PRODUCT SPEC			
1 PLC ± -		APPLICATION SPEC		NAME	
2 PLC ± -		WEIGHT		SIZE	
3 PLC ± -		CUSTOMER DRAWING		CAGE CODE	
4 PLC ± -		SCALE		DRAWING NO	
ANGLES ± -		SHEET		RESTRICTED TO	
FINISH		4 OF 5		REV G	

4

3

2

1



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[7-1734774-5](#)