

4

3



2

1

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
DW	/		C	REVISED (ECR-14-014356), ADD STD OFF	24NOV14	SC	HL

NOTES:

1. MATERIAL:
HOUSING: PBT WITH 30% GF, UL 94V-0, BLACK COLOR.
CONTACTS: PHOSPHOR BRONZE.
SHIELD: PHOSPHOR BRONZE.
2. FINISH:
CONTACTS: GOLD FLASH OVER
0.762µm [30µ"] MIN. PALLADIUM-NICKEL PLATED ON CONTACT AREA,
2.54µm [100µ"] MIN. MATTE-TIN ON SOLDER TAIL, WITH
ENTIRE CONTACT UNDERPLATED 1.27µm [50µ"] MIN. NICKEL.
SHIELD: 0.762µm [30µ"] MIN. NICKEL PLATED, WITH
2.54µm [100µ"] MIN. Cu UNDERPLATED OVERALL.
3. WAVE SOLDER CAPABLE TO 265°C PER TE TEST SPEC.
109-202, CONDITION B.



RECOMMENDED PCB LAYOUT (THICKNESS: 1.6MM)

(DIMENSION TOLERANCE: 1 PLC: ±0.10 2PLC: ±0.05)

3.30	1-1734775-1
2.45	1734775-1
DIM A	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN O. HU 22MAY2007	TE Connectivity			
DIMENSIONS: mm		CHK S. HOU 22MAY2007				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD W.J. KE 22MAY2007	NAME			
0 PLC ± 0.38		PRODUCT SPEC	108-57322			
1 PLC ± 0.25		APPLICATION SPEC				
2 PLC ± 0.20		WEIGHT	2.4 GRAMS			
3 PLC ± -		CUSTOMER DRAWING				
4 PLC ± -		SCALE	-			
ANGLES ± 3°		SHEET	1 OF 2			
FINISH		REV	C			
SEE NOTE						
SEE NOTE						






TE Connectivity

USB CONNECTOR, RECEPTACLE,
FLAG, R/A, DIP, A TYPE

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C=1734775	-

LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN	APVD	
		SEE SHEET 1.				



11.1 Kg	10.1 Kg	100	21	2	4200 PCS
GROSS WEIGHT	NET WEIGHT	PCS/TRAY	TRAYS /INNER BOX	INNER BOX /CARTON	QUANTITY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	TE Connectivity			
DIMENSIONS: mm		CHK				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD				
MATERIAL		PRODUCT SPEC	NAME			
FINISH		APPLICATION SPEC	USB CONNECTOR, RECEPTACLE, FLAG, R/A, DIP, A TYPE			
		WEIGHT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		CUSTOMER DRAWING	A3	00779	C=1734775	—
		SCALE	SHEET		REV	
		—	2 OF 2		C	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1734775-1](#)