





- ① .000100 BRIGHT TIN—LEAD OVER .000050 NICKEL.
- ② POINT OF MEASUREMENT FOR PLATING THICKNESS.
- ③ THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND THE HOUSING.
- ④ ON ASSEMBLIES WITH FOUR OR MORE POSITIONS, TWO POLARIZATION SLOTS.
ON ASSEMBLIES WITH TWO OR THREE POSITIONS, ONE POLARIZATION SLOT.
- ⑤ SELECT POST TAILS FORMED TO PROVIDE CONNECTOR HOLD DOWN UNTIL SOLDERED. CONFIGURATION ACCEPTS 0.69[.027]—2.03[.080] THICK PRINTED CIRCUIT BOARD. (SEE DETAIL Z).
- ⑥ .000100 BRIGHT TIN OVER .000050 NICKEL.
- ⑦ PRELIMINARY PART — NOT RELEASED FOR PRODUCTION.
- ⑧ .000100 MATTE TIN OVER .000050 NICKEL.
- ⑨ HIGH TEMPERATURE CONFIGURATION.
- ⑩ STANDOFFS NOT PRESENT ON UNDERSIDE OF ASSEMBLY
- ⑪ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINIS
- ⑫ 0.25 [.010] RECESS PERMISSIBLE IN THIS AREA FOR MOLD SHUT OFF

				23.37 [.920]	25.27 [.995]	8	9	3-103669-0	
				8.13 [.320]	10.03 [.395]	2	3	2-103669-9	
				15.75 [.620]	17.65 [.695]	5	6	2-103669-8	
				13.21 [.520]	15.11 [.595]	4	5	2-103669-7	
				10.67 [.420]	12.57 [.495]	3	4	2-103669-6	
				5.59 [.220]	7.49 [.295]	1	2	2-103669-5	
	OBSOLETE			64.01 [2.520]	65.91 [2.595]	24	25	2-103669-4	
	OBSOLETE			61.47 [2.420]	63.37 [2.495]	23	24	2-103669-3	
	OBSOLETE			58.93 [2.320]	60.83 [2.395]	22	23	2-103669-2	
	OBSOLETE			56.39 [2.220]	58.29 [2.295]	21	22	2-103669-1	
	OBSOLETE			53.85 [2.120]	55.75 [2.195]	20	21	2-103669-0	
				51.31 [2.020]	53.21 [2.095]	19	20	1-103669-9	
	OBSOLETE			48.77 [1.920]	50.67 [1.995]	18	19	1-103669-8	
	OBSOLETE			46.23 [1.820]	48.13 [1.895]	17	18	1-103669-7	
				43.69 [1.720]	45.59 [1.795]	16	17	1-103669-6	
				41.15 [1.620]	43.05 [1.695]	15	16	1-103669-5	
	OBSOLETE			38.61 [1.520]	40.51 [1.595]	14	15	1-103669-4	
				36.07 [1.420]	37.97 [1.495]	13	14	1-103669-3	
				33.53 [1.320]	35.43 [1.395]	12	13	1-103669-2	
				30.99 [1.220]	32.89 [1.295]	11	12	1-103669-1	
				28.45 [1.120]	30.35 [1.195]	10	11	1-103669-0	
				25.91 [1.020]	27.81 [1.095]	9	10	103669-9	
				23.37 [.920]	25.27 [.995]	8	9	103669-8	
				20.83 [.820]	22.73 [.895]	7	8	103669-7	
				18.29 [.720]	20.19 [.795]	6	7	103669-6	
				15.75 [.620]	17.65 [.695]	5	6	103669-5	
				13.21 [.520]	15.11 [.595]	4	5	103669-4	
				10.67 [.420]	12.57 [.495]	3	4	103669-3	
				8.13 [.320]	10.03 [.395]	2	3	103669-2	
				5.59 [.220]	7.49 [.295]	1	2	103669-1	
			REMARKS	PLATING	C	B	A	NO. OF POSN	PART NO.

[illegible]

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

By

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

OBSOLETE

11

9 10	8	64.01 [2.520]	65.91 [2.595]	24	25	7-103669-4
9 10	8	61.47 [2.420]	63.37 [2.495]	23	24	7-103669-3
9 10	8	58.93 [2.320]	60.83 [2.395]	22	23	7-103669-2
9 10	8	56.39 [2.220]	58.29 [2.295]	21	22	7-103669-1
9 10	8	53.85 [2.120]	55.75 [2.195]	20	21	7-103669-0
9 10	8	51.31 [2.020]	53.21 [2.095]	19	20	6-103669-9
9 10	8	48.77 [1.920]	50.67 [1.995]	18	19	6-103669-8
9 10	8	46.23 [1.820]	48.13 [1.895]	17	18	6-103669-7
9 10	8	43.69 [1.720]	45.59 [1.795]	16	17	6-103669-6
9 10	8	41.15 [1.620]	43.05 [1.695]	15	16	6-103669-5
9 10	8	38.61 [1.520]	40.51 [1.595]	14	15	6-103669-4
9 10	8	36.07 [1.420]	37.97 [1.495]	13	14	6-103669-3
9 10	8	33.53 [1.320]	35.43 [1.395]	12	13	6-103669-2
9 10	8	30.99 [1.220]	32.89 [1.295]	11	12	6-103669-1
9 10	8	28.45 [1.120]	30.35 [1.195]	10	11	6-103669-0
9 10	8	25.91 [1.020]	27.81 [1.095]	9	10	5-103669-9
9 10	8	23.37 [.920]	25.27 [.995]	8	9	5-103669-8
9 10	8	20.83 [.820]	22.73 [.895]	7	8	5-103669-7
9 10	8	18.29 [.720]	20.19 [.795]	6	7	5-103669-6
9 10	8	15.75 [.620]	17.65 [.695]	5	6	5-103669-5
9 10	8	13.21 [.520]	15.11 [.595]	4	5	5-103669-4
9 10	8	10.67 [.420]	12.57 [.495]	3	4	5-103669-3
9 10	8	8.13 [.320]	10.03 [.395]	2	3	5-103669-2
9 10	8	5.59 [.220]	7.49 [.295]	1	2	5-103669-1
REMARKS	PLATING	C	B	A	NO. OF POSN	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
S. SHUEY

3-5-91

CHK
M. RIDER

2-14-92

APVD
M. RIDER

2-14-92

NAME

DIMENSIONS:
INCHES

0 PLC ± —

1 PLC ± —

2 PLC ± 0.13[.005]

3 PLC ± —

4 PLC ± —

ANGLES ± —

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

FINISH

MATERIAL
HOUSING: LCP,
CONTACTS: BRASS

SEE TABLE

PRODUCT SPEC
108-25034

APPLICATION SPEC
114-25026

WEIGHT
—

SIZE
A1

CAGE CODE
00779

DRAWING NO
C=103669

RESTRICTED TO
—

CUSTOMER DRAWING

SCALE
4:1

SHEET
2

OF
2

REV
AC

STE

TE Connectivity

HDR ASSY, VERT, SINGLE ROW
2.54 [.100] C/L 0.64 [.025] SQ POST
WITH PLZN, AMPMODU MTE

4805 (1/15)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-103669-9](#)