





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		A1	REL PER ECR 08-010125	21APR08	JR	RL



SUGGESTED MATING TAB




- 1 - MATL: 1/2H BRASS OR NICKEL PL STEEL.
 - 2 - NO BURRS PERMISSIBLE AT HOLE.
 - 3 - MUST BE FLAT WITHIN 0.076 [.003] OVER THIS LENGTH.
 - 4 - TIN PLATING IS REQUIRED ON BRASS WHEN TERMAL TEMP. IS OVER 225°F.
 - 5 - HOLE MUST BE SYMMETRICAL ABOUT TAB Q WITHIN 0.076 [.003]
- * TO BE USED ONLY WHEN SHOULDER IS ELIMINATED.



- 1 CONTINUOUS STRIP ON REELS.
- 2 ACCEPTS #22-#18 AWG WIRE SIZES. WIRE CRIMP: .080 F TYPE
- 3 INSULATION RANGE IS 2.29-3.94 [.090-.155] DIA. INSULATION CRIMP: .180 F TYPE



0.002032[.000080] MIN TIN PLATE	1742630-2
-	1742630-1
FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 14AUG07		 Tyco Electronics Corporation Harrisburg, PA 17105-3608							
DIMENSIONS: MM [INCHES]		CHK MS FEHER 14AUG07									
		APVD R LONDON 14AUG07		NAME RECEPTACLE, POSITIVE LOCK, 6.35 [.250] SERIES —							
		PRODUCT SPEC —									
		APPLICATION SPEC 114-2074						SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		MATERIAL H06 BRASS						FINISH SEE TABLE		WEIGHT —	
		CUSTOMER DRAWING		SCALE 5:1		SHEET 1 of 1		REV A1			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1742630-1](#)