


LOC		DIST		REVISIONS					
AD		00		P	LTR	DESCRIPTION	DATE	DWN	APVD
					H	REVISED PER ECO-14-000068	28APR2014	NK	MM

D



RECOMMENDED HOLE LAYOUT

1 ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS.

2 TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADERS ARE HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD

3 .000100-.000200 MATTE TIN-LEAD OVER .000050 NICKEL ENTIRE POST

4 BREAKAWAY NOTCH ANGLE CAN BE ORIENTED TO THE RIGHT (AS SHOWN) OR TO THE LEFT

5 .000100-.000200 MATTE TIN OVER .000050 NICKEL ENTIRE POST

6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

OBSOLETE	5	3.984	3.900	39	40	9-103759-0
	5	3.484	3.400	34	35	-8-
	5	2.984	2.900	29	30	-8-
	5	2.484	2.400	24	25	-7-
	5	1.984	1.900	19	20	-7-
	5	1.484	1.400	14	15	-6-
	5	1.384	1.300	13	14	-6-
OBSOLETE	5	1.284	1.200	12	13	-6-
	5	1.184	1.100	11	12	-6-
	5	1.084	1.000	10	11	6-
	5	.984	.900	9	10	-6-
OBSOLETE	5	.884	.800	8	9	-5-
	5	.784	.700	7	8	-5-
	5	.684	.600	6	7	5-
OBSOLETE	5	.584	.500	5	6	-5-
	5	.484	.400	4	5	-5-
	5	.384	.300	3	4	-5-
	5	.284	.200	2	3	-5-
OBSOLETE	5	.184	.100	1	2	5-
OBSOLETE	5	.084			1	-5-103759-1
OBSOLETE	3	3.984	3.900	39	40	4-103759-0
OBSOLETE	3	3.884	3.800	38	39	3-
OBSOLETE	3	3.784	3.700	37	38	3-
OBSOLETE	3	3.684	3.600	36	37	3-
OBSOLETE	3	3.584	3.500	35	36	3-
OBSOLETE	3	3.484	3.400	34	35	3-
OBSOLETE	3	3.284	3.300	33	34	3-
OBSOLETE	3	3.284	3.200	32	33	3-
OBSOLETE	3	3.184	3.100	31	32	3-
OBSOLETE	3	3.084	3.000	30	31	3-
OBSOLETE	3	2.984	2.900	29	30	3-
OBSOLETE	3	2.884	2.800	28	29	2-
OBSOLETE	3	2.784	2.700	27	28	2-
OBSOLETE	3	2.684	2.600	26	27	2-
OBSOLETE	3	2.584	2.500	25	26	2-
OBSOLETE	3	2.484	2.400	24	25	2-
OBSOLETE	3	2.384	2.300	23	24	2-
OBSOLETE	3	2.284	2.200	22	23	2-
OBSOLETE	3	2.184	2.100	21	22	2-
OBSOLETE	3	2.084	2.000	20	21	2-
OBSOLETE	3	1.984	1.900	19	20	2-
OBSOLETE	3	1.884	1.800	18	19	1-
OBSOLETE	3	1.784	1.700	17	18	1-
OBSOLETE	3	1.684	1.600	16	17	1-
OBSOLETE	3	1.584	1.500	15	16	1-
OBSOLETE	3	1.484	1.400	14	15	-4-
	3	1.384	1.300	13	14	-4-
	3	1.284	1.200	12	13	-4-
	3	1.184	1.100	11	12	-4-
OBSOLETE	3	1.084	1.000	10	11	1-
	3	.984	.900	9	10	-4-
	3	.884	.800	8	9	-9-
	3	.784	.700	7	8	-8-
	3	.684	.600	6	7	-7-
	3	.584	.500	5	6	-6-
	3	.484	.400	4	5	-5-
OBSOLETE	3	.384	.300	3	4	-4-
	3	.284	.200	2	3	-3-
	3	.184	.100	1	2	-2-
	3	.084			1	-103759-1

PLATING	C	B	A	NO OF POS	ASSEMBLY PART NUMBER
---------	---	---	---	-----------	----------------------

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. D. RINGLEY 23JUL85	TE Connectivity	
DIMENSIONS: INCHES		CHK R. FLICKER 12NOV87	NAME	
		APVD R. FLICKER 12NOV87	PRODUCT SPEC	
		APPLICATION SPEC		
		SIZE CAGE CODE DRAWING NO		
MATERIAL: HOUSING: FLAME RETARDANT THERMOPLASTIC; COLOR: BLACK; POSTS: COPPER ALLOY	FINISH: SEE TABLE	WEIGHT: --	A1 00779 103759	
CUSTOMER DRAWING		SCALE: 4:1	SHEET 1 OF 1	REV

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[103759-6](#)