






- 1 POINT OF MEASUREMENT FOR PLATING THICKNESS
- 2 ASSEMBLIES MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS
- 3 TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADERS ARE HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD
- 4 .000030 GOLD ON THE CONTACT AREA, .000100-.000200 MATTE TIN-LEAD ON THE SOLDER TAIL, ALL OVER .000050 NICKEL
- 5 BREAKAWAY NOTCH ANGLE CAN BE ORIENTED TO THE RIGHT (AS SHOWN) OR TO THE LEFT
- 6 .000030 GOLD ON THE CONTACT AREA, .000100-.000200 MATTE TIN ON THE SOLDER TAIL, ALL OVER .000050 NICKEL
- 7 HIGH TEMPERATURE CONFIGURATION
- 8 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

[illegible]

REMARKS	PLATING	C	B	A	NO OF POS	ASSEMBLY PART NUMBER	REMARKS	PLATING	C	B	A	NO OF POS	ASSEMBLY PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.							OWN L. D. RINGLEY 31-7-85		 TE Connectivity				
							CHK: R. FLICKER 31-7-85						
DIMENSIONS:							APVD R. FLICKER 31-7-85		NAME				
INCHES							TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC				
							0 PLC ± .—		ASSEMBLY, MOD II, HEADER, BREAKAWAY, DOUBLE ROW, RIGHT ANGLE, .100X.100 C/L, WITH .025 SQUARE POSTS				
							1 PLC ± .—						
							2 PLC ± .—						
							3 PLC ± .005						
							4 PLC ± .—						
MATERIAL HOUSING : FLAME RETARDANT THERMOPLASTIC							APPLICATION SPEC		SIZE				
COLOR - BLACK							—		CAGE CODE				
POSTS : COPPER ALLOY							FINISH		DRAWING NO				
SEE TABLE							WEIGHT		RESTRICTED TO				
							—		A1 00779 © 103801				
							CUSTOMER DRAWING					SCALE 4:1 SHEET 1 OF 1 REV J	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[103801-3](#)