






REVISIONS					
P	LTR	DESCRIPTION	ECN	DATE	DWN APVD
	O	RELEASED	FJD0-0414-04	11NOV 2004	T.S D.M
	O1	ADDITION PART NO	ECR-07-007149	28MAR 2007	M.M D.M
	A	REVISED(ADD NATURAL COLOR)	ECR-14-009682	27JUN 2014	Z.S N.Y



- NOTES
- MATERIAL: HOUSING: GLASS FILLED THERMO PLASTIC, POLYESTER(94V-0)
COLOR: -1/-2 BLACK
-3 NATURAL
TAB CONTACT: COPPER ALLOY
RETENTION LEG: BRASS
 - FINISH (CONTACT AREA): 0.38μm MIN GOLD PLATING OVER Ni PLATING
 - FINISH (RETENTION LEG): TIN PLATED (CONTACT TAIL) OVER NICKEL
 - APPEARANCE CRITERIA IS BASED ON TE CRITERIA.


RECOMENDED PC BOARD HOLE PATTERN(TOL:±0.05)
PC BOARD THICKNESS:1.6±0.3
(CONNECTOR MOUNT SIDE)

- 注記
- 材料: ハウジング: ガラス入り熱可塑性
ポリエスチル樹脂 (94V-0)
色: -1/-2 黒
-3 ナチュラル
タブ コンタクト: 銅合金
リテンション レグ: 黄銅
 - めっき: コンタクト: 全面Ni下地
接触部: 0.38μm MIN金めっき
 - めっき: リテンションレグとコンタクト半田付部
: ニッケル下地の上にスズめっき
 - 外觀基準はTE基準に基づく



1747994-1
(KEYING X)
SCALE: 2-1

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN 11/NOV/'04 CHK T.Sakamoto 11/NOV/'04 APVD D.Mitsugi 11/NOV/'04		TE Connectivity	
DIMENSIONS: 単位 長 mm		TOLERANCES UNLESS OTHERWISE SPECIFIED 一般公差 10 ±0.3 30 ±0.35 100 ±0.4 ANGLE: ±3°		NAME 2列 ヘッダーアセンブリ 16P (垂直タイプ) DOUBLE ROW HEADER ASS'Y 16P ("V" TYPE) "DYNAMIC D-2100D"	
MATERIAL 材料 注記参照 SEE NOTES		FINISH 仕上 注記参照 SEE NOTES		SIZE A3 CAGE CODE 00779 DRAWING NO C=1747994 RESTRICTED TO	
CUSTOMER DRAWING				SCALE 4-1 SHEET 1 OF 2 REV A	



TE TE Connectivity

NAME 2列 ヘッダーアセンブリー 16P
<垂直タイプ>
DOUBLE ROW HEADER ASS'Y 16P ("V" TYPE)
<DYNAMIC D-2100D>

SIZE A3 CAGE CODE 00779 DRAWING NO C-1747994 RESTRICTED TO -

SCALE 4-1 SHEET 2 OF 2 REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1747994-1](#)