

D

C

B

A



D

C

B

A

- 1 TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADER IS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD.
- 2 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING.
- 3 POINT OF MEASUREMENT FOR PLATING THICKNESS.
- 4 RETENTION FEATURES ON SOLDER TAILS, LOCATED AT MANUFACTURERS OPTION.
- 5 FOR 2 POSITION PART ONLY, THE NOTED DIM. IS .184.
- 6 $\varnothing .020 \text{ (M)}$ FOR KINKED TAILS.
- 7 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI.



7	OBSOLETE	3.084	3.000	30	62	2-104350-1	
		3.984	3.900	39	80	2-104350-0	
	OBSOLETE	2.984	2.900	29	60	1-104350-9	
	7	2.484	2.400	24	50	1-104350-8	
		1.984	1.900	19	40	1-104350-7	
		1.684	1.600	16	34	1-104350-6	
	SUPERSEDED BY 6-146269-5		1.484	1.400	14	30	1-104350-5
		1.384	1.300	13	28	1-104350-4	
	OBSOLETE	1.284	1.200	12	26	1-104350-3	
	7	1.184	1.100	11	24	1-104350-2	
		1.084	1.000	10	22	1-104350-1	
		.984	.900	9	20	1-104350-0	
	7	.884	.800	8	18	104350-9	
		.784	.700	7	16	104350-8	
		.684	.600	6	14	104350-7	
		.584	.500	5	12	104350-6	
		.484	.400	4	10	104350-5	
		.384	.300	3	8	104350-4	
		.284	.200	2	6	104350-3	
		.184	.100	1	4	104350-2	
		.084	—	—	2	104350-1	
		C	B	A	NO OF POSN	ASSEMBLY PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H MOLL 08FEB88	TE Connectivity			
		CHK R FEIDT 08FEB88				
DIMENSIONS: INCHES		APVD R FEIDT 08FEB88	NAME			
		PRODUCT SPEC				
		APPLICATION SPEC				
MATERIAL HOUSING FLAME RETARDANT THERMOPLASTIC COLOR-BLACK POST: COPPER ALLOY		WEIGHT —	SIZE A1	CAGE CODE —	DRAWING NO. 104350	RESTRICTED TO —
CUSTOMER DRAWING			SCALE 4:1	SHEET 1 of 1	REV N	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[104350-3](#)