


NUMBER C-175124





METRIC


単位: 全尺寸 IN MM. DO NOT SCALE PRINT

PRINT DIST


REV. 10/89






断面 B-B
SECT. B-B



断面 C-C
SECT. C-C



断面 D-D
SECT. D-D



断面 A-A
SECT. A-A

注:
△ 部分金めつき
2. 圧着規格 114-5134

NOTES;
△ SELECTIVE GOLD
2. CRIMP SPEC. 114-5134

Copyright ©1992 AMP (Japan), LTD. ALL RIGHTS RESERVED.				Copyright ©1992 AMP (Japan), LTD. ALL RIGHTS RESERVED.				AMP 東京エー・エム・ピー株式会社 Tokyo, Japan			
電線断面 (WIRE RANGED)				絶縁外径 (INSULATION DIA.)				名称 (NAME)			
0.3-0.56 mm ² (AWG#22-#20)				1.0-1.4 mmφ				.070 SERIES RECEPTACLE			
材料 (MATERIAL)				仕上 (FINISH)				.070 シリーズ リセプタクルコンタクト			
BRASS, 板厚: 0.25				SEE TABLE 表参照				一般公差 (GENERAL TOLERANCE)			
0 作成 (J-1380) 9/22/92				DR. Y. Kishida				10mm: ±0.2			
LTR 変更 (REVISION RECORD)				CHK. J. Asakura 5/9/92				10mm以上 30mm以下: ±0.25			
DR				APP. J. Asakura 5/9/92				30mm以上 100mm以下: ±0.3			
DATE				REV. 0				公差: ±3°			
SHEET				5-1				1 OF 1			

(CUSTOMER DRAWING) 参考 面

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[175124-1](#)