


LOC	DIST	REVISIONS			
		P	LTR	DESCRIPTION	DATE
J			D	REVISED PER ECR-15-011723	08AUG2015



- ① 標準接圧型コンタクト：一般向け及び多極用
- ② 高接圧型コンタクト：高電流用及び強振動用
- ③ 金めっきは接続部のみとする
- 4 製品規格：108-5349
- 5 取付け適用規格：114-5148

OBSOLETE	②	H	5	光沢錫めっき (BRIGHT TIN-PL.)	2-175195-5			
			5	光沢錫めっき (BRIGHT TIN-PL.)	1-175195-5			
			3	0.76μm 最小金めっき (0.76μm MIN. Au-PL.)	1-175195-3			
			2	0.38μm 最小金めっき (0.38μm MIN. Au-PL.)	1-175195-2			
	①	INACTIVE	5	光沢錫めっき (BRIGHT TIN-PL.)	175195-5			
			3	0.76μm 最小金めっき (0.76μm MIN. Au-PL.)	175195-3			
				2	0.38μm 最小金めっき (0.38μm MIN. Au-PL.)	175195-2		
	備考 (REMARK)		接圧表示 (ID-MARK)		めっきコード (PL. ID NO)	仕 上 (FINISH)	③	型 番 (P/N)
	接点タイプ		(CONT. TYPE)					

- ① CONTACT TYPE; LOW PRESSURE TYPE (FOR GENERAL)
- ② CONTACT TYPE; HIGH PRESSURE TYPE (FOR HIGH CURRENT OR ANTI-VIBRATION)
- ③ GOLD-PL. CONTACT AREA ONLY
- 4 PRODUCT SPEC: 108-5349
- 5 APPLICATION SPEC: 114-5148

GENERAL TOLERANCE 一般公差
10 ≥ : ±0.2
30 ≥ > 10: ±0.25
100 ≥ > 30: ±0.3
ANGLES: ±3°

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位: 耗
mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

MATERIAL
材料
(COPPER ALLOY)
銅合金

FINISH
仕上
(SEE TABLE)
表参照

DWN T-YONEBAYASHI 27JUN1990

CHK H.OBATA 14FEB1991

APVD S.MANABE 14FEB1991

PRODUCT SPEC
製品規格

APPLICATION SPEC
取付適用規格

WEIGHT

CUSTOMER DRAWING

SCALE 5:1

SHEET 1 OF 1

REV D

WIRE RANGE
抱合電線断面積 AWG 24-20
(0.2-0.5mmSQ) mm²

INSULATION DIA
被覆外径 1.2-2.6 mmø

TE Connectivity

M SIZE
DYNAMIC SERIES REC. CONTACT
ダイナミックシリーズリセプタクルコンタクト

SIZE A3

CAGE CODE 00779

DRAWING NO
番号 C-175195

RESTRICTED TO

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-175195-2](#)