


LOC		DIST		REVISIONS				
P	LTR	DESCRIPTION			DATE	DWN	APVD	
		S	REVISED	PER ECO-14-000066				

D




- TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADER IS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD.
- THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING.
- POINT OF MEASUREMENT FOR PLATING THICKNESS.
- PART INDICATED IS PACKAGED IN SINGLE TUBES.
- RETENTION FEATURES ON SOLDER TAILS, LOCATED AT MANUFACTURERS OPTION.
- FOR 2 POSITION PART ONLY, THE NOTED DIMENSION IS $.184$
- $\phi .1020$ FOR KINKED TAILS
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

C

B

SUPERSEDED BY 104351-8	8 OBSOLETE	1.784	1.700	17	36	2-104351-3
	4	.784	.700	7	16	2-104351-2
SUPERSEDED BY 1-104351-3	4	1.284	1.200	12	26	2-104351-1
	8 OBSOLETE	3.984	3.900	39	80	2-104351-0
8 OBSOLETE	8 OBSOLETE	2.984	2.900	29	60	1-104351-9
	8 OBSOLETE	2.484	2.400	24	50	1-104351-8
OBSOLETE	8 OBSOLETE	1.984	1.900	19	40	1-104351-7
	8 OBSOLETE	1.684	1.600	16	34	1-104351-6
SUPERSEDED BY 6-146268-4	8 OBSOLETE	1.484	1.400	14	30	1-104351-5
	8 OBSOLETE	1.384	1.300	13	28	1-104351-4
SUPERSEDED BY 6-146268-1	8 OBSOLETE	1.284	1.200	12	26	1-104351-3
	8 OBSOLETE	1.184	1.100	11	24	1-104351-2
8 OBSOLETE	8 OBSOLETE	1.084	1.000	10	22	1-104351-1
	8 OBSOLETE	.984	.900	9	20	1-104351-0
8 OBSOLETE	8 OBSOLETE	.884	.800	8	18	104351-9
	8 OBSOLETE	.784	.700	7	16	104351-8
8 OBSOLETE	8 OBSOLETE	.684	.600	6	14	104351-7
	8 OBSOLETE	.584	.500	5	12	104351-6
8 OBSOLETE	8 OBSOLETE	.484	.400	4	10	104351-5
	8 OBSOLETE	.384	.300	3	8	104351-4
8 OBSOLETE	8 OBSOLETE	.284	.200	2	6	104351-3
	8 OBSOLETE	.184	.100	1	4	104351-2
8 OBSOLETE	8 OBSOLETE	.084	—	—	2	104351-1
	8 OBSOLETE	REMARKS	C	B	A	NO OF POSN
	8 OBSOLETE	REMARKS	C	B	A	ASSEMBLY PART NUMBER



RECOMMENDED HOLE LAYOUT

A

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN	H MOLL	08FEB88	 TE Connectivity			
DIMENSIONS: INCHES				CHK	R FEJDT	08FEB88	NAME			
				APVD	R FEJDT	08FEB88				
TOLERANCES UNLESS OTHERWISE SPECIFIED:				PRODUCT SPEC			HEADER ASSY, MOD II, BREAKAWAY, DBL ROW, .100X.100 CL VERT, .025 SQ POSTS, WITH RETENTION FEATURE			
0 PLC ± .005				APPLICATION SPEC						
1 PLC ± .005				—			SIZE			
2 PLC ± .005				—			CAGE CODE			
3 PLC ± .005				—			DRAWING NO			
4 PLC ± .005				—			RESTRICTED TO			
MATERIAL				WEIGHT			A1			
HOUSING: FLAME RETARDANT THERMOPLASTIC				—			C=104351			
COLOR: BLACK				—			CUSTOMER DRAWING			
CONTACT: COPPER ALLOY				—			SCALE			
FINISH: .00015 GOLD IN CONTACT AREA, .000125-.000200 MATTE TIN-LEAD ON SOLDER TAIL, ALL OVER .000050 NICKEL				—			4:1			
—				—			SHEET			
—				—			1 OF 1			
—				—			REV			
—				—			S			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-104351-7](#)