






LOC	DIST	REVISIONS				
AD	39	REV	LTR	DESCRIPTION	DATE	DWN
		R2		REVISED PER ECO-15-004641	28MAR2015	JO




SECTION A—A
SCALE 20:1



SECTION B—B
INSULATION RANGE .025—.060
SCALE 20:1



SECTION C—C
SCALE 20:1



SECTION D—D
SCALE 20:1

- 1 .000100 MIN BRIGHT TIN—LEAD OVER .000050 MIN NICKEL ON ENTIRE CONTACT
- 2 .000050 MIN NICKEL ON ENTIRE CONTACT; .000015 MIN GOLD ON CONTACT AREA; .000050 MIN BRIGHT TIN—LEAD ON AREA M.
- 3 .000050 MIN NICKEL ON ENTIRE CONTACT; .000030 MIN GOLD ON CONTACT AREA; .000050 MIN BRIGHT TIN—LEAD ON AREA M.
- 4 LOOSE PIECE CUT—OFF DIMENSION.
- 5 .000100—.000200 TIN OVER .000050—.000100 NICKEL ON ENTIRE CONTACT.
- 6 PREPLATED MATERIAL: (.000015 MIN GOLD ON CONTACT AREA, .000050—.000100 TIN ON AREA M, ALL OVER .000050—.000100 NICKEL ON ENTIRE CONTACT).
- 7 PREPLATED MATERIAL: (.000030 MIN GOLD ON CONTACT AREA, .000050—.000100 TIN ON AREA M, ALL OVER .000050—.000100 NICKEL ON ENTIRE CONTACT).

STRIP	7	1-104479-8
LOOSE PIECE	7 REF	1-104479-3
LOOSE PIECE	6 REF	1-104479-2
LOOSE PIECE	5 REF	1-104479-1
STRIP	7	1-104479-0
STRIP	6	104479-9
STRIP	5	104479-8
LOOSE PIECE	5 REF	104479-7
LOOSE PIECE	2 REF	104479-6
LOOSE PIECE	2 REF	104479-5
STRIP	3	104479-4
STRIP	2	104479-3
STRIP	1	104479-2
REMARKS	FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. OBERMAN 5-9-89	TE Connectivity	
DIMENSIONS: INCHES		CHK K. HELM 5-12-89		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPROV R. ELICKER 5-12-89	NAME	
0 PLC ± .005		PRODUCT SPEC	CONTACT, CRIMP SNAP-IN	
1 PLC ± .005		108-1472	AMPMODU SHORT POINT, 20-24 AWG	
2 PLC ± .005		APPLICATION SPEC	SIZE	
3 PLC ± .005		114-25038	CAGE CODE	
4 PLC ± .005		WEIGHT	DRAWING NO	
ANGLES		—	A100779C104479	
MATERIAL PHOSPHOR BRONZE		FINISH SEE TABLE	RESTRICTED TO	
CUSTOMER DRAWING		SCALE 10:1	SHEET 1 OF 1	
			REV R2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[104479-5](#)