

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

JUN2011

© COPYRIGHT JUN2011 BY Tyco Electronics Japan G.K.


ALL RIGHTS RESERVED.

LOC
JDIST
-

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED PER ECR-10-020319	13OCT2010	HMR	TM
	C	REVISED	27JUN2011	M.M	N.Y
	CI	REVISED PER ECR-17-017336	28NOV2017	T.S	E.I

AS SHOWN:1-1871935-6



1. MATERIAL: HOUSING: GLASS FILLED THERMO PLASTIC
POLYESTER(94V-0), COLOR: BLACK
CONTACT: COPPER ALLOY
RETENTION LEG: COPPER ALLOY

2. FINISH(ALL OVER): NICKEL PL. 1.27μmMIN

3. FINISH(CONTACT AREA): GOLD PL. 0.3μmMIN AFTER 2.




4. FINISH(CONTACT TAIL, RETENTION LEG)

: TIN PL. 2μmMIN AFTER 2.


2 3
CONTACT TAB

2 4
RETENTION LEG

ROW ID
BOTH SIDE



RECOMEND PC BOARD HOLE PATTEEN
: CONNECTOR MOUNT SIDE (NOT ACCUMULATE TOLERANCE)
PC BOARD THICKNESS : 1.0~1.6±0.1



SCALE: 1
(1-1871935-8)
(2-1871935-5)

38	18	63.0	70.3	72.3	2-1871935-9
30	14	49.0	56.3	58.3	2-1871935-5
22	10	35.0	42.3	44.3	2-1871935-1
16	7	24.5	31.8	33.8	1-1871935-8
12	5	17.5	24.8	26.8	1-1871935-6
8	3	10.5	17.8	19.8	1-1871935-4
POS.	n	A	B	C	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN S. TAKADA 09APR2007

CHK J. AKASAKA 09APR2007

APVD J. AKASAKA 09APR2007

PRODUCT SPEC

108-78336

APPLICATION SPEC


-

WEIGHT -

CUSTOMER DRAWING

DIMENSIONS:

mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

±0.3, ±3°

0-PLC ±

1-PLC ±

2-PLC ±

3-PLC ±

4-PLC ±

ANGLES ±

MATERIAL

-

FINISH

2

3

4

TE

TE Connectivity

NAME				
DYNAMIC D1900D 3.5mmPITCH HDR ASSY (H-TYPE) 8-38 POS				
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
A3	00779	C-1871935	-	
SCALE		SHEET	OF	REV
4:1		1	1	CI

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-1871935-5](#)