

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	20
© COPYRIGHT 20	BY -	ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B3	REVISED PER ECO-11-005027	12MAR2011	RK	HMR

1 MATERIAL:
CONTACT: BRASS
LATCH HOUSING, INSERT, COLLET, COLLET NUT:
UL 94V-0 RATED THERMOPLASTIC
COLOR:
COLLET AND INSERT: GRAY
LATCH HOUSING AND NUT: SEE TABLE


2 FINISH:
CONTACT, 0.75µm MIN. GOLD OVER NICKEL

3 SOLDER TERMINATION CONTACT, 28 AWG WIRE MAX.


4. PRODUCT IS SUPPLIED UNASSEMBLED.




SCALE 3:1



INSERT SUB-ASSY
CIRCUIT DESIGNATION VIEW



80° KEYING
SCALE 4:1



0° KEYING
SCALE 4:1

SEE SHEET 2 FOR
PART NUMBER SELECTION

PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. MILLER CHK L. BREKOSKY APVD - PRODUCT SPEC 108-2249 APPLICATION SPEC 114-13184 WEIGHT -		09MAR2006 09MAR2006		 TE Connectivity							
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME									
		0 PLC ± 1 PLC ±0.13 2 PLC ±0.08 3 PLC ± 4 PLC ± ANGLES ±1° FINISH		10 POSITION, CABLE COLLET STRAIGHT PLUG ASSEMBLY 0 AND 80 DEGREE KEYING									
MATERIAL		1		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO			
				A2		00779		C-1877848		-			
CUSTOMER DRAWING						SCALE		4:1		SHEET 1 OF 3		REV B3	

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

LOC

DIST

AD

00

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

Ø 2.7-Ø 3.9

BLUE

GRAY

80°

7-1877848-2

Ø 4.0-Ø 5.2

BLUE

GRAY

80°

7-1877848-1

Ø 5.3-Ø 6.5

BLUE

GRAY

80°

7-1877848-0

Ø 2.7-Ø 3.9

BLUE

GRAY

0°

6-1877848-9

Ø 4.0-Ø 5.2

BLUE

GRAY

0°

6-1877848-8

Ø 5.3-Ø 6.5

BLUE

GRAY

0°

6-1877848-7

Ø 2.7-Ø 3.9

BLUE

BLACK

80°

6-1877848-6

Ø 4.0-Ø 5.2

BLUE

BLACK

80°

6-1877848-5

Ø 5.3-Ø 6.5

BLUE

BLACK

80°

6-1877848-4

Ø 2.7-Ø 3.9

BLUE

BLACK

0°

6-1877848-3

Ø 4.0-Ø 5.2

BLUE

BLACK

0°

6-1877848-2

Ø 5.3-Ø 6.5

BLUE

BLACK

0°

6-1877848-1

Ø 2.7-Ø 3.9

GREEN

GRAY

80°

6-1877848-0

Ø 4.0-Ø 5.2

GREEN

GRAY

80°

5-1877848-9

Ø 5.3-Ø 6.5

GREEN

GRAY

80°

5-1877848-8

Ø 2.7-Ø 3.9

GREEN

GRAY

0°

5-1877848-7

Ø 4.0-Ø 5.2

GREEN

GRAY

0°

5-1877848-6

Ø 5.3-Ø 6.5

GREEN

GRAY

0°

5-1877848-5

Ø 2.7-Ø 3.9

GREEN

BLACK

80°

5-1877848-4

Ø 4.0-Ø 5.2

GREEN

BLACK

80°

5-1877848-3

Ø 5.3-Ø 6.5

GREEN

BLACK

80°

5-1877848-2

Ø 2.7-Ø 3.9

GREEN

BLACK

0°

5-1877848-1

Ø 4.0-Ø 5.2

GREEN

BLACK

0°

5-1877848-0

Ø 5.3-Ø 6.5

GREEN

BLACK

0°

4-1877848-9

Ø 2.7-Ø 3.9

YELLOW

GRAY

80°

4-1877848-8

Ø 4.0-Ø 5.2

YELLOW

GRAY

80°

4-1877848-7

Ø 5.3-Ø 6.5

YELLOW

GRAY

80°

4-1877848-6

Ø 2.7-Ø 3.9

YELLOW

GRAY

0°

4-1877848-5

Ø 4.0-Ø 5.2

YELLOW

GRAY

0°

4-1877848-4

Ø 5.3-Ø 6.5

YELLOW

GRAY

0°

4-1877848-3

Ø 2.7-Ø 3.9

YELLOW

BLACK

80°

4-1877848-2

Ø 4.0-Ø 5.2

YELLOW

BLACK

80°

4-1877848-1

Ø 5.3-Ø 6.5

YELLOW

BLACK

80°

4-1877848-0

Ø 2.7-Ø 3.9

YELLOW

BLACK

0°

3-1877848-9

Ø 4.0-Ø 5.2

YELLOW

BLACK

0°

3-1877848-8

Ø 5.3-Ø 6.5

YELLOW

BLACK

0°

3-1877848-7

CABLE RANGE

COLLET NUT
COLOR

LATCH HOUSING
COLOR

KEYING

PART NO.

PART NUMBERS 37 THRU 72

Ø 2.7-Ø 3.9

WHITE

GRAY

80°

3-1877848-6

Ø 4.0-Ø 5.2

WHITE

GRAY

80°

3-1877848-5

Ø 5.3-Ø 6.5

WHITE

GRAY

80°

3-1877848-4

Ø 2.7-Ø 3.9

WHITE

GRAY

0°

3-1877848-3

Ø 4.0-Ø 5.2

WHITE

GRAY

0°

3-1877848-2

Ø 5.3-Ø 6.5

WHITE

GRAY

0°

3-1877848-1

Ø 2.7-Ø 3.9

WHITE

BLACK

80°

3-1877848-0

Ø 4.0-Ø 5.2

WHITE

BLACK

80°

2-1877848-9

Ø 5.3-Ø 6.5

WHITE

BLACK

80°

2-1877848-8

Ø 2.7-Ø 3.9

WHITE

BLACK

0°

2-1877848-7

Ø 4.0-Ø 5.2

WHITE

BLACK

0°

2-1877848-6

Ø 5.3-Ø 6.5

WHITE

BLACK

0°

2-1877848-5

Ø 2.7-Ø 3.9

RED

GRAY

80°

2-1877848-4

Ø 4.0-Ø 5.2

RED

GRAY

80°

2-1877848-3

Ø 5.3-Ø 6.5

RED

GRAY

80°

2-1877848-2

Ø 2.7-Ø 3.9

RED

GRAY

0°

2-1877848-1

Ø 4.0-Ø 5.2

RED

GRAY

0°

2-1877848-0

Ø 5.3-Ø 6.5

RED

GRAY

0°

1-1877848-9

Ø 2.7-Ø 3.9

RED

BLACK

80°

1-1877848-8

Ø 4.0-Ø 5.2

RED

BLACK

80°

1-1877848-7

Ø 5.3-Ø 6.5

RED

BLACK

80°

1-1877848-6

Ø 2.7-Ø 3.9

RED

BLACK

0°

1-1877848-5

Ø 4.0-Ø 5.2

RED

BLACK

0°

1-1877848-4

Ø 5.3-Ø 6.5

RED

BLACK

0°

1-1877848-3

Ø 2.7-Ø 3.9

GRAY

GRAY

80°

1-1877848-2

Ø 4.0-Ø 5.2

GRAY

GRAY

80°

1-1877848-1

Ø 5.3-Ø 6.5

GRAY

GRAY

80°

1-1877848-0

Ø 2.7-Ø 3.9

GRAY

GRAY

0°

1877848-9

Ø 4.0-Ø 5.2

GRAY

GRAY

0°

1877848-8

Ø 5.3-Ø 6.5

GRAY

GRAY

0°

1877848-7

Ø 2.7-Ø 3.9

BLACK

BLACK

80°

1877848-6

Ø 4.0-Ø 5.2

BLACK

BLACK

80°

1877848-5

Ø 5.3-Ø 6.5

BLACK

BLACK

80°

1877848-4

Ø 2.7-Ø 3.9

BLACK

BLACK

0°

1877848-3

Ø 4.0-Ø 5.2

BLACK

BLACK

0°

1877848-2

Ø 5.3-Ø 6.5

BLACK

BLACK

0°

1877848-1

CABLE RANGE

COLLET NUT
COLOR

LATCH HOUSING
COLOR


KEYING

PART NO.

PART NUMBERS 1 THRU 36

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±0.13
2 PLC ±0.08
3 PLC ±
4 PLC ±
ANGLES ±1°
FINISH

DWN
K. MILLER
CHK
L. BREKOSKY
APVD
-

PRODUCT SPEC
108-2249
APPLICATION SPEC
114-13184
WEIGHT
-

CUSTOMER DRAWING

09MAR2006
09MAR2006
-

NAME
10 POSITION, CABLE COLLET
STRAIGHT PLUG ASSEMBLY
0 AND 80 DEGREE KEYING

SIZE
A2

CAGE CODE
00779

DRAWING NO
1877848

RESTRICTED TO
-

SCALE
4:1

SHEET
2

OF
3

REV
B3

TE Connectivity

1471-9 (3/11)

LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			-	SEE SHEET 1	-	-	-

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 09MAR2006 K. MILLER CHK 09MAR2006 L. BREKOSKY		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME 10 POSITION, CABLE COLLET STRAIGHT PLUG ASSEMBLY 0 AND 80 DEGREE KEYING	
		0 PLC ±. 1 PLC ±0.13 2 PLC ±0.08 3 PLC ±. 4 PLC ±. ANGLES ±1°		PRODUCT SPEC 108-2249 APPLICATION SPEC 114-13184	
MATERIAL -		FINISH -		SIZE A2	CAGE CODE 00779
		WEIGHT -		DRAWING NO C-1877848	
CUSTOMER DRAWING				SCALE 4:1	SHEET 3 OF 3
				REV B3	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-1877848-4](#)