




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		C	REVISED PER ECR-12-013486	09JAN13	KH	KR


SUGGESTED MATING TAB



- MATL: 1/2 H BRASS OR NICKEL PL STEEL.
- NO BURRS PERMISSIBLE AT HOLE.
MUST BE FLAT WITHIN 0.076 [.003] OVER THIS LENGTH.
- TIN PLATING IS REQUIRED ON BRASS WHEN TERMINAL TEMP. IS OVER 225° F
- HOLE MUST BE SYMMETRICAL ABOUT TAB C WITHIN 0.076 [.003]
- * TO BE USED ONLY WHEN SHOULDER IS ELIMINATED.




SECTION D-D




SECTION B-B

- CONTINUOUS STRIP ON REELS.
- ACCEPTS [#16-#12] SINGLE WIRE SIZES AND COMBINATIONS OF TWO[#16'S] OR TWO[#18'S] OR ONE[#16 WITH ONE#18]. WIRE CRIMP WIDTH IS .140, F TYPE
- FITS INSULATION RANGE 3.05-4.32 [.120-.170] DIA OR TWO AT 3.05 [.120] MAX. INSULATION CRIMP WIDTH .240 F TYPE



SECTION A-A



SECTION C-C

TIN PLATE	1217092-2
-	1217092-1
FINISH	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 6/3/98		 TE Connectivity			
		CHK MS FEHER 6/3/98					
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		APVD D BRATINA 6/3/98		NAME	
		0 PLC ± -		RECEPTACLE, POSITIVE LOCK, 6.35 [.250] SERIES -			
		1 PLC ± -					
		2 PLC ± 0.25 [.010]					
		3 PLC ± -					
4 PLC ± -		PRODUCT SPEC					
		APPLICATION SPEC					
		114-2061		SIZE		CAGE CODE	
MATERIAL		FINISH		WEIGHT		DRAWING NO	
BRASS		SEE TABLE		-		A2 00779 C=1217092	
				CUSTOMER DRAWING		RESTRICTED TO	
						-	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1217092-1](#)