






SUGGESTED MATING TAB




- 1 - MATL: 1/2H BRASS OR NICKEL PL STEEL.
- 2 - NO BURRS PERMISSIBLE AT HOLE.
- 3 - MUST BE FLAT WITHIN 0.076 [.003] OVER THIS LENGTH.
- 4 - TIN PLATING IS REQUIRED ON BRASS WHEN TERMINAL TEMP. IS OVER 225°F.
- 5 - HOLE MUST BE SYMMETRICAL ABOUT TAB Q WITHIN 0.076 [.003]
- * TO BE USED ONLY WHEN SHOULDER IS ELIMINATED.




SECTION D-D



SECTION B-B




SECTION A-A



SECTION C-C

- 1 CONTINUOUS STRIP ON REELS.
- 2 ACCEPTS [#16-#12] SINGLE WIRE SIZES AND COMBINATIONS OF TWO[#16'S] OR TWO[#18'S] OR ONE[#16 WITH ONE#18]. WIRE CRIMP WIDTH IS .140, F TYPE
- 3 FITS INSULATION RANGE 3.05-4.32 [.120-.170] DIA OR TWO AT 3.05 [.120] MAX. INSULATION CRIMP WIDTH .240 F TYPE
- 4 PRELIMINARY - NOT FOR PRODUCTION

4	SILVER 0.00381 [.000150] MIN	1217095-3
	TIN 0.002032 [.000080] MIN	1217095-2
	-	1217095-1
	FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 6/19/98		 TE Connectivity				
DIMENSIONS: mm[INCHES]		CHK MS FEHER 6/19/98						
		APVD J GILLESPIE 6/19/98		NAME RECEPTACLE, POSITIVE LOCK, 6.35 [.250] SERIES —				
		PRODUCT SPEC —						
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± 0.25 [.010] 3 PLC ± — 4 PLC ± — ANGLES ± —		APPLICATION SPEC 114-2074		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
MATERIAL H06 BRASS		WEIGHT —		A2	00779	C-1217095	—	
SEE TABLE		CUSTOMER DRAWING				SCALE 5:1	SHEET 1 of 1	REV B2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1217095-1](#)