




LOC E	DIST B	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			BA1	REVISED PER ECO-11-005150	21MAR11	RK	HMR



Technical Specification

Dissipation at 25°C	10 Watts Mounted on std heatsink
BS Ohmic Range	R01 to 10K
Stability	$\Delta R \leq 1\%$ per 1000hrs
Isolation Voltage	1400V DC/AC pk
Max Working Voltage	160 V DC/AC rms
Temp Coefficient	$<100R \pm 50 \text{ ppm/}^\circ\text{C}$ $>100R \pm 30 \text{ ppm/}^\circ\text{C}$
Climatic Category	55/200/56



RoHS Compliant

FOR A SPECIFIC PN FOR A RESISTANCE VALUE AND TOLERANCE, PLEASE REFER TO DMF.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R BLANCH 19SEPT06		<div>TE Connectivity</div>			
		CHK J CATCHPOLE 19SEPT06					
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD J CATCHPOLE 19SEPT06		NAME THS10 METAL CLAD RESISTOR			
	0 PLC ± 0.5	PRODUCT SPEC		SIZE A3 CAGE CODE 00779 DRAWING NO C-1879073 RESTRICTED TO —			
	1 PLC ± 0.2	—					
	2 PLC ± 0.1	APPLICATION SPEC					
	3 PLC ± —	—					
4 PLC ± —	± 5	WEIGHT —					
MATERIAL —	FINISH —	CUSTOMER DRAWING			SCALE NTS	SHEET 1 OF 1	REV BA1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-1879073-3](#)