





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
E	B		BB	ECR-15-016499	16NOV2015	KR	TN

D

C

B

A



NOTES:

- POWER RATING: 120W
- INSULATION RESISTANCE DC 500V - 20M Ohms Min.
- VOLTAGE RESISTABILITY: AC 2500V, 50Hz/1 Min.
- TUBE BORE AND SIDE FACES SHOULD BE FREE OF PAINT
- PARTS SHALL BE BLANK, SMOOTH, FREE OF BURRS AND ALL OTHER FOREIGN MATERIAL
- FOR FURTHER INFORMATION SEE DATASHEET FOR TE SERIES HIGH POWER WIRE WOUND RESISTOR
- FOR SPECIFIC PART NUMBER, RESISTANCE VALUE AND TOLERANCE PLEASE REFER TO SMART PART SEARCH

D

C

B

A

RoHS Compliant

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN PRASAD K 26SEP2011	 TE Connectivity			
DIMENSIONS: mm		CHK J.CATCHPOLE 26SEP2011				
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.5 1 PLC ±0.1 2 PLC ±0.05 3 PLC ± 4 PLC ± ANGLES ±0.5°	APVD J.CATCHPOLE 26SEP2011	NAME HIGH POWER WIRE WOUND RESISTOR TE 120W SERIES			
		PRODUCT SPEC -				
		MATERIAL -	FINISH -	APPLICATION SPEC -	SIZE A2	CAGE CODE 00779
CUSTOMER DRAWING			SCALE 1:1	SHEET 1	OF 1	REV BB

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1879445-4](#)