



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	E1	REVISED PER ECR-18-007294	21MAR2019	BDA	SV



- 1 CONTINUOUS STRIP ON REELS (SPLICE FREE) WITH TERMINALS LOCATED ON 5.59 ± 0.08 [$.220 \pm .003$] CENTERS.
-  2 SLOT TERMINATES A SINGLE OR DOUBLE MAGNET WIRE. COPPER RANGE: 0.36–0.57mm [#27–#23] AWG. OR ALUMINIUM RANGE: 0.51–0.64mm [#24–#22] AWG. ALUMINIUM RANGE IS APPLICABLE FOR POST TIN PLATED PART NUMBERS ONLY.
- 3 AFTER INSERTION INTO PLASTIC HOLDER TAB PORTION MUST BE BENT OVER 45° TO 90° OR POTTED-IN TO PREVENT PULL-OUT WHEN MATING RECEPTACLE IS DISCONNECTED.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 200CT2016 VJUI SUBRAMANIAN		 TE Connectivity	
		CHK 200CT2016 VJUI SUBRAMANIAN			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME TAB, 4.75[.187] FASTON TM 300 SERIES MAG-MATE TM —	
		APVD 200CT2016 SENTHIL PRODUCT SPEC 108-2012			
0 PLC ± — 1 PLC ± — 2 PLC ± 0.25[.010] 3 PLC ± — 4 PLC ± — ANGLES ± 1°		APPLICATION SPEC 114-2046			
MATERIAL 4M PRE-MILLED BRASS		FINISH 0.002032[.000080] MIN TIN PLATE			
		WEIGHT 0		SIZE A2	
		CAGE CODE 00779		DRAWING NO C-1217243	
		RESTRICTED TO —			
		CUSTOMER DRAWING		SCALE 10:1 SHEET 1 of 1 REV F1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1217243-1](#)