



1. MATERIAL:
HOUSING:
PBT POLYESTER, BLACK, UL 94V-0
TERMINALS:
0.33 THICK PHOSPHOR BRONZE PLATED WITH 1.27µm MINIMUM THICK
HARD GOLD IN LOCALIZED AREA AND 2.0µm MINIMUM THICK
MATTE TIN IN COMPLIANT PIN TERMINAL AREA
OVER 1.27µm MINIMUM THICK NICKEL UNDERPLATE
SHIELD:
0.25 THICK COPPER ALLOY PLATED WITH 2.03µm MINIMUM TIN
OVER 1.27 µm MINIMUM NICKEL
GROUND CLIP: 0.25 THICK COPPER ALLOY PRE-PLATED WITH 2.03µm
MINIMUM MATTE TIN OVER 1.27µm MINIMUM NICKEL
2. JACK CAVITY CONFORMS TO FCC RULES AND REGULATIONS, PART 68
SUBPART F.




15.88	WITH GROUND CLIP	1888654-4
15.88	WITH GROUND CLIP	1888654-3 (SHOWN)
16.13	WITHOUT GROUND CLIP	1888654-2
16.13	WITHOUT GROUND CLIP	1888654-1
M DIM	DESCRIPTION	PART NUMBER

AMP 4805 REV 31MAR2000




AMC PANEL AND PRINTED CIRCUIT BOARD LAYOUT


SCALE 2:1



DETAIL B
SCALE 8:1
PLATED PADS REQUIRED FOR
1888654-3 & -4 (PRODUCT WITH
GROUNDING CLIP)
8 PLC



PC BOARD LAYOUT (COMPONENET SIDE)

101. DRAWING IS A COMPUTER GENERATED DRAWING. THE INFORMATION CONTAINED HEREIN IS UNCLASSIFIED EXCEPT WHERE SHOWN OTHERWISE. IT IS THE PROPERTY OF THE U.S. GOVERNMENT AND IS NOT TO BE DISTRIBUTED OUTSIDE THE GOVERNMENT. IT SHOULD BE CONTAINED FOR THE LATEST VERSION.		DWN 280C2006 J. A. MAYER CHW 280C2006 WESTMAN APPD 280C2006 S. E. CLINKINGER		Tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm 		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± .03 2 PLC ± 3 PLC ± ANGLES ±1° FINISH		NAME STACKED MOD JACK ASSEMBLY, 2 X 8, 8 POSN, SHIELDED, PANEL GROUND, OFFSET, CAT 5	
MATERIAL SEE NOTE 1		WEIGHT -		SIZE CAGE CODE DRAWING NO A 00779 C=1888654	
SEE NOTE 1		CUSTOMER DRAWING		RESTRICTED TO SCALE 1:1 SHEET 2 OF 2 REV C	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1888654-3](#)