

4

3

2


1

THIS DRAWING IS UNPUBLISHED.



RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
AF	50		C	REVISED PER 0G3A-0252-04	05APR04	MF DD



- 1 CONTINUOUS STRIP ON REELS
- 2 WIRE SIZE IS [#20-#16] AWG.
- 3 INSULATION RANGE IS 3.30 [.130] MAX
- △ PRELIMINARY — NOT FOR PRODUCTION.



SECTION X-X



SECTION Y-Y

TERMINALS OFF BOTTOM OF REEL
FOR -2 ONLY

DETAIL D

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 30APR2002 MICHAEL S. FEHER		SEE DETAIL D		△ 1217825-2	
DIMENSIONS: mm		CHK 30APR2002 DONALD DECKER		STANDARD		1217825-1	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 30APR2002 DONALD DECKER		REELING		PART NUMBER	
0 PLC ± -		PRODUCT SPEC		NAME		FLUORESCENT TUBE SOCKET TERMINAL	
1 PLC ± -		APPLICATION SPEC		SIZE		CAGE CODE	
2 PLC ± 0.25 [.010]		WEIGHT		DRAWING NO		RESTRICTED TO	
3 PLC ± -		CUSTOMER DRAWING		A2 00779		C=1217825	
4 PLC ± -		SCALE		8:1		SHEET 1 OF 1	
ANGLES ± -		REV		C			
MATERIAL H04 BRASS		FINISH 0.002032 [.000080] MIN TIN PLATE					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1217825-1](#)