



THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION
© COPYRIGHT - By -	ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B2	REVISED PER ECO-11-004820	11MAR11	RK	HMR
	B3	REVISED PER ECO-18-007846	13AUG2018	RS	DR
	B4	REVISED PER ECO-18-015552	03OCT2018	RS	DR



- 1** STAMP "AMP 12-10*", LOCATION APPROX AS SHOWN.
- 2** BODY MATERIAL THICKNESS IS 0.991 ± 0.051 [$.039 \pm .002$]
- 3** APPLIES FROM THE EDGE OF THE METAL WIRE BARREL TO CENTER OF STUD HOLE.
- 4** NOTE DELETED
- 5** BODY - COPPER PER ASTM B-152
SLEEVE - COPPER PER ASTM B-152
INSULATION - NYLON
- 6** BODY - TIN PL PER ASTM B-545
SLEEVE - TIN PL PER ASTM B-545
INSULATION - COLOR - YELLOW
- 7** 105°C [221°F] MAX OPERATING TEMPERATURE.
- 8** 300 VOLT MAX
- 9** 2.62-6.64mm² [5,180 - 13,100 CMA]
SOLID OR STRANDED
- 10** NOTE DELETED
- 11** INTERNAL EDGE FEATURE MAY BE SOLID OR SCALLOPED

.150-.250	2500	REELED ON TAPE	2-130171-1
.150-.250	500	LOOSE PIECE	130171
WIRE INSULATION OD RANGE	QTY	PACKAGE TYPE	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN jr ruth 20FEB06	 TE Connectivity Ltd.			
DIMENSIONS: mm [INCHES]		CHK T MICHIELUTTI 20FEB06				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD T MICHIELUTTI 20FEB06	NAME TERMINAL RING TONGUE, PIDG, WIRE SIZE 12-10 AWG			
		PRODUCT SPEC UL 486 A-B				
MATERIAL		APPLICATION SPEC 114-2157	SIZE A3			
FINISH		WEIGHT -	CAGE CODE 00779			
5		6	DRAWING NO C-130171			
CUSTOMER DRAWING		SCALE 4:1	SHEET 1 of 1		REV B4	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-130171-1](#)