

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -


ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A2	ECR-15-009282	04AUG2015	KG	DW

BOOT ASSEMBLY
MAT'L: STAINLESS ALLOY / EPDM

SET SCREW, M4x6
MAT'L: STAINLESS
STEEL



EXTENSION
MAT'L: SEE TABLE
FINISH: SEE TABLE


CRIMP SUPPORT
MAT'L: NICKEL-SILVER ALLOY

CRIMP SLEEVE
MAT'L: NICKEL-SILVER ALLOY

1918933-1 SHOWN

BOOT ASSEMBLY
MAT'L: STAINLESS ALLOY / EPDM

SET SCREW, M4x6
MAT'L: STAINLESS
STEEL



EXTENSION
MAT'L: SEE TABLE
FINISH: SEE TABLE

CRIMP SUPPORT
MAT'L: NICKEL-SILVER ALLOY

CRIMP SLEEVE
MAT'L: NICKEL-SILVER ALLOY

1918933-3 SHOWN

EXTENSION USED ON
1918933-7

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 30OCT2006

K. GLATFELTER

CHK 04JUN2008

D. WERTMAN

APVD 04JUN2008

D. WERTMAN

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

Customer Drawing



TE Connectivity


NAME
CABLE ADAPTER KIT W/BOOT,
STD BULKHEAD, PRO BEAM JR.

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A300779C-1918933

SCALE 2:1 SHEET 1 OF 2 REV A2

DIMENSIONS:
mm



TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

MATERIAL
AS LISTED

FINISH
AS LISTED

4

3

2

1

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	20
© COPYRIGHT 20	BY -	ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

SUPERSEDED BY:
3-1918933-2

SUPERSEDED BY:
3-1918933-1

SUPERSEDED BY:
3-1918933-0

SUPERSEDED BY:
2-1918933-9

SUPERSEDED BY:
2-1918933-8

SUPERSEDED BY:
2-1918933-7

SUPERSEDED BY:
2-1918933-6

SUPERSEDED BY:
2-1918933-5

CONDUCTIVE OLIVE DRAB ZINC
ON ALUMINUM ALLOY

4 x 3mm	2-1918933-4
7.5mm	2-1918933-3
6.7mm	2-1918933-2
6.0mm	2-1918933-1
5.5mm	2-1918933-0
5.0mm	1-1918933-9
4.2mm	1-1918933-8
3.2mm	1-1918933-7

NICKEL ALUMINUM BRONZE ALLOY


4 x 3mm	1-1918933-6
7.5mm	1-1918933-5
6.7mm	1-1918933-4
6.0mm	1-1918933-3
5.5mm	1-1918933-2
5.0mm	1-1918933-1
4.2mm	1-1918933-0
3.2mm	1918933-9

HARD ANODIZE FINISH
ON ALUMINUM ALLOY

4 x 3mm	1918933-8
7.5mm	1918933-7
6.7mm	1918933-6
6.0mm	1918933-5
5.5mm	1918933-4
5.0mm	1918933-3
4.2mm	1918933-2
3.2mm	1918933-1

CONDUCTIVE BLACK ZINC-NICKEL ON ALUMINUM ALLOY	4 x 3mm	3-1918933-2
	7.5mm	3-1918933-1
	6.7mm	3-1918933-0
	6.0mm	2-1918933-9
	5.5mm	2-1918933-8
	5.0mm	2-1918933-7
	4.2mm	2-1918933-6
	3.2mm	2-1918933-5
DESCRIPTION	MAXIMUM CABLE DIAMETER	PART NUMBER

DESCRIPTION	MAXIMUM CABLE DIAMETER	PART NUMBER
-------------	---------------------------	-------------

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. GLATFELTER 30OCT2006	 TE Connectivity			
DIMENSIONS: mm		CHK D. WERTMAN 04JUN2008				
		APVD D. WERTMAN 04JUN2008	NAME CABLE ADAPTER KIT W/BOOT, STD BULKHEAD, PRO BEAM JR. -			
		PRODUCT SPEC -				
		APPLICATION SPEC -				
		WEIGHT -				
MATERIAL AS LISTED -		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-	SIZE A3	CAGE CODE 00779	DRAWING NO C-1918933	RESTRICTED TO -
FINISH AS LISTED -		Customer Drawing	SCALE 1:1	SHEET 2 OF 2	REV A2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1918933-4](#)