

4										3										2										1									
THIS DRAWING IS UNPUBLISHED.										RELEASED FOR PUBLICATION																				REVISIONS									
© COPYRIGHT - -										ALL RIGHTS RESERVED.																				P LTR DESCRIPTION DATE DWN APVD									
																														V REVISED PER ECO-15-011608 04NOV2015 NK MZ									
																														W REVISED PER ECO-18-000435 17JAN2018 RS MZ									
																														Y REVISED PER ECO-19-014914 27SEP2019 RS MZ									

A	[.46]	[.028]	--	12	9.5[.375]	6	38	0.18[.007]	04121	5-192043-0		
A	[.46]	[.028]	--	12	9.5[.375]	1-2	38	0.18[.007]	04128	4-192043-9	OBSOLETE	
A	[.46]	[.028]	--	12	9.5[.375]	UNPL	38	0.18[.007]	04120	4-192043-8	OBSOLETE	
A	[.55]	[.024]	--	12	9.5[.375]	6	38	0.15[.006]	04108	4-192043-7		
A	[.60]	[.028]	--	12	9.5[.375]	3-2	39	0.15[.006]	--	4-192043-6		
A	[.55]	[.024]	--	12	9.5[.375]	3-2	38	0.15[.006]	04053	4-192043-5		
A	[.53]	[.024]	--	12	9.5[.375]	1-2	38	0.15[.006]	04067	4-192043-4	OBSOLETE	
A	--	--	--	12	9.5[.375]	1-2	38	0.15[.006]	04092	4-192043-3	OBSOLETE	
SUPERSEDED BY 4-192043-1										04107	4-192043-2	
A	[.55]	[.024]	--	12	9.5[.375]	UNPL	38	0.15[.006]	04071	4-192043-1		
A	[.55]	[.026]	--	12	9.5[.375]	5-2	38	0.12[.005]	--	4-192043-0	OBSOLETE	
A	[.55]	[.026]	--	13	9.5[.375]	1-2	38	0.12[.005]	04174	3-192043-9		
A	[.55]	[.026]	--	13	9.5[.375]	UNPL	38	0.12[.005]	--	3-192043-8		
A	[.54]	[.026]	--	12	9.1[.359]	3-2	36	0.18[.007]	04204	3-192043-7	OBSOLETE	
A	[.54]	[.026]	--	12	9.1[.359]	1-2	36	0.18[.007]	04184	3-192043-6	OBSOLETE	
A	[.54]	[.026]	--	12	9.1[.359]	UNPL	36	0.18[.007]	04183	3-192043-5		
A	--	--	--	12	8.9[.359]	3-2	35	0.115[.006]	04178	3-192043-4	OBSOLETE	
A	--	--	--	12	8 [.315]	3-2	30	0.18[.007]	04177	3-192043-3	OBSOLETE	
A	--	[.026]	--	12	8 [.315]	3-2	29	0.18[.007]	04179	3-192043-2	OBSOLETE	
A	[.38]	[.026]	--	12	8 [.315]	1-2	29	0.18[.007]	04206	3-192043-1		
A	[.38]	[.026]	--	12	8 [.315]	UNPL	29	0.18[.007]	04185	3-192043-0	OBSOLETE	
A	[.43]	[.024]	--	12	8 [.315]	3-2	32	0.15[.006]	--	2-192043-9		
A	[.40]	[.024]	--	12	8 [.315]	1-2	31	0.15[.006]	--	2-192043-8		
A	[.43]	[.024]	--	12	8 [.315]	1-2	32	0.15[.006]	04076	2-192043-7	OBSOLETE	
A	[.43]	[.024]	--	12	8 [.315]	UNPL	32	0.15[.006]	04052	2-192043-6	OBSOLETE	
A	[.40]	[.026]	--	13	7.9[.312]	UNPL	32	0.12[.005]	04079	2-192043-5	OBSOLETE	
A	--	--	--	12	7.5[.296]	1-2	32	0.18[.007]	04189	2-192043-4	OBSOLETE	
A	--	--	--	12	7.49[.295]	3-2	30	0.15[.006]	04051	2-192043-3	OBSOLETE	
A	--	--	--	12	7.44[.293]	3-2	29	0.12[.005]	04050	2-192043-2	OBSOLETE	
A	--	--	--	12	7.14[.281]	3-2	28	0.20[.008]	04049	2-192043-1	OBSOLETE	
A	[.45]	[.024]	--	12	7.1[.280]	3-2	28	0.15[.006]	04106	2-192043-0		
A	[.45]	[.024]	--	12	7.1[.280]	UNPL	28	0.15[.006]	04199	1-192043-9	OBSOLETE	
A	--	--	--	12	7[.276]	3-2	27	0.12[.005]	04047	1-192043-8	OBSOLETE	
A	--	--	--	12	6.45[.254]	7-2	26	0.15[.006]	04065	1-192043-7	OBSOLETE	
A	[.35]	[.024]	--	12	6.45[.254]	3-2	26	0.15[.006]	04075	1-192043-6		
A	[.35]	[.024]	--	12	6.45[.254]	1-2	26	0.15[.006]	04086	1-192043-5	OBSOLETE	
A	[.35]	[.024]	--	12	6.45[.254]	UNPL	26	0.15[.006]	04046	1-192043-4	OBSOLETE	
A	[.50]	[.026]	--	13	6.45[.254]	UNPL	26	0.12[.005]	04093	1-192043-3	OBSOLETE	
A	[.29]	[.024]	--	12	6.35[.250]	3-2	26	0.20[.008]	04045	1-192043-2		
A	[.29]	[.024]	--	12	6.35[.250]	1-2	26	0.20[.008]	04116	1-192043-1		
SUPERSEDED BY 1-192043-6										--	1-192043-0	
A	[.29]	[.016]	--	13	6.35[.250]	UNPL	26	0.12[.005]	04082	192043-9		
A	[.28]	[.024]	--	12	6 [.237]	3-2	24	0.15[.006]	04041	192043-8	OBSOLETE	
A	[.28]	[.024]	--	12	6 [.237]	UNPL	24	0.15[.006]	04042	192043-7		
A	[.28]	[.024]	--	12	5.54[.218]	1-2	23	0.15[.006]	04146	192043-6	OBSOLETE	
A	[.28]	[.024]	--	12	5.54[.218]	UNPL	23	0.15[.006]	04143	192043-5	OBSOLETE	
A	--	--	--	12	5.5[.217]	3-2	21	0.20[.008]	04040	192043-4	OBSOLETE	
A	[.27]	[.024]	--	12	5.5[.217]	3-2	21	0.15[.006]	04105	192043-3		
A	[.26]	[.024]	--	12	5 [.197]	3-2	20	0.15[.006]	04215	192043-2	OBSOLETE	
A	[.26]	[.024]	--	12	5 [.197]	UNPL	20	0.15[.006]	04216	192043-1		
STYLE	(FREE DIA)	LH	LENGTH	MAT'L (NOTE)	MATING PIN Ø REF	PLATING (NOTE NO.)	NUM LOUV	MAT'L THK	REF	PART NUMBER		

8.1
[.32]

(FREE DIA)

LENGTH
MIN

(LOUVER HEIGHT)

8.1
[.32]

LH

STYLE A
(FEMALE)

STYLE C
(STRIP)

1 FINISH-SILVER PLATE 200 μINCH THICK MIN.
2 FINISH-NICKEL PLATE 40 μINCH THICK MIN.
3 FINISH-GOLD PLATE 10 μINCH THICK MIN.
4 FINISH
5 FINISH-GOLD PLATE 40 μINCH THICK MIN.
6 FINISH-TIN PLATE 300 μINCH THICK MIN.
7 FINISH-GOLD PLATE 50 μINCH THICK MIN.
8 FINISH-NICKEL PLATE 100 μINCH THICK MIN.
9 FINISH-PREPLATE
10
11 PLATING NOTES ARE TO BE INTERPRETED AS FOLLOWS,
6-8 AS 6 OVER 8.
12 MATERIAL-CDA172, BeCu.
13 MATERIAL-STAINLESS STEEL
14 PRODUCT IS SOLD BY THE FOOT.

15 OBSOLETE (PENDING).

16 MATERIAL: ELGILOY.

17 PRELIMINARY PART NUMBER.

18 FINISH: COPPER PLATE 10 μINCH THICK MIN.

19 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

THIS DRAWING IS A CONTROLLED DOCUMENT.										DWN RA JAYNE 09-21-91		TE Connectivity CONTACT BAND, FEMALE												
DIMENSIONS: mm[INCHES]										CHK J.TURNER 07-21-93														
										APVD -		NAME												
										PRODUCT SPEC -		SIZE A2 CAGE CODE 00779 DRAWING NO C-192043 RESTRICTED TO -												
										APPLICATION SPEC -														
										WEIGHT -														
MATERIAL -										SEE TABLE		CUSTOMER DRAWING										SCALE 1:1	SHEET 1 of 2	REV Y

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[7-192043-2](#)