





9	OBSOLETE	9.51	19.02	7.6	15.2	19.35	7.795	15.2	17.34	2 1 8	40	6-1375870-8
9	OBSOLETE	9.11	18.22	7.2	14.4	18.55	7.395	14.4	16.54		38	6-1375870-7
9	OBSOLETE	8.71	17.42	6.8	13.6	17.75	6.995	13.6	15.74		36	6-1375870-6
9	OBSOLETE	8.31	16.62	6.4	12.8	16.95	6.595	12.8	14.94		34	6-1375870-5
		7.91	15.82	6	12	16.15	6.195	12	14.14		32	6-1375870-4
9	OBSOLETE	7.51	15.02	5.6	11.2	15.35	5.795	11.2	13.34		30	6-1375870-3
9	OBSOLETE	7.11	14.22	5.2	10.4	14.55	5.395	10.4	12.54		28	6-1375870-2
9	OBSOLETE	6.71	13.42	4.8	9.6	13.75	4.995	9.6	11.74		26	6-1375870-1
		6.31	12.62	4.4	8.8	12.95	4.595	8.8	10.94		24	6-1375870-0
9	OBSOLETE	5.91	11.82	4	8	12.15	4.195	8	10.14		22	5-1375870-9
9	OBSOLETE	5.51	11.02	3.6	7.2	11.35	3.795	7.2	9.34	20	5-1375870-8	
9	OBSOLETE	5.11	10.22	3.2	6.4	10.55	3.395	6.4	8.54	18	5-1375870-7	
		4.71	9.42	2.8	5.6	9.75	2.995	5.6	7.74	16	5-1375870-6	
		4.31	8.62	2.4	4.8	8.95	2.595	4.8	6.94	14	5-1375870-5	
		3.91	7.82	2	4	8.15	2.195	4	6.14	12	5-1375870-4	
		3.51	7.02	1.6	3.2	7.35	1.795	3.2	5.34	10	5-1375870-3	
9	OBSOLETE	3.11	6.22	1.2	2.4	6.55	1.395	2.4	4.54	8	5-1375870-2	
		2.71	5.42	0.8	1.6	5.75	0.995	1.6	3.74	6	5-1375870-1	
		9.51	19.02	7.6	15.2	19.35	7.795	15.2	17.34	40	1-1375870-8	
9	OBSOLETE	9.11	18.22	7.2	14.4	18.55	7.395	14.4	16.54	38	1-1375870-7	
9	OBSOLETE	8.71	17.42	6.8	13.6	17.75	6.995	13.6	15.74	36	1-1375870-6	
9	OBSOLETE	8.31	16.62	6.4	12.8	16.95	6.595	12.8	14.94	34	1-1375870-5	
		7.91	15.82	6	12	16.15	6.195	12	14.14	32	1-1375870-4	
9	OBSOLETE	7.51	15.02	5.6	11.2	15.35	5.795	11.2	13.34	30	1-1375870-3	
9	OBSOLETE	7.11	14.22	5.2	10.4	14.55	5.395	10.4	12.54	28	1-1375870-2	
9	OBSOLETE	6.71	13.42	4.8	9.6	13.75	4.995	9.6	11.74	26	1-1375870-1	
		6.31	12.62	4.4	8.8	12.95	4.595	8.8	10.94	24	1-1375870-0	
9	OBSOLETE	5.91	11.82	4	8	12.15	4.195	8	10.14	22	1375870-9	
		5.51	11.02	3.6	7.2	11.35	3.795	7.2	9.34	20	1375870-8	
		5.11	10.22	3.2	6.4	10.55	3.395	6.4	8.54	18	1375870-7	
		4.71	9.42	2.8	5.6	9.75	2.995	5.6	7.74	16	1375870-6	
		4.31	8.62	2.4	4.8	8.95	2.595	4.8	6.94	14	1375870-5	
		3.91	7.82	2	4	8.15	2.195	4	6.14	12	1375870-4	
		3.51	7.02	1.6	3.2	7.35	1.795	3.2	5.34	10	1375870-3	
		3.11	6.22	1.2	2.4	6.55	1.395	2.4	4.54	8	1375870-2	
		2.71	5.42	0.8	1.6	5.75	0.995	1.6	3.74	6	1375870-1	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG. K. KOEGL 07JUN2000 CHK. W. DAVIS 07JUN2000		STE TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		NAME AMPHINO MICRO INTERCONNECT RECEPTACLE ASSEMBLY	
		PRODUCT SPEC 108-1955		APVD	
MATERIAL 		APPLICATION SPEC 114-13051		SIZE CAGE CODE DRAWING NO A100779 C-1375870	
FINISH SEE TABLE		WEIGHT		RESTRICTED TO -	
CUSTOMER DRAWING				SCALE	20:1
				SHEET	1 OF 1
				REV	B2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-1375870-6](#)