

D

C

B

A




FIG. 1




FIG. 2







FIG. 3  
(8 POS ONLY)



P.C.B. HOLE LAYOUT  
TOLERANCE ±.003



- 1 MATERIALS:  
INSULATOR: POLYESTER, UL RATED 94V-0  
CONTACT:  
800 & 1800 SERIES CONTACT: 4 BEAM, COPPER ALLOY, MACHINED (PREMIUM VERSION) OR FORMED (ECONOMY VERSION, WITH SUFFIX -ES OR -ESL).  
800 SERIES HIGH RETENTION CONTACT: 4 BEAM, COPPER ALLOY, MACHINED.  
1000 SERIES CONTACT: 6 BEAM, COPPER ALLOY, MACHINED (LOW INSERTION FORCE SERIES)  
SLEEVE- ALL SERIES: COPPER ALLOY, FORMED
- 2 ELECTRICAL:  
CONTACT RESISTANCE: 10 MILLIOHMS MAX  
CONTACT RATING: 3 AMPS  
CAPACITANCE: 1.0 pF PER MIL-STD-202, METHOD 305  
INSULATION RESISTANCE: 5000 OHMS MIN @ 500 VDC PER MIL-STD-1344, METHOD 3003.1  
DIELECTRIC WITHSTANDING VOLTAGE: 1000 VOLTS (RMS) PER MIL-STD-1344, METHOD 3001.1
- 3 MECHANICAL:  
AFTER INSERTION FORCE: 37 GRAMS AVG (6 BEAM CONTACT) 134 GRAMS AVG (4 BEAM PREMIUM) 179 GRAMS AVG (4 BEAM ECONOMY) AND 334 GRAMS AVG (HIGH RETENTION)  
AFTER WITHDRAWAL FORCE: 15 GRAMS AVG (6 BEAM CONTACT) 63 GRAMS AVG (4 BEAM PREMIUM OR ECONOMY) AND 245 GRAMS AVG (HIGH RETENTION)
- 4 ENVIRONMENTAL:  
OPERATING TEMPERATURE: -55°C TO -105°C
- 5 PLATING: 25μ" MIN GOLD OVER 50μ" MIN NICKEL CONTACT WITH 5μ" MIN GOLD OVER 50μ" MIN NICKEL SLEEVE.
- 6 PLATING: 25μ" MIN GOLD OVER 50μ" MIN NICKEL CONTACT WITH 80μ" MIN TIN-LEAD OVER 50μ" MIN COPPER SLEEVE.
- 7 PLATING: 80μ" MIN TIN-LEAD OVER 75μ" MIN COPPER CONTACT WITH 180μ" MIN TIN-LEAD OVER 75μ" MIN NICKEL SLEEVE.
- 8 PLATING: 5μ" MIN GOLD FLASH OVER 50μ" MIN NICKEL CONTACT WITH 5μ" MIN GOLD FLASH OVER 50μ" MIN NICKEL SLEEVE.
- 9 PLATING: 5μ" MIN GOLD FLASH OVER 50μ" MIN NICKEL CONTACT WITH 80μ" MIN TIN-LEAD OVER 50μ" MIN COPPER SLEEVE.
- 10 PLATING: 7.5μ" MIN GOLD OVER 50μ" MIN NICKEL CONTACT WITH 80μ" MIN TIN-LEAD OVER 50μ" MIN COPPER SLEEVE.
- 11 PRELIMINARY PART - NOT RELEASED FOR PRODUCTION.
- 12 806-AGXXD-XXX SERIES IS SUPERSEDED BY 506-AGXXD-XXX SERIES (REFER TO CUSTOMER DRAWING 1437532-2)
- 13 PLATING: 25μ" MIN GOLD OVER 50μ" MIN NICKEL CONTACT WITH 80μ" MIN MATTE TIN OVER 50μ" MIN COPPER SLEEVE.
- 14 PLATING: 80μ" MIN MATTE TIN OVER 75μ" MIN COPPER CONTACT WITH 180μ" MIN MATTE TIN OVER 75μ" MIN NICKEL SLEEVE.
- 15 PLATING: 5μ" MIN GOLD FLASH OVER 50μ" MIN NICKEL CONTACT WITH 80μ" MIN MATTE TIN OVER 50μ" MIN COPPER SLEEVE.
- 16 PLATING: 7.5μ" MIN GOLD OVER 50μ" MIN NICKEL CONTACT WITH 80μ" MIN MATTE TIN OVER 50μ" MIN COPPER SLEEVE.
- 17 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

8 XX - AX XXX D - XXX - LF  
800 SERIES POSITIONS  
LF= LEAD FREE  
BLANK = MACHINED CONTACT  
ES = FORMED CONTACT, GOLD PLATE, NOTE 1  
ESL = FORMED CONTACT, LOW GOLD PLATE, 5μIN MAX  
D = PC TAIL STANDARD  
LSG STYLE AND TAIL CONFIGURATION  
AG = INSULATOR  
AR = INSULATOR WITH RAILS  
(ALMOST RUN THE LENGTH UNDER THE INSULATOR INSIDE THE CONTACT ROWS, .075 REF HIGH & .045 REF WIDE)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R BROWN 06MAY04	Tyco Electronics Corporation Harrisburg, Pa 17105-3608
DIMENSIONS: INCHES		CHK K WRIGHT 06MAY04	
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD K WRIGHT 06MAY04	
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± -	NAME	
MATERIAL	FINISH	SIZE A1	CAGE CODE 00779
-	-	DRAWING NO 1437539-2	RESTRICTED TO
CUSTOMER DRAWING		SCALE 1:1	SHEET 1 OF 4



8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOCAD

DIST00

REV F

LTR

DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1

-

-

-

800 SERIES MACHINED PREMIUM  
CONTACT LEAD FREE PART NUMBER TABLE

OBSOLETE	HIGH RETENTION		.895/.905	1.000	3.200	2	864-AG34D-LF	5-6437538-4
	HIGH RETENTION		.595/.605	.700	2.400	2	848-AG34D-LF	9-1437538-5
	W/RAILS						840-AR11D-LF	8-1437538-6
	.180 PC LEAD		.595/.605	.700	2.000	2	840-AG43D-LF	8-1437538-4
	HIGH RETENTION						840-AG34D-LF	8-1437538-3
	HIGH RETENTION						832-AG38D-LF	9-6437533-4
	HIGH RETENTION		.595/.605	.700	1.600	2	832-AG34D-LF	2-6437538-5
OBSOLETE	W/RAILS						828-AR12D-LF	6-6437538-9
OBSOLETE	W/RAILS		.595/.605	.700	1.400	1	828-AR11D-LF	1-6437538-6
	.180 PC LEAD						828-AG43D-LF	6437538-4
OBSOLETE	HIGH RETENTION						828-AG34D-LF	1-6437538-3
OBSOLETE	W/RAILS		.295/.305	.400	1.200	1	824-AR31D-LF	5-6437538-1
OBSOLETE	W/RAILS		.595/.605	.700	1.200	1	824-AR11D-LF	9-6437537-9
	.180 PC LEAD		.295/.305	.400	1.200	1	824-AG47D-LF	9-6437537-7
OBSOLETE	.180 PC LEAD		.395/.405	.500	1.200	1	824-AG446D-LF	9-6437537-6
	HIGH RETENTION		.595/.605	.700	1.200	1	824-AG34D-LF	9-6437537-5
	HIGH RETENTION						824-AG338D-LF	9-6437537-4
	HIGH RETENTION		.295/.305	.400	1.200	1	824-AG334D-LF	9-6437537-3
	.180 PC LEAD		.295/.305	.400	1.000	1	820-AG43D-LF	7-6437537-3
	HIGH RETENTION						820-AG34D-LF	7-6437537-2
OBSOLETE	.180 PC LEAD W/RAILS		.295/.305	.400	.900	1	818-AR44D-LF	4-6437539-9
OBSOLETE	W/RAILS						818-AR11D-LF	6-6437537-2
OBSOLETE	W/RAILS						816-AR11D-LF	5-6437537-4
	HIGH RETENTION		.295/.305	.400	.800	1	816-AG34D-LF	5-6437537-1
OBSOLETE	W/RAILS						814-AR11D-LF	3-6437537-5
	.180 PC LEAD		.295/.305	.400	.700	1	814-AG43D-LF	3-6437537-2
	HIGH RETENTION						814-AG34D-LF	3-6437537-1
OBSOLETE	W/RAILS		.295/.305	.400	.400	3	808-AR11D-LF	1-6437537-9
	.180 PC LEAD						808-AG43D-LF	6437537-5
	HIGH RETENTION						808-AG34D-LF	6437537-4
	COMMENTS	PLATING	C	B	A	FIG	AUGAT PART NO.	TE PART NO.

800 SERIES MACHINED PREMIUM  
CONTACT PART NUMBER TABLE

OBSOLETE	W/RAILS		.295/.305	.400	1.200	1	824-AR31D	0-1437538-1
	W/RAILS		.595/.605	.700	1.200	1	824-AR11D	9-1437537-9
	-		.395/.405	.500	1.200	1	824-AG66D	9-1437537-8
	.180 PC LEAD		.295/.305	.400	1.200	1	824-AG47D	9-1437537-7
	.180 PC LEAD		.595/.605	.700	1.200	1	824-AG45D	6-1437538-6
OBSOLETE	.180 PC LEAD		.395/.405	.500	1.200	1	824-AG446D	9-1437537-6
	HIGH RETENTION		.595/.605	.700	1.200	1	824-AG34D	9-1437537-5
	HIGH RETENTION					1	824-AG33D	8-1437539-2
	HIGH RETENTION					1	824-AG338D	9-1437537-4
	HIGH RETENTION					1	824-AG334D	9-1437537-3
	-		.295/.305	.400	1.200	1	824-AG32D	9-1437537-2
	-					1	824-AG31D	8-1437537-9
	-					1	824-AG30D	8-1437537-7
	-		.395/.405	.500	1.200	1	824-AG14D	8-1437537-6
	-					1	824-AG12D	8-1437537-5
	-		.595/.605	.700	1.200	1	824-AG11D	8-1437537-2
	-					1	824-AG10D	8-1437537-1
OBSOLETE	-		.395/.405	.500	1.100	1	822-AG11D	7-1437537-8
	-						822-AG10D	7-1437537-7
	W/RAILS						820-AR11D	7-1437537-6
	.180 PC LEAD						820-AG45D	7-1437537-5
	.180 PC LEAD						820-AG44D	7-1437537-4
OBSOLETE	.180 PC LEAD		.295/.305	.400	1.000	1	820-AG43D	7-1437537-3
	HIGH RETENTION						820-AG34D	7-1437537-2
	-						820-AG12D	6-1437537-9
	-						820-AG11D	6-1437537-6
	-						820-AG10D	6-1437537-4
OBSOLETE	.180 PC LEAD W/RAILS		.295/.305	.400	.900	1	818-AR44D	4-1437539-9
	W/RAILS						818-AR11D	6-1437537-2
	.180 PC LEAD						818-AG44D	6-1437537-1
	HIGH RETENTION S/B 5-1437537-7						818-AG34D	5-1437538-8
	-						818-AG12D	6-1437537-0
	-					818-AG11D	5-1437537-7	
	-					818-AG10D	5-1437537-6	
OBSOLETE	W/RAILS		.295/.305	.400	.800	1	816-AR11D	5-1437537-4
	.180 PC LEAD						816-AG45D	5-1437537-3
	.180 PC LEAD						816-AG44D	5-1437537-2
	HIGH RETENTION						816-AG34D	5-1437537-1
	HIGH RETENTION						816-AG33D	5-1437537-0
OBSOLETE	-					816-AG12D	4-1437537-6	
	-					816-AG11D	4-1437537-0	
	-					816-AG10D	3-1437537-7	
OBSOLETE	.180 PC LEAD, W/RAILS S/B 3-1437537-3		.295/.305	.400	.700	1	814-AR44D	5-1437533-2
	W/RAILS						814-AR11D	3-1437537-5
	.180 PC LEAD						814-AG45D	3-1437537-4
	.180 PC LEAD						814-AG44D	3-1437537-3
	.180 PC LEAD						814-AG34D	3-1437537-2
OBSOLETE	HIGH RETENTION						814-AG34D	3-1437537-1
	-						814-AG12D	2-1437537-9
	-						814-AG11D	2-1437537-4
	-						814-AG10D	2-1437537-1
	-						808-AR11D	1-1437537-9
OBSOLETE	W/RAILS		.295/.305	.400	.400	3	808-AG45D	1-1437537-8
OBSOLETE	.180 PC LEAD						808-AG44D	1-1437537-7
	.180 PC LEAD						808-AG43D	1-1437537-5
	.180 PC LEAD						808-AG34D	1-1437537-4
	HIGH RETENTION						808-AG12D	1-1437537-2
	-						808-AG11D	0-1437537-8
	-					808-AG10D	0-1437537-5	
	S/B 6-1437529-8		.295/.305	.400	.300	-	806-AG11D	2-1437533-5
	SUPERSEDED BY 6-1437529-5						806-AG10D	2-1437533-3
	COMMENTS	PLATING	C	B	A	FIG	AUGAT PART NO.	TE PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

MATERIAL-

TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± -

FINISH-

DWN R BROWN 06MAY04

CHK K WRIGHT 06MAY04

APVD K WRIGHT 06MAY04

PRODUCT SPEC

APPLICATION SPEC

WEIGHT-

CUSTOMER DRAWING

Tyco Electronics Corporation Harrisburg, Pa 17105-3608

NAME

DIP SOCKET, 800 SERIES

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

00779

1437539-2

SCALE 1:1

SHEET 2 OF 4

REV A4

AMP 4805 REV 31MAR2000

8

7

6

5

4

3

2

1



800 SERIES STAMPED ECONOMY  
CONTACT LEAD FREE PART NUMBER TABLE

OBSOLETE	W/RAILS		.595/.605	.700	2.400	2	848-AR11D-ES-LF	8-1437540-0
OBSOLETE	W/RAILS						840-AR12D-ES-LF	6-6447099-8
OBSOLETE	W/RAILS						840-AR11D-ESL-LF	7-1437540-2
OBSOLETE	W/RAILS		.595/.605	.700	2.000	2	840-AR11D-ES-LF	7-1437540-1
	.180 PC LEAD						840-AG44D-ESL-LF	7-1437540-0
OBSOLETE	W/RAILS						832-AR11D-ESL-LF	0-6437540-9
OBSOLETE	W/RAILS						832-AR11D-ES-LF	0-6437540-8
	.180 PC LEAD		.595/.605	.700	1.600	2	832-AG44D-ES-LF	0-6437540-7
	.180 PC LEAD						832-AG43D-ES-LF	0-6437540-6
OBSOLETE	.180 PC LEAD W/RAILS						828-AR44D-ESL-LF	9-6437539-8
OBSOLETE	W/RAILS		.595/.605	.700	1.400	1	828-AR12D-ES-LF	6-6447099-7
OBSOLETE	W/RAILS						828-AR11D-ES-LF	9-6437539-6
	.180 PC LEAD						828-AG44D-ES-LF	9-6437539-5
OBSOLETE	.180 PC LEAD W/RAILS		.295/.305	.400	1.200	1	824-AR47D-ESL-LF	8-6437533-3
OBSOLETE	W/RAILS		.295/.305	.400	1.200	1	824-AR31D-ES-LF	8-6437539-7
OBSOLETE	W/RAILS		.595/.605	.700	1.200	1	824-AR12D-ES-LF	6-6447099-6
	.180 PC LEAD		.595/.605	.700	1.200	1	824-AG44D-ESL-LF	8-6437539-3
	.180 PC LEAD		.395/.405	.500	1.100	1	822-AG44D-ES-LF	6-6437539-5
OBSOLETE	W/RAILS		.295/.305	.400	1.000	1	820-AR11D-ESL-LF	5-6437539-8
OBSOLETE	W/RAILS						820-AR11D-ES-LF	5-6437539-7
OBSOLETE	W/RAILS						816-AR11D-ESL-LF	3-6437539-5
OBSOLETE	W/RAILS						816-AR11D-ES-LF	3-6437539-4
	.180 PC LEAD		.295/.305	.400	.800	1	816-AG44D-ESL-LF	3-6437539-2
OBSOLETE	W/RAILS		.295/.305	.400	.700	1	814-AR11D-ES-LF	2-6437539-2
OBSOLETE	W/RAILS						808-AR11D-ES-LF	1-6437539-0
	.180 PC LEAD		.295/.305	.400	.400	1	808-AG43D-ES-LF	6437537-6
COMMENTS		PLATING	C	B	A	FIG	AUGAT PART NO.	TE PART NO.

800 SERIES STAMPED ECONOMY  
CONTACT PART NUMBER TABLE

OBSOLETE	.180 PC LEAD W/RAILS		.295/.305	.400	1.200	1	824-AR47D-ESL	8-1437533-3
SUPERSEDED	.180 PC LEAD W/RAILS S/B 8-1437539-3		.595/.605	.700	1.200	1	824-AR44D-ESL	8-1437533-2
OBSOLETE	W/RAILS		.295/.305	.400	1.200	1	824-AR31D-ESL	3-1437540-9
OBSOLETE	W/RAILS						824-AR31D-ES	8-1437539-7
OBSOLETE	W/RAILS						824-AR12D-ES	6-1447099-6
OBSOLETE	W/RAILS		.595/.605	.700	1.200	1	824-AR11D-ESL	8-1437539-6
OBSOLETE	W/RAILS						824-AR11D-ES	8-1437539-5
	-		.395/.405	.500	1.200	1	824-AG66D-ESL	8-1437539-4
	-						824-AG65D-ES	0-1571180-1
OBSOLETE	.180 PC LEAD		.595/.605	.700	1.200	1	824-AG44D-ESL	8-1437539-3
	-						824-AG32D-ES	8-1437539-1
	-						824-AG31D-ESL	7-1437539-7
	-		.295/.305	.400	1.200	1	824-AG31D-ES	7-1437539-6
	-						824-AG30D-ESL	7-1437539-4
	-						824-AG30D-ES	7-1437539-3
	-						824-AG12D-ES	7-1437539-2
	-		.595/.605	.700	1.200	1	824-AG11D-ESL	7-1437539-0
	-						824-AG11D-ES	6-1437539-9
	-						824-AG10D-ES	6-1437539-7
OBSOLETE	.180 PC LEAD						822-AG44D-ES	6-1437539-5
	-						822-AG12D-ES	6-1437539-4
	-		.395/.405	.500	1.100	1	822-AG11D-ESL	6-1437539-3
	-						822-AG11D-ES	6-1437539-2
OBSOLETE	-						822-AG10D-ES	6-1437539-0
SUPERSEDED	.180 PC LEAD W/RAILS S/B 7-1437537-4						820-AR44D-ESL	7-1437533-1
OBSOLETE	W/RAILS						820-AR11D-ESL	5-1437539-8
OBSOLETE	W/RAILS		.295/.305	.400	1.000	1	820-AR11D-ES	5-1437539-7
	.180 PC LEAD S/B 7-1437537-4						820-AG44D-ES	7-1437533-0
	-						820-AG12D-ES	5-1437539-6
	-						820-AG11D-ESL	5-1437539-3
	-						820-AG11D-ES	5-1437539-2
	-						820-AG10D-ES	5-1437539-0
	.180 PC LEAD W/RAILS S/B 4-1437539-9						818-AR44D-ESL	6-1437533-4
OBSOLETE	W/RAILS						818-AR11D-ESL	4-1437539-8
OBSOLETE	W/RAILS						818-AR11D-ES	4-1437539-7
	.180 PC LEAD S/B 6-1437537-1		.295/.305	.400	.900	1	818-AG44D-ESL	6-1437533-3
	-						818-AG12D-ES	4-1437539-6
	-						818-AG11D-ESL	4-1437539-4
	-						818-AG11D-ES	4-1437539-3
	-						818-AG10D-ES	4-1437539-1
OBSOLETE	W/RAILS						816-AR11D-ESL	3-1437539-5
OBSOLETE	W/RAILS						816-AR11D-ES	3-1437539-4
OBSOLETE	.180 PC LEAD		.295/.305	.400	.800	1	816-AG45D-ES	3-1437539-3
	.180 PC LEAD						816-AG44D-ESL	3-1437539-2
	-						816-AG12D-ES	3-1437539-1
	-						816-AG11D-ESL	2-1437539-9
	-						816-AG11D-ES	2-1437539-8
	-						816-AG10D-ES	2-1437539-6
	.180 PC LEAD, W/RAILS S/B 3-1437537-3						814-AR44D-ESL	5-1437533-3
OBSOLETE	W/RAILS						814-AR11D-ESL	2-1437539-3
OBSOLETE	W/RAILS						814-AR11D-ES	2-1437539-2
SUPERSEDED	.180 PC LEAD		.295/.305	.400	.700	1	814-AG45D-ES	2-1437539-1
	.180 PC LEAD S/B 3-1437537-3						814-AG44D-ESL	4-1437540-5
	-						814-AG12D-ES	2-1437539-0
	-						814-AG11D-ESL	1-1437539-7
	-						814-AG11D-ES	1-1437539-6
	-						814-AG10D-ES	1-1437539-4
	.180 PC W/RAILS, S/B 1437539-9						808-AR44D-ESL	3-1437533-1
OBSOLETE	W/RAILS						808-AR11D-ESL	1-1437539-1
	W/RAILS						808-AR11D-ES	1-1437539-0
OBSOLETE	.180 PC LEAD		.295/.305	.400	.400	1	808-AG44D-ESL	0-1437539-9
	.180 PC LEAD						808-AG43D-ES	1-1437537-6
	-						808-AG12D-ES	0-1437539-8
	-						808-AG11D-ESL	0-1437539-6
	-						808-AG11D-ES	0-1437539-5
	-						808-AG10D-ES	0-1437539-2
	S/B 7-1437529-1						806-AG12D-ES	2-1437533-8
	S/B 1437535-8		.295/.305	.400	.300	1	806-AG11D-ESL	8-1437536-5
	S/B 1437535-7						806-AG11D-ES	2-1437533-7
COMMENTS		PLATING	C	B	A	FIG	AUGAT PART NO.	TE PART NO.

800 SERIES STAMPED ECONOMY  
CONTACT PART NUMBER TABLE

OBSOLETE	-						864-AG12D-ES	5-1437538-3
	-		.895/.905	1.000	3.200	2	864-AG11D-ESL	5-1437538-0
	-						864-AG11D-ES	4-1437538-9
OBSOLETE	-						864-AG10D-ES	3-1437540-2
OBSOLETE	W/RAILS						848-AR11D-ESL	6-1437540-2
OBSOLETE	W/RAILS						848-AR11D-ES	3-1437540-0
	-						848-AG12D-ES	2-1437540-8
	-		.595/.605	.700	2.400	2	848-AG11D-ESL	4-1437538-2
	-						848-AG11D-ES	2-1437540-6
OBSOLETE	-						848-AG10D-ES	2-1437540-5
	-		.595/.605	.700	2.100	2	842-AG11D-ESL	2-1437540-4
	-						842-AG11D-ES	2-1437540-3
	.180 PC LEAD W/RAILS S/B 2-1437540-0						840-AR44D-ESL	0-1437534-7
OBSOLETE	W/RAILS						840-AR12D-ES	6-1447099-8
OBSOLETE	W/RAILS						840-AR11D-ESL	2-1437540-2
OBSOLETE	W/RAILS		.595/.605	.700	2.000	2	840-AR11D-ES	2-1437540-1
	.180 PC LEAD						840-AG44D-ESL	2-1437540-0
	-						840-AG12D-ES	1-1437540-9
	-						840-AG11D-ESL	1-1437540-7
	-						840-AG11D-ES	1-1437540-6
	-						840-AG10D-ES	1-1437540-4
OBSOLETE	-		.595/.605	.700	1.800	2	836-AG12D-ES	1-1437540-2
	-						836-AG11D-ESL	1-1437540-1
	-						836-AG11D-ES	1-1437540-0
OBSOLETE	W/RAILS						832-AR11D-ESL	0-1437540-9
OBSOLETE	W/RAILS						832-AR11D-ES	0-1437540-8
	.180 PC LEAD S/B 1437540-1						832-AG45D-ESL	6-1437538-0
	.180 PC LEAD S/B 1437540-7		.595/.605	.700	1.600	2	832-AG44D-ESL	9-1437533-5
OBSOLETE	.180 PC LEAD						832-AG44D-ES	0-1437540-7
	.180 PC LEAD						832-AG43D-ES	0-1437540-6
	-						832-AG12D-ES	0-1437540-5
	-						832-AG11D-ESL	0-1437540-3
	-						832-AG11D-ES	0-1437540-2
	-						832-AG10D-ES	0-1437540-1
OBSOLETE	.180 PC LEAD W/RAILS						828-AR44D-ESL	9-1437539-8
OBSOLETE	W/RAILS						828-AR12D-ES	6-1447099-7
OBSOLETE	W/RAILS						828-AR11D-ESL	9-1437539-7
OBSOLETE	W/RAILS						828-AR11D-ES	9-1437539-6
OBSOLETE	.180 PC LEAD		.595/.605	.700	1.400	1	828-AG44D-ES	9-1437539-5
	-						828-AG12D-ES	9-1437539-4
	-						828-AG11D-ESL	9-1437539-2
	-						828-AG11D-ES	9-1437539-1
	-						828-AG10D-ES	8-1437539-9
COMMENTS		PLATING	C	B	A	FIG	AUGAT PART NO.	TE PART NO.



8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOCAD

DIST00

REV

LT

LT

DESCRIPTION

DATE

DWN

APVD

1000 SERIES MACHINED PREMIUM CONTACT, LOW INSERTION FORCE PART NUMBER TABLE

S/B 4-1437538-8		.895/.905	1.000	3.200	2	1064-AG11D	2-1437529-4
S/B 3-1437540-1		.895/.905	1.000	3.200	2	1064-AG10D	2-1437529-3
S/B 3-1437538-0		.595/.605	.700	2.000	2	1040-AG11D	2-1437529-2
S/B 2-1437538-2		.595/.605	.700	1.600	2	1032-AG11D	2-1437529-1
S/B 1437538-4		.595/.605	.700	1.400	1	1028-AG11D	1-1437529-9
S/B 8-1437537-9		.295/.305	.400	1.200	1	1024-AG31D	1-1437529-8
S/B 8-1437537-2		.595/.605	.700	1.200	1	1024-AG11D	1-1437529-6
S/B 8-1437537-1		.595/.605	.700	1.200	1	1024-AG10D	1-1437529-5
S/B 6-1437537-6		.295/.305	.400	1.000	1	1020-AG11D	1-1437529-4
S/B 6-1437537-4		.295/.305	.400	.900	1	1020-AG10D	1-1437529-3
S/B 5-1437537-7		.295/.305	.400	.900	1	1018-AG11D	1-1437529-2
S/B 5-1437537-6		.295/.305	.400	.900	1	1018-AG10D	1-1437529-1
S/B 4-1437537-0		.295/.305	.400	.800	1	1016-AG11D	1-1437529-0
S/B 3-1437537-7		.295/.305	.400	.800	1	1016-AG10D	0-1437529-9
S/B 2-1437537-4		.295/.305	.400	.700	1	1014-AG11D	0-1437529-7
S/B 2-1437537-1		.295/.305	.400	.700	1	1014-AG10D	0-1437529-6
S/B 1437537-8		.295/.305	.400	.400	3	1008-AG11D	0-1437529-5
S/B 1437537-5		.295/.305	.400	.400	3	1008-AG10D	0-1437529-4
COMMENTS	PLATING	C	B	A	FIG	AUGAT PART NO.	TE PART NO.

1800 SERIES MACHINED PREMIUM CONTACT, LOW GOLD PART NUMBER TABLE

S/B 5-1437538-0		.895/.905	1.000	3.200	2	1864-AG111D	5-1437529-1
S/B 6-1437540-2 W/RAILS		.595/.605	.700	2.400	2	1848-AR111D	5-1437529-0
S/B 4-1437538-2		.595/.605	.700	2.400	2	1848-AG111D	4-1437529-9
S/B 2-1437540-4		.595/.605	.700	2.100	2	1842-AG111D	4-1437529-8
S/B 2-1437540-2 W/RAILS		.595/.605	.700	2.000	2	1840-AR111D	4-1437529-7
S/B 1-1437540-7		.595/.605	.700	2.000	2	1840-AG111D	4-1437529-6
S/B 1437540-3		.595/.605	.700	1.600	2	1832-AG111D	4-1437529-5
S/B 9-1437539-7 W/RAILS		.595/.605	.700	1.400	1	1828-AR111D	4-1437529-4
S/B 9-1437539-2		.595/.605	.700	1.400	1	1828-AG111D	4-1437529-3
S/B 3-1437540-9 W/RAILS		.295/.305	.400	1.200	1	1824-AR131D	4-1437529-2
S/B 8-1437539-6 W/RAILS		.595/.605	.700	1.200	1	1824-AR111D	4-1437529-1
S/B 8-1437539-4		.395/.405	.500	1.200	1	1824-AG141D	4-1437529-0
S/B 7-1437539-7		.295/.305	.400	1.200	1	1824-AG131D	3-1437529-9
S/B 7-1437539-0		.595/.605	.700	1.200	1	1824-AG111D	3-1437529-8
S/B 6-1437539-3		.395/.405	.500	1.100	1	1822-AG111D	3-1437529-7
S/B 5-1437539-8 W/RAILS		.295/.305	.400	1.000	1	1820-AR111D	3-1437529-6
S/B 5-1437539-3		.295/.305	.400	1.000	1	1820-AG111D	3-1437529-5
S/B 4-1437539-8 W/RAILS		.295/.305	.400	.900	1	1818-AR111D	3-1437529-4
S/B 4-1437539-4		.295/.305	.400	.900	1	1818-AG111D	3-1437529-3
S/B 3-1437539-5 W/RAILS		.295/.305	.400	.800	1	1816-AR111D	3-1437529-2
S/B 2-1437539-9		.295/.305	.400	.800	1	1816-AG111D	3-1437529-1
S/B 2-1437539-3 W/RAILS		.295/.305	.400	.700	1	1814-AR111D	3-1437529-0
S/B 1-1437539-7		.295/.305	.400	.700	1	1814-AG111D	2-1437529-9
S/B 1-1437539-1 W/RAILS		.295/.305	.400	.400	3	1808-AR111D	2-1437529-6
S/B 1437539-6		.295/.305	.400	.400	3	1808-AG111D	2-1437529-5
S/B 1437535-8		.295/.305	.400	.300		1806-AG111D	0-1437535-2
COMMENTS	PLATING	C	B	A	FIG	AUGAT PART NO.	TE PART NO.

AMP 4805 REV 31MAR2000

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± .005

4 PLC ± -

ANGLES ± -

FINISH -

MATERIAL -

FINISH -

DWN R BROWN 06MAY04

CHK K WRIGHT 06MAY04

APVD K WRIGHT 06MAY04

PRODUCT SPEC

APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING

Tyco Electronics Corporation

Harriaburg, Pa 17105-3608

DIP SOCKET, 800 SERIES

SIZE A1

CAGE CODE 00779

DRAWING NO 1437539-2

RESTRICTED TO -

SCALE 1:1

SHEET 4 OF 4

REV A4



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-1437539-6](#)