





REVISIONS					
P.	LTR.	DESCRIPTION	DATE	OWN	APVD
-	-	SEE SHEET 1	-	-	-




1438129-1
KEYING OPTION "A"




1438129-2
KEYING OPTION "B"




1438129-3
KEYING OPTION "C"



1438129-4
KEYING OPTION "D"



1438129-5
KEYING OPTION "E"



1438129-6
KEYING OPTION "F"

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN R. VESTAL 15APR2005	TE Connectivity	
DIMENSIONS:		CHK T. VALASEK 15APR2005		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD T. VALASEK 15APR2005	NAME 50-WAY HARNESS ASSEMBLY, PCM	
	0 PLC ±.3 1 PLC ±0.3 2 PLC ±0.10 3 PLC ±. 4 PLC ±. ANGLES ±1° FINISH	PRODUCT SPEC APPLICATION SPEC	SIZE CAGE CODE DRAWING NO	
MATERIAL	-	WEIGHT	A 00779 C=1438129	
-	-	CUSTOMER DRAWING	RESTRICTED TO	
		SCALE 2:1	SHEET 2 OF 10	REV F41

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

KEYING OPTION B

CAVITIES WITH A NUMERIC SYMBOL INDICATES CLOSED TERMINAL LOCATIONS


BLANK CAVITIES INDICATES OPEN TERMINAL HOLE LOCATIONS


TERMINAL HOLE POSITION

5S4T-14A464-M* PIN-OUT CHART



ASSEMBLY
PART
NUMBER

PART NUMBER
FOR PRINTING


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN CHK T. VALASEK	15APR2005	 TE Connectivity	
DIMENSIONS: mm		APVD T. VALASEK	15APR2005		
		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±.0 1 PLC ±0.3 2 PLC ±0.10 3 PLC ±.1 4 PLC ±.15 ANGLES ±1°		NAME 50-WAY HARNESS ASSEMBLY, PCM	
MATERIAL -		FINISH -		SIZE A	
				CAGE CODE 100779	
				DRAWING NO C=1438129	
				RESTRICTED TO REV F 41	
				SCALE 1:1	
				SHEET 4	
				OF 10	
				CUSTOMER DRAWING	



SCALE 2:1




SECTION B-B



DETAIL E
SCALE 8:1

NOTES: UNLESS OTHERWISE SPECIFIED

- GENERAL TOLERANCE:
±0.3 ALL ONE PLACE DIMENSIONS
±0.10 ALL TWO PLACE DIMENSIONS
±1°00' ALL ANGULAR DIMENSIONS
- DRAFT ANGLE PERMISSIBLE ONLY WITHIN DRAWING TOLERANCE.
- SEALING SURFACE, NO WITNESS LINES OR DAMAGE PERMITTED.
- ALL UNMARKED RADIUS TO BE 0.5 MAX., UNLESS OTHERWISE SPECIFIED.
- VENT HOLE SIZE AND LOCATION IS OPTIONAL.
- THIS AREA TO REMAIN CLEAR FOR THE HARNESS ASSEMBLY.
- TERMINAL POSITION IDENTIFICATION.
- MATES WITH TYCO ELECTRONICS PART NUMBERS 1438129-# & 1438950-#












SECTION A-A

SEE RECOMMENDED CONTACT
PIN 0.8 X 1.5 DETAIL

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN R. VESTAL 15APR2005		TE Connectivity	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK T. VALASEK 15APR2005			
		APVD T. VALASEK 15APR2005			
		PRODUCT SPEC -			
	0 PLC ±0.3	APPLICATION SPEC -	NAME 50-WAY HARNESS ASSEMBLY, PCM		
	1 PLC ±0.3				
MATERIAL - - -	2 PLC ±0.10	SIZE CAGE CODE DRAWING NO A 00779 C = 1438129	RESTRICTED TO		
	3 PLC ±0.10				
	4 PLC ±0.10				
	ANGLES ±1°				
FINISH -	WEIGHT -	CUSTOMER DRAWING	SCALE 1:1	SHEET 9 OF 10	REF 4

HEADER INTERFACE KEYING OPTIONS



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. VESTAL 15APR2005	TE Connectivity	
DIMENSIONS:		CHK T. VALASEK 15APR2005		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD T. VALASEK 15APR2005	NAME 50-WAY HARNESS ASSEMBLY, PCM	RESTRICTED TO
	0 PLC ±0.3 1 PLC ±0.3 2 PLC ±0.10 3 PLC ±0.1 4 PLC ±0.1	PRODUCT SPEC	SIZE A100779	10 OF 10
MATERIAL	FINISH	APPLICATION SPEC	WEIGHT	REV F41
-	-	CUSTOMER DRAWING	SCALE 1:1	SHEET 10

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[8-1438129-4](#)