






PART NUMBER:  
1438136-1  
SHOWN WITH SPACER  
IN SEATED POSTION



| REVISIONS |      |                           |           |      |       |
|-----------|------|---------------------------|-----------|------|-------|
| P.        | LTR. | DESCRIPTION               | DATE      | DWN. | APVD. |
| G45       |      | REVISED PER ECO-13-011449 | 16JUL2013 | DLD  | DCM   |
| G46       |      | REVISED PER ECO-14-007153 | 19MAY2014 | DLD  | DCM   |
| G47       |      | REVISED PER ECO-14-014965 | 09OCT2013 | DLD  | DCM   |
| G48       |      | REVISED PER ECO-20-012739 | 05OCT2020 | AP   | CM    |

1. PRINT FORD PART NUMBER (SEE ATTACHED CHARTS) AND TRACEABILITY CODE (YY = 2 DIGIT YEAR, JJJ = JULIAN DATE, HH = 2 DIGIT MILITARY HOUR) IN THIS LOCATION AT ASSEMBLY. SEE SHEETS 3, 4 AND 5 (-\*) PART NUMBERS.


2. APPLICABLE MOLEX (1.5) POWER TERMINAL PART NUMBERS:  
33012-0002 TIN 0.50-1.50mm<sup>2</sup>

3. CAM LEVER AND SPACER ARE SHIPPED IN THEIR PRE-ASSEMBLED POSITIONS.



4. REFERENCE TE INSTRUCTION SHEET 408-8893.

△ COMPANY LOGO.



△ OBSOLETE PART.



SECTION A-A  
SPACER AND LEVER  
IN PRE-SEATED POSITION  
(DELIVERY POSITION)



SHOWN WITH CAM  
LEVER AND SPACER  
IN LOADED POSTION



MIN. FEED THRU CONDITION  
WITH 1mm CLEARANCE ALL AROUND  
SHOWN WITH SPACER IN SEATED POSTION

APPLICABLE COMPONENTS (FOR REFERENCE ONLY)




| DESCRIPTION            | NOMINAL<br>TERMINAL SIZE | COLOR/<br>PLATING | FORD COMPONENT<br>PART NUMBER | SUPPLIER<br>PART NUMBER | MATERIAL/SPECIFICATION<br>NUMBER | SAE<br>WIRE SIZE |
|------------------------|--------------------------|-------------------|-------------------------------|-------------------------|----------------------------------|------------------|
| TERMINAL - FEMALE (Ag) | 0.64 (CAT. 0)            | SILVER            | 7S4T-14474-AA                 | 1393366-2               | COPPER ALLOY/SILVER PLATE        | 20AWG<br>18AWG   |
| TERMINAL - FEMALE (Ag) | 0.64 (CAT. 0)            | SILVER            | 7S4T-14474-BA                 | 1393367-2               | COPPER ALLOY/SILVER PLATE        | 22AWG            |
| TERMINAL - FEMALE (Sn) | 0.64 (CAT. 0)            | TIN               | 1L2T-14474-AA                 | 1393366-1               | COPPER ALLOY/TIN PLATE           | 20AWG<br>18AWG   |
| TERMINAL - FEMALE (Sn) | 0.64 (CAT. 0)            | TIN               | 1L2T-14474-BA                 | 1393367-1               | COPPER ALLOY/TIN PLATE           | 22AWG            |
| TERMINAL - FEMALE (Au) | 0.64 (CAT. 0)            | GOLD              | 1L2T-14474-CA                 | 1393365-1               | COPPER ALLOY/GOLD PLATE          | 20AWG<br>18AWG   |
| TERMINAL - FEMALE (Au) | 0.64 (CAT. 0)            | GOLD              | 1L2T-14474-DA                 | 1393364-1               | COPPER ALLOY/GOLD PLATE          | 22AWG            |

SEE SHEETS 3 THRU 7  
PART NUMBER


|                                        |  |                                                                              |           |                                 |  |
|----------------------------------------|--|------------------------------------------------------------------------------|-----------|---------------------------------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |  | DWN<br>R. VESTAL                                                             | 15APR2005 | TE Connectivity                 |  |
|                                        |  | CHK<br>T. VALASEK                                                            | 15APR2005 |                                 |  |
| DIMENSIONS:                            |  | TOLERANCES UNLESS<br>OTHERWISE SPECIFIED:                                    |           | NAME                            |  |
| mm                                     |  | 0 PLC ±.3<br>1 PLC ±0.3<br>2 PLC ±0.10<br>3 PLC ±.<br>4 PLC ±.<br>ANGLES ±1° |           | PRODUCT SPEC                    |  |
|                                        |  |                                                                              |           | APPLICATION SPEC                |  |
| MATERIAL                               |  |                                                                              |           | WEIGHT                          |  |
|                                        |  |                                                                              |           | CUSTOMER DRAWING                |  |
|                                        |  |                                                                              |           | SIZE CAGE CODE DRAWING NO       |  |
|                                        |  |                                                                              |           | A100779C=1438136                |  |
|                                        |  |                                                                              |           | RESTRICTED TO                   |  |
|                                        |  |                                                                              |           | SCALE 2:1 SHEET 1 OF 11 REV G48 |  |




| REVISIONS |      |             |      |      |       |
|-----------|------|-------------|------|------|-------|
| P.        | LTR. | DESCRIPTION | DATE | DWN. | APVD. |
| -         | -    | SEE SHEET 1 | -    | -    | -     |
|           |      |             |      |      |       |
|           |      |             |      |      |       |




KEYING OPTION "A"




KEYING OPTION "B"




KEYING OPTION "C"



KEYING OPTION "D"



KEYING OPTION "E"



KEYING OPTION "F"

|                                        |                                        |                            |                         |               |
|----------------------------------------|----------------------------------------|----------------------------|-------------------------|---------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |                                        | DWN. R. VESTAL 15APR2005   | TE Connectivity         |               |
| DIMENSIONS:                            |                                        | CHKD. T. VALASEK 15APR2005 |                         |               |
| mm                                     | TOLERANCES UNLESS OTHERWISE SPECIFIED: | APVD. T. VALASEK 15APR2005 | NAME                    |               |
|                                        | 0 PLC ±.3                              | PRODUCT SPEC               | 70-WAY HARNESS ASSEMBLY |               |
|                                        | 1 PLC ±0.3                             | APPLICATION SPEC           |                         |               |
|                                        | 2 PLC ±0.10                            | WEIGHT                     | SIZE                    | CAGE CODE     |
|                                        | 3 PLC ±.1                              | CUSTOMER DRAWING           | A100779                 | 1438136       |
|                                        | 4 PLC ±.1                              | SCALE                      | 2:1                     | SHEET 2 OF 11 |
| MATERIAL                               | FINISH                                 | REV                        | 648                     |               |



|                                                                                       |  |                                        |  |                                 |                                                                                                       |                                  |  |  |
|---------------------------------------------------------------------------------------|--|----------------------------------------|--|---------------------------------|-------------------------------------------------------------------------------------------------------|----------------------------------|--|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                |  |                                        |  | DWG<br>R. VESTAL<br>15APR2005   |  TE Connectivity |                                  |  |  |
|                                                                                       |  |                                        |  | CHG<br>T. VALASEK<br>15APR2005  |                                                                                                       |                                  |  |  |
| DIMENSIONS:<br>mm                                                                     |  | TOLERANCES UNLESS OTHERWISE SPECIFIED: |  | APVD<br>T. VALASEK<br>15APR2005 | NAME                                                                                                  |                                  |  |  |
|  |  | 0 PLC ± -                              |  | PRODUCT SPEC                    |                                                                                                       | 70-WAY HARNESS ASSEMBLY          |  |  |
|                                                                                       |  | 1 PLC ±0.3                             |  | -                               |                                                                                                       |                                  |  |  |
|                                                                                       |  | 2 PLC ±0.10                            |  | APPLICATION SPEC                |                                                                                                       |                                  |  |  |
|                                                                                       |  | 3 PLC ± -                              |  | -                               |                                                                                                       |                                  |  |  |
|                                                                                       |  | 4 PLC ± -                              |  | -                               |                                                                                                       |                                  |  |  |
| MATERIAL                                                                              |  | ANGLES ±1°                             |  | SIZE CAGE CODE DRAWING NO       |                                                                                                       | RESTRICTED TO                    |  |  |
| -                                                                                     |  | FINISH                                 |  | WEIGHT                          |                                                                                                       | -                                |  |  |
| -                                                                                     |  | -                                      |  | CUSTOMER DRAWING                |                                                                                                       | SCALE 2:1 SHEET 3 OF 11 REV. 648 |  |  |















|                                                                          |
|--------------------------------------------------------------------------|
| CAVITIES WITH A NUMERIC<br>SYMBOL INDICATES CLOSED<br>TERMINAL LOCATIONS |
| BLANK CAVITIES INDICATES<br>OPEN TERMINAL<br>HOLE LOCATIONS              |

|                                     |                             |
|-------------------------------------|-----------------------------|
| <b>ASSEMBLY<br/>PART<br/>NUMBER</b> | <b>FORD PART<br/>NUMBER</b> |
|-------------------------------------|-----------------------------|

4805 (3/13)



| REVISIONS |     |             |  |  |      |     |
|-----------|-----|-------------|--|--|------|-----|
| P         | LTR | DESCRIPTION |  |  | DATE | OWN |
| -         | -   | SEE SHEET 1 |  |  | -    | -   |
|           |     |             |  |  |      |     |
|           |     |             |  |  |      |     |
|           |     |             |  |  |      |     |

KEYING OPTION D

CAVITIES WITH A NUMERIC SYMBOL INDICATES CLOSED TERMINAL LOCATIONS

BLANK CAVITIES INDICATES OPEN TERMINAL HOLE LOCATIONS

TERMINAL HOLE POSITION

8U5T-14A464-B\* PIN-OUT CHART

THIS DRAWING IS A CONTROLLED DOCUMENT.

OWN  
R. VESTAL

CHK  
T. VALASEK

APVD  
T. VALASEK

15APR2005

15APR2005

15APR2005

DIMENSIONS:  
mm

0 PLC  
1 PLC  
2 PLC  
3 PLC  
4 PLC  
ANGLES  
FINISH

±  
±0.3  
±0.10  
±  
±  
±1°

MATERIAL

-

MATERIAL

-

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

NAME

70-WAY HARNESS ASSEMBLY

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A100779

©=1438136

SCALE

2:1

SHEET

8

OF

11

REV

648

TE

TE Connectivity



|                              |                          |                      |
|------------------------------|--------------------------|----------------------|
| THIS DRAWING IS UNPUBLISHED. | RELEASED FOR PUBLICATION | 20                   |
| © COPYRIGHT 20               | BY -                     | ALL RIGHTS RESERVED. |

| REVISIONS |     |             |      |     |      |
|-----------|-----|-------------|------|-----|------|
| #         | LTR | DESCRIPTION | DATE | DWN | APVD |
|           | -   | SEE SHEET I | -    | -   | -    |
|           |     |             |      |     |      |
|           |     |             |      |     |      |
|           |     |             |      |     |      |

KEYING OPTION F


[illegible]

KEYING OPTION E

[illegible]

|                                                                                       |  |                                                                                                                       |  |                                                                                                       |  |
|---------------------------------------------------------------------------------------|--|-----------------------------------------------------------------------------------------------------------------------|--|-------------------------------------------------------------------------------------------------------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                |  | DWG<br><b>T. VESTAL</b> 15APR2005<br>CHK<br><b>T. VALASEK</b> 15APR2005<br>APPR<br><b>T. VALASEK</b> 15APR2005        |  |  TE Connectivity |  |
| DIMENSIONS:<br>mm                                                                     |  | TOLERANCES UNLESS OTHERWISE SPECIFIED:<br>0 PLC ±.<br>1 PLC ±0.3<br>2 PLC ±0.10<br>3 PLC ±.<br>4 PLC ±.<br>ANGLES ±1° |  | NAME<br>70-WAY HARNESS ASSEMBLY                                                                       |  |
|  |  | PRODUCT SPEC<br>-<br>APPLICATION SPEC<br>-                                                                            |  | SIZE CAGE CODE DRAWING NO<br>A100779 C1438136                                                         |  |
| MATERIAL<br>-                                                                         |  | WEIGHT<br>-                                                                                                           |  | RESTRICTED TO<br>-                                                                                    |  |
| FINISH<br>-                                                                           |  | CUSTOMER DRAWING<br>-                                                                                                 |  | SCALE 2:1 SHEET 9 OF 11 REV 648                                                                       |  |





1. GENERAL TOLERANCE:  
 $\pm 0.3$  ALL ONE PLACE DIMENSIONS  
 $\pm 0.10$  ALL TWO PLACE DIMENSIONS  
 $\pm 1^{\circ}00'$  ALL ANGULAR DIMENSIONS

3 SEALING SURFACE, NO WITNESS LINES OF DAMAGE PERMITTED.

4. ALL UNMARKED RADII TO BE 0.5 MAX., UNLESS OTHERWISE SPECIFIED

5 VENT HOLE SIZE AND LOCATION IS OPTIONAL.

6 THIS AREA TO REMAIN CLEAR FOR THE HARNESS ASSEMBLY.

 TERMINAL POSITION IDENTIFICATION.

8. MATES WITH TYCO ELECTRONICS PART# 1438136-\*












|                                                                                                            |  |                                                                                                                   |                                                                                                       |                                                                       |
|------------------------------------------------------------------------------------------------------------|--|-------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                                     |  | DWN<br>R. VESTAL<br>15APR2005<br>CHK<br>T. VALASEK<br>15APR2005<br>APVD<br>T. VALASEK<br>15APR2005                |  TE Connectivity |                                                                       |
| DIMENSIONS:<br>mm<br> |  | TOLERANCES UNLESS OTHERWISE SPECIFIED:<br>0 PLC ±<br>1 PLC ±0.3<br>2 PLC ±0.10<br>3 PLC ±<br>4 PLC ±<br>ANGLES ±° |                                                                                                       |                                                                       |
| MATERIAL<br>-<br>-<br>-                                                                                    |  | NAME<br>PRODUCT SPEC<br>-<br>APPLICATION SPEC<br>-<br>WEIGHT<br>-<br>CUSTOMER DRAWING                             |                                                                                                       |                                                                       |
| FINISH<br>-<br>-<br>-                                                                                      |  | SIZE<br>A1<br>CAGE CODE<br>100779<br>DRAWING NO<br>C=1438136                                                      |                                                                                                       | RESTRICTED TO<br>-<br>SCALE<br>2:1<br>SHEET<br>10 OF 11<br>REV<br>648 |



HEADER INTERFACE KEYING OPTIONS

| REVISIONS |      |             |      |      |       |
|-----------|------|-------------|------|------|-------|
| P.        | LTR. | DESCRIPTION | DATE | DWN. | APVD. |
| -         | -    | SEE SHEET 1 | -    | -    | -     |
|           |      |             |      |      |       |
|           |      |             |      |      |       |
|           |      |             |      |      |       |



|                                        |                                        |                            |                                  |  |
|----------------------------------------|----------------------------------------|----------------------------|----------------------------------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |                                        | DWN. R. VESTAL 15APR2005   | TE Connectivity                  |  |
| DIMENSIONS:                            |                                        | CHK. T. VALASEK 15APR2005  |                                  |  |
| mm                                     | TOLERANCES UNLESS OTHERWISE SPECIFIED: | APVD. T. VALASEK 15APR2005 | NAME                             |  |
| 0 PLC ±0.3                             | 1 PLC ±0.10                            | 2 PLC ±0.10                | PRODUCT SPEC                     |  |
| 3 PLC ±0.10                            | 4 PLC ±0.10                            | 5 PLC ±0.10                | APPLICATION SPEC                 |  |
| ANGLES                                 | FINISH                                 | WEIGHT                     | SIZE CAGE CODE DRAWING NO        |  |
| MATERIAL                               |                                        |                            | A100779C=1438136                 |  |
|                                        |                                        |                            | CUSTOMER DRAWING                 |  |
|                                        |                                        |                            | SCALE 2:1 SHEET 11 OF 11 REV 648 |  |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1438136-3](#)