


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AA	00		E5	ADD NEW DASH NUMBER -81	04AUG2015	SZ	SZ



1. HOUSING: GLASS FILLED HIGH TEMP THERMO PLASTIC, COLOR: BLACK, UL 94 V-O RATED
SIGNAL CONTACT: COPPER ALLOY
SIGNAL OVERMOLD: GLASS FILLED POLYESTER
POWER CONTACT: COPPER ALLOY
BOARD LOCKS: COPPER ALLOY
2. CONTACT FINISH: NOBLE METAL PLATING ON CONTACT FUNCTIONAL AREA OF POWER AND SIGNAL CONTACTS,
3. CONTACT MATING AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT, TECHNICAL REFERENCE: GR-1217-CORE, ISSUE 1, NOVEMBER 1995.
4. THIS CONNECTOR EMPLOYS UL RECOGNIZED Z-PACK 2mm HM SIGNAL CONTACTS
5. DATUMS AND BASIC DIMENSIONS TO BE ESTABLISHED BY CUSTOMER.
6. PC BOARD THICKNESS 1.4mm MIN, FOR WAVE SOLDER PC BOARD THICKNESS 2.62 MAX
7. SEE APPLICATION SPEC 114-13215 FOR PLATED THROUGH HOLE INFORMATION
8. SEE CUSTOMER DRAWING 1926731 OR 1926733 FOR MATING CONNECTOR

9. UNPLATED HOLES


2-1926730-5 SHOWN

12	20	1	3	22.60	27.71	20S X 2P	8-1926730-3
12	25	1	4	24.60	29.71	25S X 2P	8-1926730-1
12	15	1	2	20.60	25.71	15S X 2P	8-1926730-0
12	10	1	1	18.60	23.71	10S X 2P	7-1926730-9
36	20	5	3	33.60	38.71	20S X 6P	1-1926730-0
144	40	23	10	91.10	96.21	40S X 24P	7-1926730-7
96	25	15	4	63.10	68.21	25S X 16P	4-1926730-6
72	15	11	2	48.10	53.21	15S X 12P	3-1926730-0
60	25	9	4	46.60	51.71	25S X 10P	2-1926730-5
48	25	7	4	41.10	46.21	25S X 8P	1-1926730-8
24	10	3	1	24.10	29.21	10S X 4P	1926730-1
DIM F	DIM E	DIM D	DIM C	DIM B	DIM A	NUMBER OF POSITIONS	PART NUMBER


1. IT IS THE POLICY OF TYCO ELECTRONICS CORPORATION THAT ALL DIMENSIONS BE SHOWN IN MILLIMETERS UNLESS OTHERWISE SPECIFIED. IF A DIMENSION IS SHOWN IN INCHES, IT IS SUBJECT TO CHANGE AND THE CUSTOMER'S ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST NOTATION.		DWN G. PETERS 19OCT2007	Tyco Electronics Harrisburg, PA 17105-3608					
DIMENSIONS: mm		CHK N. REESER 11APR2008	NAME					
		APVD N. REESER 11APR2008	PRODUCT SPEC					
		108-2325						
		APPLICATION SPEC						
MATERIAL SEE NOTE 1		FINISH SEE NOTE 2		WEIGHT -	SIZE A	CAGE CODE 00779	DRAWING NO 1926730	RESTRICTED TO -
CUSTOMER DRAWING					SCALE 4:1	SHEET 1	OF 3	REV E6

LOC	DIST	REVISIONS					
AA	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		-	-	SEE SHEET 1	-	-	-


D



C



B



C


B

A

A

DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.13 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH		DWN G.PETERS 19OCT2007	Tyco Electronics Harrisburg, PA 17105-3608	
				CHK N.REESER 11APR2008		
		MATERIAL SEE NOTE 1		APVD N.REESER 11APR2008	NAME PLUG ASSEMBLY, RIGHT ANGLE, PASSIVE GUIDE, SIGNAL/POWER, WITH BOARD LOCKS, MINIPAK HDL	
				PRODUCT SPEC 108-2325		
WEIGHT -		CUSTOMER DRAWING		APPLICATION SPEC 114-13215	SIZE A100779C=1926730	
				ANGLES		
SCALE 4:1		SHEET 2 OF 3		REV E6		

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
AA	00	-	-	SEE SHEET 1	-	-



2-1926730-5 SHOWN

RECOMMENDED PRINTED CIRCUIT BOARD LAYOUT

(AS VIEWED FROM COMPONENT SIDE)

DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ±0.13 3 PLC ± 4 PLC ± ANGLES ± FINISH		DWN G. PETERS 19OCT2007	Tyco Electronics Harrisburg, PA 17105-3608	
				CHK N. REESER 11APR2008		
		MATERIAL SEE NOTE 1		APVD N. REESER 11APR2008	NAME PLUG ASSEMBLY, RIGHT ANGLE, PASSIVE GUIDE, SIGNAL/POWER, WITH BOARD LOCKS, MINIPAK HDL	
				PRODUCT SPEC 108-2325		
CUSTOMER DRAWING		SCALE 4:1		APPLICATION SPEC 114-13215	SIZE A	
				WEIGHT -		
				RESTRICTED TO -		
				SHEET 3 OF 3	REV E6	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-1926730-0](#)