



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AA	00		A2	REV PER ECO-13-015117	16SEP2013	OL	SZ
			A3	ADD NEW PART 6--2	18NOV2013	OL	SZ
			A4	ECR-15-001425	19JAN2015	SZ	SZ



2-1926739-5 SHOWN

- HOUSING: GLASS FILLED LIQUID CRYSTAL POLYMER, COLOR: BLACK, UL 94 V-0 RATED
SIGNAL CONTACT: PHOSPHOR BRONZE
SIGNAL OVERMOLD: GLASS FILLED POLYESTER
POWER CONTACT: COPPER ALLOY
- SIGNAL CONTACT: 0.00127mm MIN NICKEL ALL OVER,
MATING AREA: 0.00008mm MIN GOLD OVER
0.00076mm MIN PALLADIUM-NICKEL
TAIL AREA: 0.0005mm MIN MATTE TIN




POWER CONTACT: 0.00127mm MIN NICKEL ALL OVER,
MATING AREA: 0.00008mm MIN GOLD OVER
0.00076mm MIN PALLADIUM-NICKEL,
TAIL AREA: 0.0005mm MIN MATTE TIN
- CONTACT MATING AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT,
TECHNICAL REFERENCE: GR-1217-CORE, ISSUE 1, NOVEMBER 1995
- THIS CONNECTOR EMPLOYS UL RECOGNIZED Z-PACK 2mm HM SIGNAL CONTACTS

- 5 DATUMS AND BASIC DIMENSIONS TO BE ESTABLISHED BY CUSTOMER
- 6 PC BOARD THICKNESS 1.4mm MIN, FOR WAVE SOLDER PC BOARD THICKNESS 2.62 MAX
- 7 SEE APPLICATION SPEC 114-13215 FOR PLATED THROUGH HOLE INFORMATION
8. SEE CUSTOMER DRAWING 1926730 OR 1926732 FOR MATING CONNECTOR
- 9 UNPLATED HOLES
- 10 #4-40 UNC PAN HEAD SCREW WITH HEX NUT, NOT SHOWN, SUPPLIED BY CUSTOMER


12	15	1	2	21.94	25.74	15S X 2P	8-1926739-0
144	40	23	7	92.44	96.24	40S X 24P	7-1926739-7
120	35	19	6	79.44	83.24	35S X 20P	6-1926739-2
108	35	17	6	73.94	77.74	35S X 18P	5-1926739-5
96	25	15	4	64.44	68.24	25S X 16P	4-1926739-6
72	15	11	2	49.44	53.24	15S X 12P	3-1926739-0
48	20	7	3	40.44	44.24	20S X 8P	1-1926739-1
72	25	11	4	51.44	57.24	25S X 12P	1926739-9
48	25	7	4	42.44	46.24	25S X 8P	1-1926739-8
36	20	5	3	36.74	40.54	20S X 6P	1-1926739-0
60	25	9	4	47.94	51.74	25S X 10P	2-1926739-5
F PLC	E PLC	D SPACES	C SPACES	DIM B	DIM A	NO OF POSITIONS	PART NUMBER

THIS DRAWING IS UNPUBLISHED. IT IS SUBJECT TO CHANGE WITHOUT NOTICE AND WITHOUT LIABILITY. ANY CHANGES TO THIS DRAWING SHOULD BE CONTACTED FOR THE LATEST REVISION.				DWN ORLANDO LI 28OCT2011	Tyco Electronics Shanghai, PR 200233		
DIMENSIONS:				CHK SUNY ZHAO 28OCT2011			
mm				APVD SUNY ZHAO 28OCT2011	NAME RECEPTACLE ASSEMBLY, RIGHT ANGLE, PASSIVE GUIDE, SIGNAL/POWER, WITH SCREW MOUNT, MINIPAK HDL		
TOLERANCES UNLESS OTHERWISE SPECIFIED:				PRODUCT SPEC			
0 PLC ±				108-2325	SIZE CAGE CODE DRAWING NO		
1 PLC ±				APPLICATION SPEC			
2 PLC ±				114-13215	RESTRICTED TO		
3 PLC ±				ANGLES			
4 PLC ±				FINISH	A 00779 C=1926739		
MATERIAL SEE NOTE 1				WEIGHT			
SEE NOTE 2				Customer Drawing	SCALE 3:1 SHEET 1 OF 3 REV A4		

LOC	DIST	REVISIONS					
AA	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		-	-	SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND SHOULD BE CONTACTED FOR THE LATEST REVISION. SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN	ORANDO LI	28OCT2011	Tyco Electronics Shanghai, PR 200233			
		CHK	SUNY ZHAO	28OCT2011				
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:			NAME			
mm		0 PLC ±			RECEPTACLE ASSEMBLY, RIGHT ANGLE, PASSIVE GUIDE, SIGNAL/POWER, WITH SCREW MOUNT, MINIPAK HDL			
		1 PLC ±0.13						
		2 PLC ±			SIZE			
		3 PLC ±			CAGE CODE			
		4 PLC ±						
ANGLES		FINISH		DRAWING NO				
					RESTRICTED TO			
MATERIAL		WEIGHT		A100779C=1926739				
SEE NOTE 1		SEE NOTE 2		Customer Drawing				
				SCALE 3:1 SHEET 2 OF 3 REV A4				



2-1926739-5 SHOWN

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-1926739-0](#)