






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	ECR-19-014657	13DEC2020	RR	SZ



1. MATERIAL: HOUSING – HIGH TEMPERATURE NYLON, BLACK,
IR COMPATIBLE, UL 94V-O.
TERMINALS – 0.33[.013] THICK PHOS BRONZE
PLATED WITH 1.27 μ m[.000050] MINIMUM
HARD GOLD ON LOCALIZED AREA AND 3.81 μ m
[.000150] MINIMUM MATTE TIN IN SOLDER AREA
OVER 1.27 μ m [.000050] MINIMUM NICKEL
UNDERPLATE.
-  JACK CAVITY CONFORMS TO FCC RULES AND
REGULATIONS, PART 68 SUBPART F.
-  CAUTION: CATEGORY 5 JACK SOLDER TAIL
POSITIONS DO NOT FOLLOW SAME NUMBER
SEQUENCE AS THAT OF THE TRADITIONAL
JACKS.



1932371-1
PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TERRY.YU 19MAY2009	 TE Connectivity			
		CHK MARTIN.LI 19MAY2009				
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD STEVEN.YAO 19MAY2009	NAME MODULAR JACK ASSEMBLY, 4 PORT, 8 POSITION, RIGHT ANGLE, CATEGORY 5e			
		PRODUCT SPEC 108-1392				
		APPLICATION SPEC 114-2048				
		SIZE A2			CAGE CODE 00779	DRAWING NO C-1932371
MATERIAL SEE NOTE 1	FINISH SEE NOTE 1	WEIGHT 0.000000	SCALE 4:1		SHEET 1 OF 1	REV Δ 1
CUSTOMER DRAWING						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1932371-1](#)