




LOC		DIST		REVISES			
AD		00		P	LTR	DESCRIPTION	DATE
				C		REVISED PER ECO-13-002771	25FEB2013
				D		REVISED PER ECO-19-009248	08JUL2019

- 1 MATERIAL:
CONTACT AND SHIELD: PHOS BRONZE
HOUSING AND CHICKLET: LCP, UL 94V-0, COLOR: BLACK
- 2 FINISH:
CONTACT AREA FINISH CONFORMS TO THE REQUIREMENTS OF TE PRODUCT SPECIFICATION 108-2303; BASED ON TELCORDIA GR-1217-CORE FOR SYSTEM QUALITY LEVEL III APPLICATIONS IN CONTROLLED ENVIRONMENTS (CENTRAL OFFICE).
COMPLIANT PIN AREA- 0.5µm MIN MATTE TIN OVER 1.27µm MIN NICKEL.
SHIELD 1.27µm MIN NICKEL.
- 3 CONNECTOR MARKED WITH PART NUMBER, DATE CODE, AND STANDARD IN APPROXIMATE AREA SHOWN.
- 4 DIMENSION APPLIES TO CENTERLINE OF THRU HOLE.
- 5 DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
6. CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT.
TECHNICAL REFERENCE: GR-1217-CORE, ISSUE 1, NOVEMBER 1995.
- 7 REFERENCE APPLICATION SPEC 114-13202 FOR RECOMMENDED PLATED THRU HOLE DIAMETER AND PLATING THICKNESS.
- 8 ALL GROUNDS IN ODD NUMBERED COLUMNS ARE COMMONED.
ALL GROUNDS IN EVEN NUMBERED COLUMNS, EXCEPT FOR ROW A ARE COMMONED.
- 9 SHOWN LOGO OR OTHER TE OWNED LOGOS IN APPROXIMATE AREA.

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN W. SOURBEER 13AUG2007	TE Connectivity	
		CHK W. DAVIS 13AUG2007		
DIMENSIONS:		APVD R. PATTERSON 12OCT2007	NAME	
mm		PRODUCT SPEC	RIGHT ANGLE HEADER ASSEMBLY, DOUBLE WALL, 5 PAIR, 8 COLUMN, Z-PACK TinMan	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	SIZE	
0 PLC ±			CAGE CODE	
1 PLC ±			DRAWING NO	
2 PLC ±			RESTRICTED TO	
3 PLC ±			A100779C=1934350	
4 PLC ±			SCALE	
ANGLES			6:1	
FINISH			SHEET	
MATERIAL			1 OF 1	
CUSTOMER DRAWING			REV	
			D	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1934350-1](#)