

4

15

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By - TE CONNECTIVITY

ALL RIGHTS RESERVED.

LOC
HB

DIST

—


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	C1	CHANGE LOGO&ADD LINE IDENTIFICATION ECO-12-001771	22Aug2012	YS.H	BH.Y



PART A

PART B



14.6 ±0.5

C:MADE IN CHINA


LOT NO. (C) SEE NOTE 5 (C)

0.45

0.3


0.3

4.1 ±0.3



1

1



CONNECTION FIGURE





FIGURE FOR PRINTED CIRCUIT BOARD PROCESSING (BOTTOM VIEW)



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H.Sasaki	TE Connectivity		
		CHK A.Nagai			
DIMENSIONS: mm		APVD Y.Oikawa	NAME OJ-SH-DM SPEC.000 CUSTOMER DRWAING		
		PRODUCT SPEC	SIZE A3		
		APPLICATION SPEC	CAGE CODE 00779		
MATERIAL		FINISH	DRAWING NO 1461406		
			RESTRICTED TO		
		WEIGHT	CUSTOMER DRAWING		
			SCALE 5:1	SHEET 1 OF 2	REV C1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-.-

© COPYRIGHT - By - TE CONNECTIVITY

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

HB

-

P

LTR

DESCRIPTION

DATE

DWN

APVD

-

-

SEE SHEET 1

-

-

-

Ⓒ	OBSOLETE	1461406-6	OJ-SH-148DM, 000	107-79010	48V	OJ-SH-148DM	g
	ACTIVE	1461406-5	OJ-SH-124DM, 000	107-79010	24V	OJ-SH-124DM	f
	ACTIVE	1461406-4	OJ-SH-112DM, 000	107-79010	12V	OJ-SH-112DM	e
Ⓒ	OBSOLETE	1461406-3	OJ-SH-109DM, 000	107-79010	9V	OJ-SH-109DM	d
Ⓒ	OBSOLETE	1461406-2	OJ-SH-106DM, 000	107-79010	6V	OJ-SH-106DM	c
	ACTIVE	1461406-1	OJ-SH-105DM, 000	107-79010	5V	OJ-SH-105DM	b
Ⓒ	OBSOLETE	1461406-7	OJ-SH-103DM, 000	107-79010	3V	OJ-SH-103DM	a
	PART STATUS	TE PART NO	TE TYPE NAME	PACKAGE SPEC	PART B	PART A	TYPE

RELAY TYPE

Ⓒ Ⓐ NOTE:

1.LOT NO SYSTEM AS FOLLOWING:

WEEK
YEAR

Ⓒ 2.TERMINAL DIMENSION IS BEFORE SOLDER DIP;

Ⓒ 3.FOR THE TIN-PLATING OF THE PINS:
+0.1mm FOR WIDTH,THICKNESS AND DIAMETER.
+0.5mm FOR LENGTH.

Ⓒ 4.MARKING FROM INK TO LASER.

Ⓒ 5.ADD LOT NO. SYSTEM AS FOLLOWING;

1	1	A
I	II	III

I, DIGITS FOR DAY OF THE WEEK

1...MONDAY IN THIS WEEK;

2...TUESDAY IN THIS WEEK;

.....

7...SUNDAY IN THIS WEEK

II, DIGITS FOR SHIFT OF THE DAY

1...DAY SHIFT IN THIS DAY;

2...NIGHT SHIFT IN THIS DAY;

III, ONE CHARACTER DISTINGUISH THE
LINE IDENTITY, SUCH AS: A,B.....Z

		UV RESIN	SEAL (VENT HOLE)	16
		EPOXY RESIN	SEAL (BASE & BOBBIN)	15
		3UEW	MAGNETIC WIRE	14
94V-0		P.B.T	CASE	13
94V-0		P.B.T	BASE	12
94V-0		P.B.T	BOBBIN	11
	SOLDER DIP	C.P WIRE	COIL TERMINAL	10
94V-0		P.P.S	CARD	9
		Ag ALLOY	MOVABLE CONTACT	8
		Ag	NO.CONTACT	7
		STEEL	HINGE SPRING	6
	SOLDER DIP	PBP	NO.TERMINAL	5
	SOLDER DIP	PBS	MOVABLE SPRING	4
	NIP	STEEL	CORE	3
	NIP	STEEL	ARMATURE	2
	NIP	STEEL	YOKE	1
INCOMBUSTIBILITY	TREATMENT	MATERIAL	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	H.Sasaki	
		CHK	A.Nagai	
DIMENSIONS: mm		APVD	Y.Oikawa	
		PRODUCT SPEC		
		APPLICATION SPEC		
MATERIAL		WEIGHT	-	
FINISH		-		
		CUSTOMER DRAWING		

TE Connectivity		NAME	
-		-	
OJ-SH-DM SPEC.000		CUSTOMER DRAWING	
-		-	
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C= 1461406	-
SCALE 5:1		SHEET 2 OF 2	REV C1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1461406-4](#)