


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		G	EC 0G3C 0808 04	15JAN05	BSV	RB
			G1	REVISED PER ECO-09-021826	03SEP09	KK	AEG



1 DATE CODE AND PART NUMBER ARE MARKED IN APPROXIMATE LOCATION SHOWN. 2 THESE DIMENSIONS PERTAIN TO CAVITY CENTERLINES ONLY, NOT TO CONTACT LOCATIONS 3 TOLERANCE IS NON-CUMULATIVE 4 DUPLEX PLATED: .000030 GOLD ON CONTACT AREA ONLY, .000150-.000300 BRIGHT TIN-LEAD ON SOLDER LEADS, ALL OVER .000050 MIN NICKEL. 5 POINT OF MEASUREMENT FOR PLATING THICKNESS (INSIDE CONTACT BEAMS) 6 HSG: FLAME RETARDANT POLYESTER PCT, COLOR:BLACK 7 CONTACT: PHOS. BRONZE 8 TYCO LOGO AND CSA LOGO ARE MOLDED INTO HOUSING. 9 DUPLEX PLATED: .000030 GOLD ON CONTACT AREA ONLY, .000150-.000300 MATTE TIN ON SOLDER LEADS, ALL OVER .000050 MIN NICKEL. 10 ROHS 2002 /95/EC COMPLIANT. 11 NO PART NUMBER MARKING REQUIRED ON THIS PART. 12 2 POSITION PART HAS THE DATE CODE OPPOSITE OF TYCO LOGO. 13 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI	RECOMMENDED PC BD LAYOUT SECTION X-X	14 OBSOLETE PARTS	<table><tr><th>14</th><th>9</th><th>35.56 [1.400]</th><th>37.97 [1.495]</th><th>30</th><th>5-146219-8</th></tr><tr><th>14</th><th>9</th><th>27.94 [1.100]</th><th>30.35 [1.195]</th><th>24</th><th>5-146219-7</th></tr><tr><th>14</th><th>9</th><th>99.06 [3.900]</th><th>101.47 [3.995]</th><th>80</th><th>5-146219-6</th></tr><tr><th>14</th><th>9</th><th>73.66 [2.900]</th><th>76.07 [2.995]</th><th>60</th><th>5-146219-5</th></tr><tr><th>14</th><th>9</th><th>48.26 [1.900]</th><th>50.67 [1.995]</th><th>40</th><th>5-146219-4</th></tr><tr><th>14</th><th>9</th><th>22.86 [.900]</th><th>25.27 [.995]</th><th>20</th><th>5-146219-3</th></tr><tr><th>11</th><th>9</th><th>10.16 [.400]</th><th>12.57 [.495]</th><th>10</th><th>5-146219-2</th></tr><tr><th>14</th><th>12</th><th>11</th><th>9</th><th>-</th><th>2.41 [.095]</th><th>2</th><th>5-146219-1</th></tr><tr><th colspan="2">FINISH</th><th>B</th><th>A</th><th>NO OF POSN</th><th>PART NUMBER</th></tr></table>	14	9	35.56 [1.400]	37.97 [1.495]	30	5-146219-8	14	9	27.94 [1.100]	30.35 [1.195]	24	5-146219-7	14	9	99.06 [3.900]	101.47 [3.995]	80	5-146219-6	14	9	73.66 [2.900]	76.07 [2.995]	60	5-146219-5	14	9	48.26 [1.900]	50.67 [1.995]	40	5-146219-4	14	9	22.86 [.900]	25.27 [.995]	20	5-146219-3	11	9	10.16 [.400]	12.57 [.495]	10	5-146219-2	14	12	11	9	-	2.41 [.095]	2	5-146219-1	FINISH		B	A	NO OF POSN	PART NUMBER
14	9	35.56 [1.400]	37.97 [1.495]	30	5-146219-8																																																						
14	9	27.94 [1.100]	30.35 [1.195]	24	5-146219-7																																																						
14	9	99.06 [3.900]	101.47 [3.995]	80	5-146219-6																																																						
14	9	73.66 [2.900]	76.07 [2.995]	60	5-146219-5																																																						
14	9	48.26 [1.900]	50.67 [1.995]	40	5-146219-4																																																						
14	9	22.86 [.900]	25.27 [.995]	20	5-146219-3																																																						
11	9	10.16 [.400]	12.57 [.495]	10	5-146219-2																																																						
14	12	11	9	-	2.41 [.095]	2	5-146219-1																																																				
FINISH		B	A	NO OF POSN	PART NUMBER																																																						
THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONS: mm [INCHES] TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH MATERIAL 6 7 DWN J KNAUB 12-12-94 CHK A GABANY 12-12-94 APVD A GABANY 12-12-94 PRODUCT SPEC APPLICATION SPEC WEIGHT CUSTOMER DRAWING Tyco Electronics Tyco Electronics Corporation Harrisburg, Pa 17105-3608 NAME ASSEMBLY, MOD IV, DBL ROW, .100 X .100 VERTICAL MOUNTED, CLOSED ENTRY SIZE A2 CAGE CODE 00779 DRAWING NO C=146219 RESTRICTED TO SCALE 4:1 SHEET 1 OF 1 REV G1																																																											

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[146219-2](#)