




- 1 ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS.
- 2 TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADER IS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD.
- 3 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING.
- 4 POST PLATING: 0.00254-0.00508[.000100-.000200] MATTE TIN-LEAD OVER 0.00127[.000050] NICKEL ENTIRE POST.
- 5 HOUSING: LCP, COLOR-BLACK.
- 6 POST: COPPER ALLOY.
- 7 POST PLATING: 0.00254-0.00508[.000100-.000200] MATTE TIN OVER 0.00127[.000050] NICKEL ENTIRE POST.
- 8 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI.

REVISIONS				
#	DATE	DESCRIPTION	DATE	BY
J2	REVISED PER ECO-16-012733		01SEP2018	RS
J3	REVISED PER ECO-19-004321		22MAR2019	RS



RECOMMENDED PC BOARD MOUNTING DIMENSIONS
FOR .063 [1.60] THICK PC BOARD AND
.012 [.305] STENCIL THICK.

101.19 [3.984]	99.06 [3.900]	39	80	9-146254-0
98.65 [3.884]	96.52 [3.800]	38	78	8-146254-9
96.11 [3.784]	93.98 [3.700]	37	76	8-146254-8
93.57 [3.684]	91.44 [3.600]	36	74	8-146254-7
91.03 [3.584]	88.90 [3.500]	35	72	8-146254-6
88.49 [3.484]	86.36 [3.400]	34	70	8-146254-5
85.95 [3.384]	83.82 [3.300]	33	68	8-146254-4
83.41 [3.284]	81.28 [3.200]	32	66	8-146254-3
80.87 [3.184]	78.74 [3.100]	31	64	8-146254-2
78.33 [3.084]	76.20 [3.000]	30	62	8-146254-1
75.79 [2.984]	73.66 [2.900]	29	60	8-146254-0
73.25 [2.884]	71.12 [2.800]	28	58	7-146254-9
70.71 [2.784]	68.58 [2.700]	27	56	7-146254-8
68.17 [2.684]	66.04 [2.600]	26	54	7-146254-7
65.63 [2.584]	63.5 [2.500]	25	52	7-146254-6
63.09 [2.484]	60.96 [2.400]	24	50	7-146254-5
60.55 [2.384]	58.42 [2.300]	23	48	7-146254-4
58.01 [2.284]	55.88 [2.200]	22	46	7-146254-3
55.47 [2.184]	53.34 [2.100]	21	44	7-146254-2
52.93 [2.084]	50.80 [2.000]	20	42	7-146254-1
50.39 [1.984]	48.26 [1.900]	19	40	7-146254-0
47.85 [1.884]	45.72 [1.800]	18	38	6-146254-9
45.31 [1.784]	43.18 [1.700]	17	36	6-146254-8
42.77 [1.684]	40.64 [1.600]	16	34	6-146254-7
40.23 [1.584]	38.10 [1.500]	15	32	6-146254-6
37.69 [1.484]	35.56 [1.400]	14	30	6-146254-5
35.15 [1.384]	33.02 [1.300]	13	28	6-146254-4
32.61 [1.284]	30.48 [1.200]	12	26	6-146254-3
30.07 [1.184]	27.94 [1.100]	11	24	6-146254-2
27.53 [1.084]	25.40 [1.000]	10	22	6-146254-1
24.99 [.984]	22.86 [.900]	9	20	6-146254-0
22.45 [.884]	20.32 [.800]	8	18	5-146254-9
19.91 [.784]	17.78 [.700]	7	16	5-146254-8
17.37 [.684]	15.24 [.600]	6	14	5-146254-7
14.83 [.584]	12.70 [.500]	5	12	5-146254-6
12.29 [.484]	10.16 [.400]	4	10	5-146254-5
9.75 [.384]	7.62 [.300]	3	8	5-146254-4
7.21 [.284]	5.08 [.200]	2	6	5-146254-3
4.67 [.184]	2.54 [.100]	1	4	5-146254-2
[-]	[-]	0	2	5-146254-1
PLATING	C	B	A	NO. OF POSITIONS
				PART NUMBER

101.19 [3.984]	99.06 [3.900]	39	80	4-146254-0
98.65 [3.884]	96.52 [3.800]	38	78	3-146254-9
96.11 [3.784]	93.98 [3.700]	37	76	3-146254-8
93.57 [3.684]	91.44 [3.600]	36	74	3-146254-7
91.03 [3.584]	88.90 [3.500]	35	72	3-146254-6
88.49 [3.484]	86.36 [3.400]	34	70	3-146254-5
85.95 [3.384]	83.82 [3.300]	33	68	3-146254-4
83.41 [3.284]	81.28 [3.200]	32	66	3-146254-3
80.87 [3.184]	78.74 [3.100]	31	64	3-146254-2
78.33 [3.084]	76.20 [3.000]	30	62	3-146254-1
75.79 [2.984]	73.66 [2.900]	29	60	3-146254-0
73.25 [2.884]	71.12 [2.800]	28	58	2-146254-9
70.71 [2.784]	68.58 [2.700]	27	56	2-146254-8
68.17 [2.684]	66.04 [2.600]	26	54	2-146254-7
65.63 [2.584]	63.5 [2.500]	25	52	2-146254-6
63.09 [2.484]	60.96 [2.400]	24	50	2-146254-5
60.55 [2.384]	58.42 [2.300]	23	48	2-146254-4
58.01 [2.284]	55.88 [2.200]	22	46	2-146254-3
55.47 [2.184]	53.34 [2.100]	21	44	2-146254-2
52.93 [2.084]	50.80 [2.000]	20	42	2-146254-1
50.39 [1.984]	48.26 [1.900]	19	40	2-146254-0
47.85 [1.884]	45.72 [1.800]	18	38	1-146254-9
45.31 [1.784]	43.18 [1.700]	17	36	1-146254-8
42.77 [1.684]	40.64 [1.600]	16	34	1-146254-7
40.23 [1.584]	38.10 [1.500]	15	32	1-146254-6
37.69 [1.484]	35.56 [1.400]	14	30	1-146254-5
35.15 [1.384]	33.02 [1.300]	13	28	1-146254-4
32.61 [1.284]	30.48 [1.200]	12	26	1-146254-3
30.07 [1.184]	27.94 [1.100]	11	24	1-146254-2
27.53 [1.084]	25.40 [1.000]	10	22	1-146254-1
24.99 [.984]	22.86 [.900]	9	20	1-146254-0
22.45 [.884]	20.32 [.800]	8	18	1-146254-9
19.91 [.784]	17.78 [.700]	7	16	1-146254-8
17.37 [.684]	15.24 [.600]	6	14	1-146254-7
14.83 [.584]	12.70 [.500]	5	12	1-146254-6
12.29 [.484]	10.16 [.400]	4	10	1-146254-5
9.75 [.384]	7.62 [.300]	3	8	1-146254-4
7.21 [.284]	5.08 [.200]	2	6	1-146254-3
4.67 [.184]	2.54 [.100]	1	4	1-146254-2
[-]	[-]	0	2	1-146254-1
PLATING	C	B	A	NO. OF POSITIONS
				PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DW: BROWN		TRANSNO
DRAWN BY: GEFORD		TRANSNO		
CHECKED BY: GEFORD		TRANSNO		
APPROVED BY: GEFORD		NAME		
PRODUCT SPEC				
APPLICATION SPEC				
MATERIAL		SIZE		CODE
FINISH		DRAWING NO		RESTRICTED TO
SEE TABLE		A100779		
CUSTOMER DRAWING		SCALE		
		4:1		
		SHEET		
		1 of 1		
		REV		
		J3		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[7-146254-0](#)