

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

LOC

DIST

AD

00

REV

LTR

DESCRIPTION

DATE

DWN

APVD

H

REVISED

PER

ECO-14-000255

16JUL2014

NK

MM

ROW M

ROW N

1

2

3

C REF

4.88

[.192]

POST NUMBER REF.
(SEE TABLE)

A SPACES @ 2.54 = B

0.64±0.03
[.025±.001]
TYP

1.17±0.08
[.046±.003]

2.54
[.100]

4.70
[.185]
(CONTACT AREA)

5.84
[.230]

2.29±0.08
[.090±.003]

3.05±0.38
[.120±.015]

0.64±0.05
[.025±.002]

1.07±0.20
[.042±.008]
2 PLACES

0.38 [.015] M

0.38 [.015] M

4

4

2

3

A SPACES @ 2.54 = B

2.54
[.100]

4.32
[.170]
(CL OF STENCIL
PATTERN)

0.76±0.05
[.030±.002]

3.81±0.05
[.150±.002]

1.02
[.040]

CL OF HOLE
PATTERN

2.54
[.100]

0.02±0.08
[.045±.003] TYP
(PLATED)

RECOMMENDED HOLE SIZE
BEFORE PLATING
ø1.14±0.02
[ø.045±.001]

RECOMMENDED PC BOARD MOUNTING DIMENSIONS
FOR .063[1.60] THICK PC BOARD AND
.012[.305] STENCIL THICK

8

OB

6

101.19
[3.984]

99.06
[3.900]

39

80

4-146269-0

8

OB

6

98.65
[3.884]

96.52
[3.800]

38

78

3-146269-9

8

OB

6

96.11
[3.784]

93.98
[3.700]

37

76

3-146269-8

8

OB

6

93.57
[3.684]

91.44
[3.600]

36

74

3-146269-7

8

OB

6

91.03
[3.584]

88.90
[3.500]

35

72

3-146269-6

8

OB

6

88.49
[3.484]

86.36
[3.400]

34

70

3-146269-5

8

OB

6

85.95
[3.384]

83.82
[3.300]

33

68

3-146269-4

8

OB

6

83.41
[3.284]

81.28
[3.200]

32

66

3-146269-3

8

OB

6

80.87
[3.184]

78.74
[3.100]

31

64

3-146269-2

8

OB

6

78.33
[3.084]

76.20
[3.000]

30

62

3-146269-1

8

OB

6

75.79
[2.984]

73.66
[2.900]

29

60

3-146269-0

8

OB

6

73.25
[2.884]

71.12
[2.800]

28

58

2-146269-9

8

OB

6

70.71
[2.784]

68.58
[2.700]

27

56

2-146269-8

8

OB

6

68.17
[2.684]

66.04
[2.600]

26

54

2-146269-7

8

OB

6

65.63
[2.584]

63.5
[2.500]

25

52

2-146269-6

8

OB

6

63.09
[2.484]

60.96
[2.400]

24

50

2-146269-5

8

OB

6

60.55
[2.384]

58.42
[2.300]

23

48

2-146269-4

8

OB

6

58.01
[2.284]

55.88
[2.200]

22

46

2-146269-3

8

OB

6

55.47
[2.184]

53.34
[2.100]

21

44

2-146269-2

8

OB

6

52.93
[2.084]

50.80
[2.000]

20

42

2-146269-1

8

OB

6

50.39
[1.984]

48.26
[1.900]

19

40

2-146269-0

8

OB

6

47.85
[1.884]

45.72
[1.800]

18

38

1-146269-9

8

OB

6

45.31
[1.784]

43.18
[1.700]

17

36

1-146269-8

8

OB

6

42.77
[1.684]

40.64
[1.600]

16

34

1-146269-7

8

OB

6

40.23
[1.584]

38.10
[1.500]

15

32

1-146269-6

8

OB

6

37.69
[1.484]

35.56
[1.400]

14

30

1-146269-5

8

OB

6

35.15
[1.384]

33.02
[1.300]

13

28

1-146269-4

8

OB

6

32.61
[1.284]

30.48
[1.200]

12

26

1-146269-3

8

OB

6

30.07
[1.184]

27.94
[1.100]

11

24

1-146269-2

8

OB

6

27.53
[1.084]

25.40
[1.000]

10

22

1-146269-1

8

OB

6

24.99
[.984]

22.86
[.900]

9

20

1-146269-0

8

OB

6

22.45
[.884]

20.32
[.800]

8

18

1-146269-9

8

OB

6

19.91
[.784]

17.78
[.700]

7

16

1-146269-8

8

OB

6

17.37
[.684]

15.24
[.600]

6

14

1-146269-7

8

OB

6

14.83
[.584]

12.70
[.500]

5

12

1-146269-6

8

OB

6

12.29
[.484]

10.16
[.400]

4

10

1-146269-5

8

OB

6

9.75
[.384]

7.62
[.300]

3

8

1-146269-4

8

OB

6

7.21
[.284]

5.08
[.200]

2

6

1-146269-3

8

OB

6

4.67
[.184]

2.54
[.100]

1

4

1-146269-2

8

SUPSD BY

5-146269-1

6

2.13
[.084]

[-]

-

2

1-146269-1

FINISH

C

B

A

NO. OF
POSITIONS

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
T. HOFFMAN
OBMA95

CHK
G. DUBNICZKI
04MAR96

APVD
G. DUBNICZKI
04MAR96

NAME
TE Connectivity

DIMENSIONS:
mm [INCHES]

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± 0.51[.02]
3 PLC ± 0.127[.005]
4 PLC ± 0.0127[.0005]
ANGLES ±

0 PLC ± -
1 PLC ± -
2 PLC ± 0.51[.02]
3 PLC ± 0.127[.005]
4 PLC ± 0.0127[.0005]
ANGLES ±

MATERIAL

FINISH
SEE TABLE

WEIGHT
-

SIZE
A1

CODE
00779

DRAWING NO
146269

RESTRICTED TO
-

CUSTOMER DRAWING

SCALE
4:1

SHEET
1

OF
2

REV
H

4805 (3/11)

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

LOC

DIST

AD

00

REVISONS

DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1

1. TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADER IS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD.

2

THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING.

3

RETENTION FEATURES ON SOLDER TAILS, LOCATED AT MANUFACTURERS OPTION.

4

⌀

0.51

[.020]

Ⓜ

FOR KINKED TAILS.

5

HOUSING: LCP, COLOR-BLACK.
POST: COPPER ALLOY.

6

0.000762[.000030] GOLD IN CONTACT AREA.
0.00254-0.00508 [.0000100-.0000200] MATTE TIN-LEAD ON SOLDER TAIL,
ALL OVER 0.00127 [.000050] NICKEL.

7

0.000762[.000030] GOLD IN CONTACT AREA.
0.00254-0.00508 [.0000100-.0000200] MATTE TIN ON SOLDER TAIL,
ALL OVER 0.00127 [.000050] NICKEL.

8

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

8

OBSOLETE

7

101.19

[3.984]

[3.900]

39

80

9-146269-0

8

OBSOLETE

7

98.65

[3.884]

[3.800]

38

78

~~8-146269-9~~

8

OBSOLETE

7

96.11

[3.784]

[3.700]

37

76

~~8-146269-8~~

8

OBSOLETE

7

93.57

[3.684]

[3.600]

36

74

~~8-146269-7~~

8

OBSOLETE

7

91.03

[3.584]

[3.500]

35

72

~~8-146269-6~~

8

OBSOLETE

7

88.49

[3.484]

[3.400]

34

70

~~8-146269-5~~

8

OBSOLETE

7

85.95

[3.384]

[3.300]

33

68

~~8-146269-4~~

8

OBSOLETE

7

83.41

[3.284]

[3.200]

32

66

~~8-146269-3~~

8

OBSOLETE

7

80.87

[3.184]

[3.100]

31

64

~~8-146269-2~~

8

OBSOLETE

7

78.33

[3.084]

[3.000]

30

62

~~8-146269-1~~

8

OBSOLETE

7

75.79

[2.984]

[2.900]

29

60

~~8-146269-0~~

8

OBSOLETE

7

73.25

[2.884]

[2.800]

28

58

~~7-146269-9~~

8

OBSOLETE

7

70.71

[2.784]

[2.700]

27

56

~~7-146269-8~~

8

OBSOLETE

7

68.17

[2.684]

[2.600]

26

54

~~7-146269-7~~

8

OBSOLETE

7

65.63

[2.584]

[2.500]

25

52

~~7-146269-6~~

8

OBSOLETE

7

63.09

[2.484]

[2.400]

24

50

~~7-146269-5~~

8

OBSOLETE

7

60.55

[2.384]

[2.300]

23

48

~~7-146269-4~~

8

OBSOLETE

7

58.01

[2.284]

[2.200]

22

46

~~7-146269-3~~

8

OBSOLETE

7

55.47

[2.184]

[2.100]

21

44

~~7-146269-2~~

8

OBSOLETE

7

52.93

[2.084]

[2.000]

20

42

~~7-146269-1~~

7

50.39

[1.984]

[1.900]

19

40

7-146269-0

8

OBSOLETE

7

47.85

[1.884]

[1.800]

18

38

~~6-146269-9~~

8

OBSOLETE

7

45.31

[1.784]

[1.700]

17

36

~~6-146269-8~~

8

OBSOLETE

7

42.77

[1.684]

[1.600]

16

34

~~6-146269-7~~

8

OBSOLETE

7

40.23

[1.584]

[1.500]

15

32

~~6-146269-6~~

7

37.69

[1.484]

[1.400]

14

30

6-146269-5

8

OBSOLETE

7

35.15

[1.384]

[1.300]

13

28

~~6-146269-4~~

8

OBSOLETE

7

32.61

[1.284]

[1.200]

12

26

~~6-146269-3~~

8

OBSOLETE

7

30.07

[1.184]

[1.100]

11

24

~~6-146269-2~~

8

OBSOLETE

7

27.53

[1.084]

[1.000]

10

22

~~6-146269-1~~

7

24.99

[.984]

[.900]

9

20

6-146269-0

8

OBSOLETE

7

22.45

[.884]

[.800]

8

18

~~5-146269-9~~

7

19.91

[.784]

[.700]

7

16

5-146269-8

7

17.37

[.684]

[.600]

6

14

5-146269-7

7

14.83

[.584]

[.500]

5

12

5-146269-6

7

12.29

[.484]

[.400]

4

10

5-146269-5

7

9.75

[.384]

[.300]

3

8

5-146269-4

7

7.21

[.284]

[.200]

2

6

5-146269-3

8

OBSOLETE

7

4.67

[.184]

[.100]

1

4

~~5-146269-2~~

7

2.13

[.084]

[-]

-

2

5-146269-1

FINISH

C

B

A

NO. OF POSITIONS

LEAD FREE PART NO.S

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

T. HOFFMAN

08MAY95

CHK

G. DUBNICZKI

04MAR96

APVD

G. DUBNICZKI

04MAR96

NAME

TE Connectivity

DIMENSIONS:

mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0. PLC ± -

1. PLC ± -

2. PLC ± 0.51[.02]

3. PLC ± 0.127[.005]

4. PLC ± 0.0127[.0005]

ANGLES ± -

SEE TABLE

APPLICATION SPEC

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

WEIGHT

A1

00779

146269

-

CUSTOMER DRAWING

SCALE

1:1

SHEET

2

OF

2

REV

H

4805 (3/11)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[7-146269-0](#)