


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION
BY AMP INCORPORATED. ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
BD	36						
			P	REDRAWN PER EC 0020-1109-95	30 OCT 95	-	-

D




C

ALTERNATE POSITION FOR
90° CABLE CLAMP



B

A



- 1 BRACKET: STAINLESS STEEL PER QQ-S-766.
U BOLT: STAINLESS STEEL PER ASTM-A-582.
CABLE CLAMP AND HEX NUTS: CARBON STEEL.
PROTECTIVE SLEEVES: POLYVINYL CHLORIDE.
- 2 U BOLT: PASSIVATED.
CABLE CLAMP: 5.08µm[.000200] MIN NICKEL.
HEX NUTS: ZINC PLATED PER ASTM-B-633.

D

C

201847

B

A

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN C.REIFSNYDER 30 OCT 95	AMP Incorporated Harrisburg, PA 17105-3608		
DIMENSIONS: mm [INCHES]		CHK R.STONE 02 NOV 95	NAME CLAMP KIT, UNASSEMBLED, 50 PLACE, STRAIN RELIEF, M SERIES		
		APVD G.A.STEINHAUER 02 NOV 95	SIZE A2		
		PRODUCT SPEC -	CAGE CODE 00779		
		APPLICATION SPEC -	DRAWING NO C-201847		
MATERIAL 1		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±0.38 [.015] 3 PLC ±- 4 PLC ±- ANGLES ±- FINISH 2	WEIGHT -		
		CUSTOMER DRAWING	SCALE 2:1		
			SHEET 1 OF 1		
			REV P		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[201847-1](#)