

THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		REVISIONS	
© COPYRIGHT	By	ALL RIGHTS RESERVED.		P	LTR
				DESCRIPTION	
				DATE	DWN
				APVD	
				T2	REVISED PER ECO-16-004223
				21JUL2016	NK
					MZ

D

D

C


C

B

B

A

A



- 1 0.76µm [.000030] MIN GOLD PER MIL-G-45204 ON MATING END FOR A LENGTH OF 5.08 [.200] MIN WITH A UNIFORM GRADIENT TO 0.25µm [.000010] MIN GOLD PER MIL-G-45204 ON THE REMAINDER OVER 0.76µm [.000030] MIN NICKEL PER QQ-N-290.
- 2 1.27µm [.000050] MIN TIN-LEAD PER MIL-T-10727 OVER 0.76µm [.000030] MIN NICKEL PER QQ-N-290.
- 3 2.54µm [.000100] MIN TIN-LEAD PER MIL-T-10727 OVER 1.27µm [.000050] MIN NICKEL PER QQ-N-290.
- 4 2.54µm [.000100] MIN TIN PER MIL-T-10727 OVER 1.27µm [.000050] MIN NICKEL PER QQ-N-290.
- 5 1.27µm [.000050] MIN TIN PER MIL-T-10727 OVER 0.76µm [.000030] MIN NICKEL PER QQ-N-290.

OBSOLETE

SMALL PACK	4	1	202237-8
STANDARD	4	1	202237-7
SMALL PACK	4	5	202237-6
STANDARD	4	5	202237-5
SMALL PACK	3	2	202237-4
SMALL PACK	3	1	202237-3
STANDARD	3	2	202237-2
STANDARD	3	1	202237-1
PACKAGING TYPE	SOLDER POST FINISH	BODY FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	R.SHIREY	31JUL91	 TE Connectivity							
		CHK	R.STONE	20SEP91								
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	J. WESTMAN	20SEP91	NAME	SOCKET ASSEMBLY, SOLDER POST, TYPE III+				
		0 PLC ± -		PRODUCT SPEC								
		1 PLC ± -		—								
		2 PLC ± 0.13[.005]		APPLICATION SPEC								
		3 PLC ± -		—		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO			
4 PLC ± -		ANGLES ± -		FINISH		A2	00779		C-202237	—		
MATERIAL		SEE CALLOUTS		WEIGHT								
SEE CALLOUTS		SEE CALLOUTS		CUSTOMER DRAWING			SCALE	8:1	SHEET	1 of 1	REV	T2

202237

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[202237-3](#)