



LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION		DATE	DWN	APVD
	C2	REVISED (ECR-13-007117)		30APR2013	B.W	H.K


D



C



B




DIMENSION OF EACH SYMBOL

P/N	POS	A	B	C	D	E	F	G	WEIGHT (gram)
2023308-1	20	9	9.5	4.75	14.4	11.25	10.3	7.5	0.21
2023308-2	30	14	14.5	7.25	19.4	16.25	15.3	12.5	0.285
2023308-3	40	19	19.5	9.75	24.4	21.25	20.3	17.5	0.36
2023308-4	50	24	24.5	12.25	29.4	26.25	25.3	22.5	0.435

2023308-1, -2, -3, -4 : AS SHOWN

D



REFERENCE P.C. BOARD LAYOUT

C

- NOTE:
- DISCOLORATION OR CHANGING TO BRIGHT MAY HAPPEN DURING REFLOW PROCESS. HOWERER IT'S NO IMPACT FOR MECHANICAL/ELECTRICAL PERFORMANCE.
 - PRODUCT MUST MEET CONTROLLED SUBSTANCES PER TE SPEC: TEC-138-702 SPECIAL REQUEST OF LOW HALOGEN SPEC.:
CHLORINE (Cl): 900 ppm MAX.
BROMINE (Br): 900 ppm MAX.
Br+Cl: 1500ppm MAX.
SPECIAL REQUEST OF REACH SvHC SPEC ON NON-METAL MATERIAL:
DBP: 1000 ppm MAX.
DEHP: 1000 ppm MAX.
BBP: 1000 ppm MAX.
HBCDD: 1000 ppm MAX.

⑤	POLYIMIDE FILM	POLYIMIDE	BROWN
④	RIGHT SOLDER PEG	COPPER ALLOY	NICKEL 0.0013 MM MIN. UNDER PLATING
③	LEFT SOLDER PEG	COPPER ALLOY	TIN PLATING 0.002MM MIN. ALL OVER
②	CONTACT	COPPER ALLOY	NICKEL 0.00127mm MIN. ALL OVER AU 0.000025~0.00008mm MIN. AT TINE AU 0.0002~0.0005mm AT CONTACT AREA
①	HOUSING	THERMOPLASTIC (UL94 V-0)	BLACK
ITEM	NAME	MATERIAL	FINISH/COLOR

B

A

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± 0.2
1 PLC	± 0.2
2 PLC	± 0.2
3 PLC	± 0.2
4 PLC	± 0.2
ANGLES	± 2°

FINISH

DWN N.SOONG 04NOV08

CHK C.WAYDE 04NOV08

APVD H.KODAMA 04NOV08

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE Connectivity

NAME

LCD COAXIAL EMBEDDED DISPLAY INTERFACE (LCEDI) SR SERIES RECEPTACLE ASSY

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

C-2023308

SCALE 4:1

SHEET 1 of 2

REV C2

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-,-



COPYRIGHT

By

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1

D

D

C



C

B




B

A



A



DETAIL F
SCALE 8:1



1. MATERIAL: CARRY TAPE: PS, COLOR:BLACK
COVER TAPE: PET; COLOR: CLEAR.
2. CARTON DIMENSIONS: 395X395X225




DIMENSION OF EACH SYMBOL

P/N	POS	H	I	J	K	L	M	N	P
2023308-1	20	8.2	16.4	24	14.7	12.45	10.8	24.4	29.2
2023308-2	30	14.2	28.4	32	19.7	17.45	15.8	32.4	37.2
2023308-3	40	20.2	40.4	44	24.7	22.45	20.8	44.4	49.2
2023308-4	50	26.2	52.4	56	29.7	27.45	25.8	56.4	61.2

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

- 0 PLC ± 0.3
- 1 PLC ± 0.3
- 2 PLC ± 0.3
- 3 PLC ± 0.3
- 4 PLC ± 0.3
- ANGLES ± 2°
- FINISH

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING



TE Connectivity

NAME

LCD COAXIAL EMBEDDED DISPLAY INTERFACE (LCEDI)
SR SERIES
RECEPTACLE ASSY

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-2023308

SCALE

1:1

SHEET

2 OF 2

REV

C2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2023308-3](#)