






LOC		DIST		REVISIONS			
AD	00	P	LYR	DESCRIPTION	DATE	DWN	APVD
		B		REVISED PER ECO-11-025276	05JAN2012	KH	DY

- 1 MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.
- 2 FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN
ON PCB TAILS, NICKEL OVERALL.
- 3 FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN-LEAD
ON PCB TAILS, NICKEL OVERALL.
4. SCREWS PACKAGED IN END OF PACKAGING TUBE.
- 5 FOR GROUNDED GUIDE PIN USE Ø3.56±0.08 PTH,
Ø3.66 DRILL, AND Ø6.5 PAD.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. K. SHOBER 3NOV2011	TE Connectivity	
DIMENSIONS:		CHK J. EABY 3NOV2011		
mm		APVD J. EABY 3NOV2011	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	IMPACT, 2 PAIR, 16 COLUMN, HEADER	
		APPLICATION SPEC	RIGHT GUIDED, LEFT END WALL	
MATERIAL		WEIGHT	SIGNAL MODULE, 0.36 PTH	
FINISH		SIZE	RESTRICTED TO	
SEE TABLE		CAGE CODE	A100779C=2057743	
		CUSTOMER DRAWING	SCALE 6:1 SHEET 1 OF 2 REV B	

LOC	DIST	REVISIONS					
AD	00	REV	LYR	DESCRIPTION	DATE	DWN	APVD
		-	-	SEE SHEET 1	-	-	-

	5.5	2057743-6
	4.9	2057743-5
	4.5	2057743-4
	5.5	2057743-3
	4.9	2057743-2
	4.5	2057743-1
FINISH	DIM M	PART NUMBER

REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. K. SHOBER	3NOV2011	TE Connectivity		
DIMENSIONS:		CHK J. EABY	3NOV2011			
mm		APVD J. EABY	3NOV2011	NAME		
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		IMPACT, 2 PAIR, 16 COLUMN, HEADER		
		9 PLC ±		RIGHT GUIDED, LEFT END WALL		
		1 PLC ±0.25		SIGNAL MODULE, 0.36 PTH		
MATERIAL		2 PLC ±0.13		SIZE		
		3 PLC ±		CAGE CODE		
		5 PLC ±		DRAWING NO		
		4 PLC ±		RESTRICTED TO		
FINISH		ANGLES ±		A100779		
SEE TABLE		WEIGHT		C=2057743		
CUSTOMER DRAWING		SCALE		5:1		
		SHEET		2		
		OF		2		
		REV		B		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2057743-1](#)