






- | | | | | |
|--------|---|---|---------------|----------------|
| FINISH | B | A | NO OF
POSN | PART
NUMBER |
|--------|---|---|---------------|----------------|

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.BINNER CHK J.OLSON 06NOV2002 06NOV02		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME RECEPTACLE ASSEMBLY, MOD IV, DOUBLE ROW, TOP ENTRY, .100X.100CL, VERTICAL MOUNT, AMPMODU	
		0 PLC ± - 1 PLC ± - 2 PLC ± 0.13[.005] 3 PLC ± - 4 PLC ± - ANGLES ± -			
MATERIAL 		FINISH  			
		APVD J.OLSON 06NOV02 PRODUCT SPEC 108-25022 APPLICATION SPEC 114-25018		SIZE A2	
		WEIGHT -		CAGE CODE 00779	
		CUSTOMER DRAWING		DRAWING NO C-146762	
				RESTRICTED TO -	
				SCALE 4:1	
				SHEET 1 of 2	
				REV 15	

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	- , -
© COPYRIGHT - By - ALL RIGHTS RESERVED.		

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	OWN	APVD
AD	00		—	SEE SHEET I	—	—	—

11	99.06[3.900]	101.60[4.000]	80	12	9-146762-0	
11	96.52[3.800]	99.06[3.900]	78	12	8-146762-9	
11	93.98[3.700]	96.52[3.800]	76	12	8-146762-8	
11	91.44[3.600]	93.98[3.700]	74	12	8-146762-7	
11	88.90[3.500]	91.44[3.600]	72	12	8-146762-6	
11	86.36[3.400]	88.90[3.500]	70	12	8-146762-5	
11	83.82[3.300]	86.36[3.400]	68	12	8-146762-4	
11	81.28[3.200]	83.82[3.300]	66	12	8-146762-3	
11	76.20[3.000]	78.74[3.100]	62	12	8-146762-2	
11	73.66[2.900]	76.20[3.000]	60	12	8-146762-1	
11	71.12[2.800]	73.66[2.900]	58	12	8-146762-0	
11	68.58[2.700]	71.12[2.800]	56	12	7-146762-9	
11	66.04[2.600]	68.58[2.700]	54	12	7-146762-8	
11	63.50[2.500]	66.04[2.600]	52	12	7-146762-7	
11	60.96[2.400]	63.50[2.500]	50	12	7-146762-6	
11	58.42[2.300]	60.96[2.400]	48	12	7-146762-5	
11	55.88[2.200]	58.42[2.300]	46	12	7-146762-4	
11	53.34[2.100]	55.88[2.200]	44	12	7-146762-3	
11	50.80[2.000]	53.34[2.100]	42	12	7-146762-2	
11	45.72[1.800]	48.26[1.900]	38	12	7-146762-1	
11	43.18[1.700]	45.72[1.800]	36	12	7-146762-0	
11	40.64[1.600]	43.18[1.700]	34	12	6-146762-9	
11	38.10[1.500]	40.64[1.600]	32	12	6-146762-8	
11	33.02[1.300]	35.56[1.400]	28	12	6-146762-7	
11	30.48[1.200]	33.02[1.300]	26	12	6-146762-6	
11	27.94[1.100]	30.48[1.200]	24	12	6-146762-5	
11	25.40[1.000]	27.94[1.100]	22	12	6-146762-4	
11	17.78[.700]	20.32[.800]	16	12	6-146762-3	
11	15.24[.600]	17.78[.700]	14	12	6-146762-2	
11	12.70[.500]	15.24[.600]	12	12	6-146762-1	
9	11	5.08[.200]	7.62[.300]	6	12	6-146762-0
9	11	2.54[.100]	5.08[.200]	4	12	5-146762-9
9	11		2.54[.100]	2	12 6	5-146762-8
11		22.86[.900]	25.40[1.000]	20	12	5-146762-7
11		78.74[3.100]	81.28[3.200]	64	12	5-146762-6
11		48.26[1.900]	50.80[2.000]	40	12	5-146762-5
11		35.56[1.400]	38.10[1.500]	30	12	5-146762-4
11		20.32[.800]	22.86[.900]	18	12	5-146762-3
9	11	10.16[.400]	12.70[.500]	10	12	5-146762-2
9	11	7.62[.300]	10.16[.400]	8	12	5-146762-1
FINISH	B	A	NO OF POSN		PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.BINNER		06NOV2002		 TE Connectivity	
		CHK J. OLSON		06NOV02			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. OLSON		NAME	
		0 PLC ± -		PRODUCT SPEC		RECEPTACLE ASSEMBLY, MOD IV, DOUBLE ROW, TOP ENTRY, .100X.100CL, VERTICAL MOUNT, AMPMODU	
		1 PLC ± -		108-25022			
		2 PLC ± 0.13[.005]		APPLICATION SPEC			
		3 PLC ± -		114-25018		SIZE	
		4 PLC ± -		WEIGHT		CAGE CODE	
MATERIAL		FINISH		-		DRAWING NO	
		 		A2		00779	
				CUSTOMER DRAWING		C-146762	
						RESTRICTED TO	
						-	
						SCALE	
						1:1	
						SHEET	
						2 of 2	
						REV	
						J5	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-146762-5](#)