

## REVISIONS

| P | LTR | DESCRIPTION          | DATE      | DWN | APVD |
|---|-----|----------------------|-----------|-----|------|
|   | T1  | AS PER ECO-20-015929 | 10NOV2020 | RJ  | MT   |





TABLE OF DIMENSIONS

| PART NUMBER | H              | J              |                | J0             | K              | M              | P               | R               | S             | T              | JW           | Hole DIA       | Torque Nm |
|-------------|----------------|----------------|----------------|----------------|----------------|----------------|-----------------|-----------------|---------------|----------------|--------------|----------------|-----------|
|             | Ref<br>b       | Min<br>a       | Max<br>b       | Max<br>b       | Ref<br>b       | THREAD<br>b    | ±10%<br>b       | ±10%<br>b       | ±10%<br>b     | Ref<br>b       | ±20%<br>b    | ±0.5<br>[0.02] |           |
| 207W213     | 12.0<br>[.47]  | 10.0<br>[.39]  | 4.0<br>[.15]   | 15.3<br>[.60]  | 23.0<br>[.90]  | 20.0<br>[.78]  | 62.0<br>[2.44]  | 49.0<br>[1.93]  | 13.0<br>[.51] | 32.0<br>[1.25] | 1.0<br>[.04] | 24.0<br>[.94]  | 3         |
| 207W223     | 20.0<br>[.78]  | 18.0<br>[.71]  | 7.0<br>[.27]   | 19.5<br>[.76]  | 33.0<br>[1.30] | 30.0<br>[1.18] | 72.0<br>[2.83]  | 59.0<br>[2.32]  | 16.0<br>[.63] | 42.0<br>[1.65] | 1.8<br>[.07] | 34.0<br>[1.33] | 8         |
| 207W234     | 31.0<br>[1.22] | 28.0<br>[1.10] | 12.0<br>[.47]  | 27.0<br>[1.06] | 46.0<br>[1.81] | 42.0<br>[1.65] | 87.0<br>[3.42]  | 74.0<br>[2.91]  | 18.0<br>[.71] | 58.0<br>[2.28] | 2.5<br>[.10] | 47.0<br>[1.85] | 11        |
| 207W245     | 45.0<br>[1.77] | 42.0<br>[1.65] | 18.0<br>[.71]  | 32.2<br>[1.26] | 59.5<br>[2.34] | 56.0<br>[2.20] | 102.0<br>[4.01] | 89.0<br>[3.50]  | 18.0<br>[.71] | 71.0<br>[2.79] | 3.0<br>[.12] | 60.5<br>[2.38] | 14        |
| 207W256     | 68.0<br>[2.67] | 64.0<br>[2.52] | 30.0<br>[1.18] | 39.0<br>[1.53] | 84.0<br>[3.30] | 80.0<br>[3.15] | 122.0<br>[4.80] | 109.0<br>[4.29] | 18.0<br>[.71] | 97.0<br>[3.82] | 3.0<br>[.12] | 85.0<br>[3.34] | 16        |
| 207W264     | 40.0<br>[1.57] | 38.0<br>[1.49] | 15.0<br>[.59]  | 28.3<br>[1.11] | 54.0<br>[2.12] | 50.0<br>[1.97] | 82.0<br>[3.74]  | 82.0<br>[3.22]  | 18.0<br>[.71] | 66.5<br>[2.62] | 2.5<br>[.10] | 55.0<br>[2.16] | 11        |

TE Connectivity. All Rights Reserved.

I



DIMENSIONS:

mm [INCHES]

DWN 25JAN2019

PRAVEEN N T

CHK 25JAN2019

N NAGAR

APVD 25JAN2019

M TAYLOR

PRODUCT SPEC

—

APPLICATION SPEC

—

WEIGHT

—

MATERIAL

SEE SHEET 2

FINISH

—



TE Connectivity Ltd.

NAME

FEEDTHROUGH SEAL

SIZE

A4

CAGE CODE

00779

DRAWING NO

C-207W213-XX-0THRU264-XX-0

RESTRICTED TO

—

CUSTOMER DRAWING

SCALE


DNS

SHEET

1 OF 2

REV T1

|        |               |
|--------|---------------|
| 0 PLC  | ± —           |
| 1 PLC  | ± 0.50 [.10]  |
| 2 PLC  | ± 0.25 [.01]  |
| 3 PLC  | ± 0.13 [.005] |
| 4 PLC  | ± —           |
| ANGLES | ± 1°          |



## REVISIONS

| P | LTR | DESCRIPTION | DATE | DWN | APVD |
|---|-----|-------------|------|-----|------|
|   | —   | SEE SHEET 1 | —    | —   | —    |

## COMPATIBILITY CHART

| MATERIAL DASH NO. | MATERIAL DESCRIPTION               | SPEC REFERENCE | COATING SLASH NUMBER | COATING S NUMBER    |
|-------------------|------------------------------------|----------------|----------------------|---------------------|
| -3                | POLYOLEFIN, SEMI RIGID             | RT-301         | /42; /86; /180       | S1017; S1048; S1030 |
| -4                | POLYOLEFIN, FLEXIBLE               | RT-1304        | /42; /86; /180       | S1017; S1048; S1030 |
| -25               | ELASTOMER, FLUID RESISTANT         | RW-2070        | /42; /86; /225       | S1017; S1048; S1206 |
| -100              | POLYOLEFIN, SEMI FLEXIBLE, ZEROHAL | RW-2082        | /86; /180            | S1048; S1030        |
|                   |                                    |                |                      |                     |

## ORDERING INFORMATION

207W2XX -XX XX /XX -0  
 BASE PART NUMBER \_\_\_\_\_  
 MATERIAL DASH NUMBER \_\_\_\_\_  
 MODIFICATION NUMBER \_\_\_\_\_  
 ADHESIVE SLASH NUMBER \_\_\_\_\_  
 (SEE COMPATIBILITY CHART BELOW)  
 COLOR DESIGNATOR \_\_\_\_\_


## NOTES

- DIMENSIONS APPEARING IN TABLE ARE AS FOLLOWS:
  - AS SUPPLIED
  - AFTER UNRESTRICTED RECOVERY
- COATING IS OPTIONAL. AS SUPPLIED DIMENSIONS APPEARING IN TABLE ARE FOR UNCOATED PARTS WHEN COATING IS ADDED, ENTRY DIAMETERS WILL BE REDUCED BY 1.5mm[.06] MAX.
- RECOMENDED MAXIMUM PANEL THICKNESS IS 8mm[.314].

TE Connectivity. All Rights Reserved.

—



|                                                                                                         |                       |           |                                                                                                                     |                    |                                          |                    |
|---------------------------------------------------------------------------------------------------------|-----------------------|-----------|---------------------------------------------------------------------------------------------------------------------|--------------------|------------------------------------------|--------------------|
| DIMENSIONS:<br>mm [INCHES]                                                                              | DWN<br>PRAVEEN N T    | 25JAN2019 | MATERIAL<br>—                                                                                                       |                    | FINISH<br>—                              |                    |
|                                                                                                         | CHK<br>N NAGAR        | 25JAN2019 | <div>TE Connectivity Ltd.</div> |                    |                                          |                    |
| TOLERANCES UNLESS<br>OTHERWISE SPECIFIED:                                                               | APVD<br>M TAYLOR      | 25JAN2019 |                                                                                                                     |                    |                                          |                    |
| 0 PLC ± —<br>1 PLC ± 0,50 [.10]<br>2 PLC ± 0,25 [.01]<br>3 PLC ± 0,13 [.005]<br>4 PLC ± —<br>ANGLES ± — | PRODUCT SPEC<br>—     |           | NAME<br>FEEDTHROUGH SEAL<br>—                                                                                       |                    |                                          |                    |
|                                                                                                         | APPLICATION SPEC<br>— |           |                                                                                                                     |                    |                                          |                    |
|                                                                                                         | —                     |           | SIZE<br>A4                                                                                                          | CAGE CODE<br>00779 | DRAWING NO<br>G-207W213-XX-0THRU264-XX-0 | RESTRICTED TO<br>— |
|                                                                                                         | WEIGHT                |           |                                                                                                                     |                    |                                          |                    |
|                      | CUSTOMER DRAWING      |           |                                                                                                                     | SCALE<br>DNS       | SHEET<br>2 OF 2                          | REV<br>T1          |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[490499-000](#)